

45.7±0.5 12.8 Ø42.3 Ø40.1 6.1 1 11/16-18 UNEF THREAD

REVISIONS REV ECO DESCRIPTION DATE BY APPR A1 RESEALE NEW DRAWING 01/MAR/22 VITO TOMMY

SIZE 12 CONTACTS / 6 ['] **SIZE 16 CONTACTS** (4 PLACES) (19 PLACES) 47.6 SIZE 20 CONTACT /6 (6 PLACES)

MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); REDUCED DIA. WIRE SEAL

3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE: IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION); IP69K (MATED CONDITION)
- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-29S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL WIRE	CURRENT		
SIZE	O.D.	O.D.	RANGE	RATING		
20	1.02 mm (.040 in)	2.10 mm (.083 in)	16-22 AWG (1.5-0.5mm²)	7.5 AMPS		
16	1.35 mm (.053in)	2.62 mm (.103 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS		
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS		

Ø43.08±0.12 $41.45^{+0.2}_{-0}$

RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS: 1.6 TO 4.7MM



QUANTITY	IUMBER			DESCRIF						
		MATERIALS LIST								
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		SIGNATURES		S DATE		Λ				
		DRAWN:	DRAWN: VITO.LI 01/MAR/22		01/MAR/22	⊦ Am				
2 PL DEC ±0.15 Angles ±1*	CHECKED:	SULLEN.ZHA	NG (02/MAR/22	Sine Syst					
3) Note reference = X		ENGINEER:				1		44724 1		
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMYXI	E (03/MAR/22	-		Clinton		
WEIGHT: 51.1g		CUSTOMER:			29POS, SIZE 24, RD SE					
	THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF PEOPPOLICTION ARE TIME INFORMATION.									
PROCESS SPECIFICATIONS:					B	C-	DWG NO:			

NEXT ASS'S

Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036

DESCRIPTION

29POS, RECEPTACLE, PIN, SIZE 24, RD SEAL, BRA, DURAMATE AHDP

ITEM

29POS. RECEPTACLE, PIN. E 24, RD SEAL, BRA, DURAMATE AHDP

AHDP04-24-29PR-BRA SCALE: NONE DURAMATE SHEET 1 OF 1

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.