


	REVISIONS								
REV	ECO	DESCRIPTION	DATE	BY	APPR				
A1	-	RELEASE NEW DRAWING	28MAR22	VITO	TOMMY				



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC: BLACK

SEAL: SILICONE RUBBER

THREADED INSERT: STAINLESS STEEL

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA.WIRE SEAL: SEALED PANEL MOUNT:

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K (MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-08P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.		TYPICAL WIRE RANGE	CURRENT RATING
12	2.46 mm (.0.97in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



DESCRIPTION

MATERIALS LIST UNLESS OTHERWISE SPECIFIED SIGNATURES DATE 28MAR22 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 SULLENZHANG 29MAR22 TOMMY.XIE 30MAR22

AHDP02-18-08SR-BRA

PART NUMBER

MATERIAL SPECIFICATIONS

QUANTITY

WEIGHT: 54.9a

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY DESIGN FEATURES, SPECIFICATIONS AND BERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHT OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. NEXT ASS'V

Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive

-BLUE

Clinton Township, MI 48036 8 POS, RECEPTACLE, SOCKET PANELMATE AHDP SIZE 18. RD SEAL. BRA

B |**C**-AHDP02-18-08SR-BRA SCALE: NONE DURAMATE SHEET 1 OF 1

TITLE: 8 POS, RECEPTACLE, SOCKET, PANELMATE AHDP SIZE 18, RD SEAL, BRA

AHDP02-18-08SR-BRA

≥ BACKSHELL RING ADAPTER