



41.3



REVISIONS REV ECO DESCRIPTION DATE APPR BY A1 RELEASE NEW DRAWING 28/MAR/22 MILO TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA. WIRE SEAL

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K(MATED CONDITION).


- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-08S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
12	2.46 mm (.097in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



BACKSHELL RING ADAPTER -BLUE

유 AHDP04-18-08PR-BRA REF:HDP24-18-8PE-L017 OLIANTITY

QUANTITY	PART NUMBER			DESCRIPTION				IIEM	
			MAT	ERI	٩LS	3 LI	ST		
UNLESS OTHERWISE SPECIFIED		DRAWN: MLO		DATE			I- I	[
All dimensions are in metric(mm). Tolerances are as follows:				28/MAR/22	Amphenol				
1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08	Fractions ±1/64 Angles ±1°	CHECKED:	SULLEN	29/MAR/22	_	Sin	Sine Systems - www.amphenol-sine.c		
3) Note reference = X		ENGINEER:				44724 Morley Drive Clinton Township, MI 48036		18036	
MATERIAL SPECIFICAT	TIONS:	APPROVAL:	TOMMY	30/MAR/22			Clinton Township, IVII 4	10000	
WEIGHT: 38.7g		CUSTOMER:		8POS, RECEPTACLE, PIN, SIZE 18,					
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL		RD SEAL, BRA, DURAMATE AHDP					
PROCESS SPECIFICATIONS:				B	C-	AHDP04-18-	08PR-BRA	A1	
NEXT ASS'Y:				SCALE:	IONE	DURAMATE	SHEET 1 C	F 1	