

	REVISIONS							
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1	-	RELEASE NEW DRAWING	01/MAR/22	IAN	TOMMY			





MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA. WIRE SEAL;

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.

 - 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED


CONDITION);

IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-24-16P* & AHDP04-24-16P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



42.5±0.5 -

BACKSHELL RING ADAPTER -BLUE

	AHDP06-24-16SR-BRA		REF:HDP26-24-16SE-L017				
QUANTITY	QUANTITY PART NUMBER			DESCRIPTION	ITEN		
			MA	(ERI	ALS LIST	•	
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.10 Angles ±1* 3) Note reference = X		DRAWN: WANXIAO 01/M		S DATE	1 Amphanal		
				01/MAR/22	Ampheno		
		CHECKED:	SULLEN.ZHANG	G 02/MAR/22	44724 Morley Drive		
		ENGINEER:					
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	03/MAR/22	Clinton Township, MI 48036		
		CUSTOMER:			16POS,PLUG,SOCKET,24SZ,		
PROCESS SPECIFICATIONS: SPECIFICATION ONLY, DI SPECIFICATION S AND P SHOWN HEREON ARE T THE AMPHENOL CORPC OF REPRODUCTION AR		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL			RD SEAL,BRA,DURAMATE AHDP		
				FORMANCE DATA PROPERTY OF TION. NO RIGHTS IPLIED. ALL	B C- AHDP06-24-16SR-BRA	A1	
			ONS.	SCALE: NONE DURAMATE SHEET 1 C	F 1		