

REV	ECO	
A1	-	






## NOTES: UNLESS OTHERWISE SPECIFIED

- 1. MATERIAL: HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER
- 2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); STANDARD DIA. WIRE SEAL;

## 3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C. 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC. 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE: IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED
- CONDITION); IP69K(MATED CONDITION).
- 3.5 MATING CYCLE DURABILITY: 100 CYCLES 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-18-20S\* & AHDP04-18-20S\* (\* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND WIRE RANGE:

CONTAC SIZE	T MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
20	1.02 mm (.040in)	2.41 mm (.095 in)	16-22 AWG (1.5-0.5mm <sup>2</sup> )	7.5 AMPS
16	2.54 mm (.100in)	3.40mm (.134 in)	14-20 AWG (2.0-0.5mm <sup>2</sup> )	13 AMPS



41.7±0.60

 $\supset \triangleright$ 

⊳D

[∞

- 5.1

BACKSHELL RING ADAPTER - GREEN

