

4

3

2





1

CUSTOMER DRAWING



REVISION

REV.	DESCRIPTION	DATE
A	INITIAL RELEASE	2020-10-21
B	UPDATE DESIGN	2021-02-20
C	UPDATE DESIGN REMOVE THE U&W KEYWAY	2021-06-15



SEPCIFICATION

CONTACT SIZE	5.7 MM (RADSOK CONTACT) / #20 (HVIL CONTACT)
CONTACT TEST CURRENT	120 Amps Max / 5 Amps
OPERATING VOLTAGE	1000V DC
OPERATING TEMPERATUE	-40°C TO 140 °C
DIELECTRIC WITHATANDING VOLTAGE	3000V AC
NUMBER OF CANTACT	3&2
DURABILITY	100 (MIN)
WATER PROOF	IP67 (MATED)
FINGER PROOF	IPXXB
HVIL&EMI	OPTION
SALT SPRAY	96 H

2. FOR ORDRING INFORMATION, PLEASE SEE CODE NUMBER REFERENCE.
TO COMPLETE IT, ADD APPLICABLE CHARACTERS FOR DESIRED REQUIREMENT.
SEE PAGE 2 FOR DETAIL INFORMATION.

1. THE REFERENCED PRODUCT SHALL BE COMPLIANT TO RoHS DIRECTIVE.

NOTES

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

N/A

Next Assembly

UNLESS OTHERWISE SPECIFIED

LINEAR DIMENSIONS ARE IN MILLIMETERS
TOLERANCES:

DIM. RANGE 0 - 3 >3-6 >6-30 >30-120 >120-400
TOLERANCE ±0.1 ±0.1 ±0.2 ±0.3 ±0.5

ANGLES = ±2°

DIM. & TOL. PER ASME Y14.5M-1994;

DRM PER MIL-DTL-31000;

OTHER AMPHENOL STANDARDS: 9-9318

THIRD ANGLE PROJECTION



APPROVALS

PREPARED BY: THOR YAN

LEAD/PRODUCT ENGINEER: THOR YAN

ENGINEERING MANAGER: ROB WENG

PRODUCT GROUP: C&I

AIPG DIVISION: AIO

MATERIAL SPEC

PROCESS SPEC

N/A

N/A

DATE

2021-02-20

AMPHENOL CORPORATION

Amphenol Technology (Zhuhai) Co. Ltd.
No. 63 Xingnan Road, Sanzao Town, Jinwan, Zhuhai, PRC

5.7mm ePower-life PLUG CONNECTOR 3PORTS

SIZE	CAGE CODE	DOCUMENT NUMBER	REV
C	77820	C()-765779-3()S()	C
SCALE: 1:1		REF: N/A	SHEET 1 OF 2

4

3

2

1

CODE NUMBER REFERENCE: ELPA3() () ()

KEYWAY MARKING
SEE TABLE 1

WIRE SIZE
SEE TABLE 1

HVIL&EMI OPTION
SEE TABLE 1

TABLE 1			
ITEM NO.	DESCRIPTION	CODE NUMBER	DIMENSION L1&L2
KEYWAY MARKING	KEYWAY A	A	L1=13,L2=13
	KEYWAY Y	Y	L1=9,L2=13
	KEYWAY Z	Z	L1=9,L2=9
WIRE SIZE	25 MM^2	25	
	16 MM^2	16	
HVIL & EMI OPTIONAL	YES EMI & YES HVIL	--	
	YES EMI & NO HVIL	01	
	NO EMI & YES HVIL	10	
	NO EMI & NO HVIL	11	

Ⓒ
Ⓒ
Ⓒ

MFG NUMBER REFERENCE: C()-765779-3()S()

HVIL&EMI OPTION
SEE TABLE 2

KEYWAY MARKING
SEE TABLE 2

WIRE SIZE
SEE TABLE 2

TABLE 2			
ITEM NO.	DESCRIPTION	MFG NUMBER	DIMENSION L1&L2
KEYWAY MARKING	KEYWAY A	A	L1=13,L2=13
	KEYWAY Y	Y	L1=9,L2=13
	KEYWAY Z	Z	L1=9,L2=9
WIRE SIZE	25 MM^2	2	
	16 MM^2	1	
HVIL & EMI OPTIONAL	YES EMI & YES HVIL	10	
	YES EMI & NO HVIL	20	
	NO EMI & YES HVIL	30	
	NO EMI & NO HVIL	40	

Ⓒ
Ⓒ
Ⓒ

NOTES:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

SIZE	CAGE CODE	DOCUMENT NUMBER	REV
C	77820	C()-765779-3()S()	C
SCALE: 1:1		REF: N/A	SHEET 2 OF 2