






NOTES

1. RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
2. NUMBER OF CONNECTORS : 8000 PCS/REEL.
3. LEAD TAPE LENGTH.




4. TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3
5. MATERIAL
CARRER TAPE :POLYSTYRENE
TOP TAPE :PET , OTHER
REEL :POLYSTYRENE(PS)(RECYCLE MATERIAL CONTAINED)


MODEL NO. 505066-**22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex				
mm		1:5									
GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0 ° 4 PLACES ± 0.01 3 PLACES ± 0.03 2 PLACES ± 0.05 1 PLACE ± 0.1 0 PLACES ± 0.2							0.35 BB CONN. H=0.6 SSB6 RP REC ASSY				
							PRODUCT CUSTOMER DRAWING				
							DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
							5050660000		PSD	008	D
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A3-SIZE	505066			GENERAL		1 OF 3	



キャリアテープ幅
CARRIER TAPE WIDTH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
mm		2:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL		± 1.0°		0.35 BB CONN. H=0.6 SSB6 RP REC ASSY			
		4 PLACES		± 0.01					
		3 PLACES		± 0.03					
		2 PLACES		± 0.05		PRODUCT CUSTOMER DRAWING			
		1 PLACE		± 0.1					
0 PLACES		± 0.2		DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION
EC NO: 685448 DRWN: YSEKI01 CHK'D: TNISHIDA02 APPR: YNAITO INITIAL REVISION: DRWN: TNISHIDA02 APPR: TKUSUHARA01				2011/11/15		2011/11/16		2011/11/16	
				2017/03/28		2017/03/28		2017/03/28	
				2017/04/03		2017/04/03		2017/04/03	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		505066	
				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						GENERAL		3 OF 3	



11.90	14.70	505066-7022	---	---	70
10.85	13.65	505066-6422	---	---	64
10.15	12.95	505066-6022	---	---	60
9.80	12.60	505066-5822	---	---	58
9.10	11.90	505066-5422	○	---	54
8.40	11.20	505066-5022	○	---	50
8.05	10.85	505066-4822	○	---	48
7.70	10.50	505066-4622	---	---	46
7.00	9.80	505066-4222	○	---	42
6.65	9.45	505066-4022	○	---	40
6.30	9.10	505066-3822	---	---	38
5.60	8.40	505066-3422	○	---	34
5.25	8.05	505066-3222	---	---	32
4.90	7.70	505066-3022	○	---	30
3.85	6.65	505066-2422	○	---	24
3.50	6.30	505066-2222	○	---	22
3.15	5.95	505066-2022	○	---	20
2.80	5.60	505066-1822	---	---	18
2.45	5.25	505066-1622	○	---	16
2.10	4.90	505066-1422	○	---	14
1.75	4.55	505066-1222	○	---	12
1.40	4.20	505066-1022	○	---	10
1.05	3.85	505066-0822	○	---	8
0.70	3.50	505066-0622	○	---	6

B	A	EMBOSSED TAPE PACKAGE	HIGH VOL. TOOL	LOW VOL. TOOL	CIRCUIT
		ORDER NO.	SAMPLE PREPARATION ○ :TOOLED △ :WORK IN PROCESS --- :TOOLING TO BE CONFIRMED		

CONNECTOR SERIES No. : 505066-**09

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: REVISED		molex		
DIMENSION UNITS mm		SCALE 20:1		0.35 BB CONN. H=0.6 SSB6 RP		
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 1.0 °		PRODUCT CUSTOMER DRAWING		
4 PLACES ± 0.001		3 PLACES ± 0.003		DOCUMENT NUMBER 5050661000		
2 PLACES ± 0.03		1 PLACE ± 0.1		DOC TYPE PSD		
0 PLACES ± 0.2		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOC PART 016		
THIRD ANGLE PROJECTION		DRAWING A3-SIZE		REVISION C		
SERIES 505066		MATERIAL NUMBER		SHEET NUMBER 1 OF 2		
CUSTOMER GENERAL		SHEET NUMBER 1 OF 2				

DOCUMENT STATUS	P1	RELEASE DATE	2019/02/27	05:28:33
-----------------	----	--------------	------------	----------

