


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentierung oder Gebrauchsmusteranmeldung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on placard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B



GKT B ATO-E010WN-LS00
Material-ID: 50297051
Mechanical coding: B
Color coding: red





GKT C ATO-E010WN-LS00
Material-ID: 50297054
Mechanical coding: C
Color coding: blue





GKT D ATO-E010WN-LS00
Material-ID: 50297055
Mechanical coding: D
Color coding: green

Panel Cut-out




GKT A ATO-E010WN-LS00
Material-ID: 50297050
Mechanical coding: A
Color coding: light brown




Nut
Nutdriver: 7TE.098.001.000.000 / 50270783
Torque: 6.0 Nm

Delivery condition
2:1



Only insert
View in direction A
6:1



Technical information:

- Current load: 5A (with AWG22) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 750 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

		Benennung/description: Receptacle Style K AMC Series T		Werkstoff: material: seeBOM
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Zeichnungs-Nr.: Drawing-Id.: 00193921		Maßstab: scale: 3:1
Status/state: Approved		Version: revision: -		Format: size: A3
Erstellt/prepared 04.01.2021	fheitzinger	Material-Nr.: Material-Id.: GKT_ATO-E010WN-LS00		Einheit: dim.: mm
Geaendert/revised 04.01.2021	fheitzinger	ODU-Nr.: ODU-Id.: GKT_ATO-E010WN-LS00		Bl.: sheet: 1
Freigabe/released 30.03.2021	chobmaier	Ursprung/origin.: -		
ODU-MUEHLDORF	Datum/date	Name/name		