


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentierung oder Gebrauchsmusteranmeldung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufrunde gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on potcard printed documents are managed. These documents are approved for production.

All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.


CAD: Creo Parametric

Additional coding
View in direction B




GBTBATO-ED08SN-0000

Material-ID: 50298438
Mechanical coding: B
Color coding: red




GBTCTATO-ED08SN-0000

Material-ID: 50298439
Mechanical coding: C
Color coding: blue





GBTDATO-ED08SN-0000

Material-ID: 50298440
Mechanical coding: D
Color coding: green




Only insert
View in direction A
6:1



GBTAAATO-ED08SN-0000

Material-ID: 50298437
Mechanical coding: A
Color coding: light brown



Technical information:

- Current load: 5A (with AWG22) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 750 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016304



1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

3) Accessory thread according to MIL-DTL-38999 Series III, shell size 09

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !



Contact	Material-ID	Wire Size
#22D	50260077	AWG 22-26

		Benennung/description: Receptacle Style 6 AMC Series T		Werkstoff: material: seeBOM
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Zeichnungs-Nr.: Drawing-Id.: 00196089		Maßstab: scale: 3:1
Status/state: Approved		Version: revision: -		Format: size: A3
Erstellt/prepared 09.02.2021 fheitzinger		Material-Nr.: Material-Id.: ODU-Nr.: ODU-Id.: GBT_ATO-ED08SN-0000		Einheit: dim.: mm
Geändert/revised 09.02.2021 fheitzinger		Ursprung/origin.: -		Bl.: sheet: 1
Freigabe/released 12.04.2021 chobmaier				
ODU-MUEHLDORF Datum/date		Name/name		