


COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



3	5	Signal contact	P0 / Brass	0.8µm Au / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
√_F = 0 √_F = 0 √_P = 0		DIMENSION UNITS		SCALE		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m						molex					
		mm		2:1													
						CURRENT REVISION						FCT D-Sub Mixed-Layout Connector					
						DRWN: DRAWN BY msteinbrueck 01-02-2019											
						APPR: APPR BY MTeubel 06-02-2019											
						INITIAL REVISION						PRODUCT CUSTOMER DRAWING					
				2		24130								MATERIAL NUMBER			
		1				DRWN: DRAWN BY Denzinger 30-10-2002						1731070061				2	
		REV.		CH.-NO.		APPR: APPR BY floßmann 30-10-2002											
		REPLACEMENT FOR:		FRIST ANGLE PROJECTION		DRAWING		DOCUMENT NUMBER				CUSTOMER		SHEET NUMBER			
						A3-SIZE		FM9W4P-K120				GENERAL MARKET		1 OF 1			