


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patenterteilung oder Gebrauchsmustererteilung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufrarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on pocard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B



CBTBATO-H005PN-0000
Material-ID: 50298861
Mechanical coding: B
Color coding: red






CBTCTATO-H005PN-0000
Material-ID: 50298862
Mechanical coding: C
Color coding: blue




CBTDATO-H005PN-0000
Material-ID: 50298863
Mechanical coding: D
Color coding: green

Only insert
View in direction A
4:1



CBTAATO-H005PN-0000
Material-ID: 50298860
Mechanical coding: A
Color coding: light brown



Delivery condition
1:1

Technical information:

- Current load: 13A (with AWG16) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 1800 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016304

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.


2) For further contact information and crimping instructions see datasheet D00016300

3) Accessory thread according to MIL-DTL-38999 Series III, shell size 13

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

Pin 2)
6:1



Contact	Material-ID	Wire Size
#16	50267258	AWG 16-20

		Benennung/description: Threaded Plug AMC Series T		Werkstoff: material: see BOM
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Zeichnungs-Nr.: Drawing-Id.: 00197294		Maßstab: scale: 2:1
Status/state: Approved		Version: revision: -		Format: size: A3
Erstellt/prepared	19.02.2021	fheitzinger	ODU-Nr.: ODU-Id.: CBT_ATO-H005PN-0000	
Geaendert/revised	19.02.2021	fheitzinger		
Freigabe/released	22.04.2021	chobmaier	Ursprung/origin.: -	
ODU-MUEHLDOERF	Datum/date	Name/name		
				Einheit: dim.: mm
				Bl.: sheet: 1