


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentierung oder Gebrauchsmusteranmeldung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufrarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on potcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B
5:2



SBTBATO-H005PN-0000
Part-ID: 50298809
Mechanical coding: B
Color coding: red







SBTCATO-H005PN-0000
Part-ID: 50298810
Mechanical coding: C
Color coding: blue




SBTDATO-H005PN-0000
Part-ID: 50298811
Mechanical coding: D
Color coding: green

Only insert
View in direction A
4:1



SBTAATO-H005PN-0000
Part-ID: 50298808
Mechanical coding: A
Color coding: light brown



Contact	Material-ID	Wire Size
#16	50267258	AWG 16-20

Technical information:

- Current load: 13A (with AWG16) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 1800 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016304

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

3) Accessory thread according to MIL-DTL-38999 Series III, shell size 13

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

		Benennung/description: Push-Pull Plug AMC Series T		Werkstoff: material: seeBOM	
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Zeichnungs-Nr.: Drawing-Id.: 00197229		Maßstab: scale: 3:1	
Status/state: Approved		Version: revision: -		Format: size: A3	
Erstellt/prepared 18.02.2021 fheitzinger		Material-Nr.: Material-Id.: SBT_ATO-H005PN-0000		Einheit: dim.: mm	
Geändert/revised 18.02.2021 fheitzinger		ODU-Nr.: ODU-Id.: SBT_ATO-H005PN-0000		Bl.: sheet: 1	
Freigabe/released 22.04.2021 chobmaier		Ursprung/origin.: -			
ODU-MUEHLDORF Datum/date		Name/name			