

CUSTOMER PRINT


PART NUMBER: CA168804PPXXX90

**NOTES:**




1. FINISHED CABLE ASSEMBLY TO BE COILED
2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
3. ELECTRICAL TEST: 100% CONTINUITY
4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHEN NOTED WITH TOLERANCE

ASS'Y P/N	"X" DIM.
CA168804PP03990	3 FT. 3 1/2 IN. ± 2 IN. [1M ±50.8mm]
CA168804PP07990	6 FT. 7 IN. ± 2 IN. [2M ±50.8mm]
CA168804PP19790	16 FT. 5 IN. ± 4 IN. [5M ±101.6mm]
CA168804PP39490	32 FT. 9 3/4 IN. ± 8 IN. [10M ±203.2mm]
CA168804PPXXX90	

CABLE LENGTH IN "INCHES"



O-RING  
MAT'L: SILICONE, RED



**CUSTOMER APPROVAL**

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_

DATE: \_\_\_\_\_

DIMENSIONS IN BRACKETS [ ] ARE METRIC

**RoHS COMPLIANT**

WIRE COLOR CODE, END "A"			
POS. 1	POS. 2	POS. 3	POS. 4
BLK	WHT	BLU	BRN

A	AN	06-01-21	DRAWING CREATED PER DOR 21-109360DS	
REV.	INIT.	DATE	DESCRIPTION	
	AN	06-01-21	ORIG. DRAWN BY: AN	DATE: 06-01-21
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			<p>601 E. WILDWOOD VILLA PARK, IL 60181</p>	
ALL UNITS ARE IN FEET, INCHES, FRACTIONS OF INCHES AND DECIMALS.				
APPROVED BY: _____			TITLE: CABLE ASSEMBLY (4) #22 PIN CONTACTS INSTA-CLICK™ MICRO-CON-X STANDARD PRODUCT	
SCALE	SIZE	SHEET	CUSTOMER: CA168804PPXXX90	
NTS	B	1 OF 1	PART NUMBER: CA168804PPXXX90	
FILE: CA168804PPXXX90			DIRECTORY: SLW	REV A