






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	24 JAN2022	SCB	PS



2385008-3 AS SHOWN



RECOMMENDED PCB LAYOUT

NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : BRASS, TIN PLATED
3. ELECTRICAL
RATED CURRENT AND VOLTAGE : 16AMP 300V(UG B)
: 10AMP 300V(UG D)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 4 TOLERANCE NOT CUMULATIVE

82.88	16	1-2385008-6
77.80	15	1-2385008-5
72.72	14	1-2385008-4
67.64	13	1-2385008-3
62.56	12	1-2385008-2
57.48	11	1-2385008-1
52.40	10	1-2385008-0
47.32	9	2385008-9
42.24	8	2385008-8
37.16	7	2385008-7
32.08	6	2385008-6
27.00	5	2385008-5
21.92	4	2385008-4
16.84	3	2385008-3
11.76	2	2385008-2
DIM A	NO. OF POS.	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24 JAN2022 SHRICHARANA B	TE Connectivity TERMINAL BLOCK, 90 DEG HEADER, PITCH 5.08mm, TAIL LENGTH 4.5mm		
DIMENSIONS: mm		CHK 24 JAN2022 SUBHASREE S			
		APVD 24 JAN2022 PRASHANTH S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32299			
		APPLICATION SPEC 114-32242	NAME		
MATERIAL 1		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2385008
FINISH 1		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV A