


Recommended PCB Layout
Thickness 0.80±0.10mm
Tolerance: ±0.05mm

▨ Solder Area □ Component Outline

Pin	Signal	Mating Sequence
A5	CC1	Second
A9	Vbus	First
A12	GND	First
B5	CC2	Second
B9	Vbus	First
B12	GND	First
SHELL	GND	



Specifications

Material

Insulator: High Temp. Plastic, UL 94V-0, Black
Contact: Copper Alloy
Shell: Stainless Steel
Shielding Plate: Stainless Steel
Gasket: Silicon

Plating

Contact
Contact Area: Gold Flash
Solder Tails: Tin over Nickel
Shell: Nickel
Shielding Plate: Nickel

Electrical

Current Rating: 3.00A collectively for Vbus pins
4.25A collectively for GND pins
1.25A for A5/B5 pin

Voltage Rating: 20V DC

Contact Resistance: 40mΩ max initial.

50mΩ max after test

Dielectric Withstanding Voltage: 100V AC

Insulation Resistance 100MΩ min

Mechanical & Environmental





Operating Temperature: -30°C to +85°C

Mating Force: 5 to 20 N.


Unmated Force: 6 to 20 N after test

Durability: 10,000 cycles


Ingress Protection Rating: IP67




Ordering Grid




Part Number		Product Description			This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	www.gct.co
USB4715		Type C Receptacle, Horizontal, Mid-Mount, SMT, IP67, For Power Charging Only, 6 Pin				
Drawing Date		4th July 2022				
By	CC	Tolerances (Except as Noted)	Units:			
Detail	Drawing Release	X.X ± 0.30	Metric (mm)			
Revision	A	X.XX ± 0.25				
Date	04/07/22	X.XXX ± 0.10				
Not to Scale		Drawn By	CC	Sheet No.	1/4	




Recommended Panel Spec



(Suggest compression 30-40% of gasket thickness)



Recommended Waterproof Gasket
 Gasket Part No.: USBTJ-04
 (Gasket must be ordered separately)
 (See separate datasheet for specification)



Plug and Receptacle Mating View


Part Number		Product Description	
USB4715		Type C Receptacle, Horizontal, Mid-Mount, SMT, IP67, For Power Charging Only, 6 Pin	
Drawing Date		4th July 2022	
By	CC	Tolerances (Except as Noted)	Units:
Detail	Drawing Release	Length X.X ± 0.30	Metric (mm)
Revision	A	Angle X.XX ± 0.25	
Date	04/07/22	X.XXX ± 0.10	




This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE




Not to Scale	Drawn By CC	Sheet No. 2/4
--------------	----------------	------------------



Step 1



Step 2




Step 3



Assembly instruction for Gasket set after Reflow
 Available for Type C Receptacle Waterproof Series

Part Number		Product Description	
USB4715		Type C Receptacle, Horizontal, Mid-Mount, SMT, IP67, For Power Charging Only, 6 Pin	
Drawing Date		4th July 2022	
By	CC	Tolerances (Except as Noted)	Units:
Detail	Drawing Release	Length X.X ± 0.30	Metric (mm)
Revision	A	Angle X.XX ± 0.25	 3rd Angle Projection
Date	04/07/22	X.XXX ± 0.10	
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	
Not to Scale	Drawn By	CC	Sheet No.
			3/4








Direction of Unreeling →



Direction of Unreeling →



Pcs / Reel	Reels / Carton	Total Quantity
700	10	7,000 pcs

Part Number USB4715		Product Description Type C Receptacle, Horizontal, Mid-Mount, SMT, IP67, For Power Charging Only, 6 Pin	
Drawing Date 4th July 2022			
By CC	Drawing Release	Tolerances (Except as Noted) Length Angle	Units: Metric (mm)
Revision A	Date 04/07/22	-	-
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	



Not to Scale	Drawn By CC	Sheet No. 4/4
--------------	----------------	------------------