

Metal Switch, Switching Voltage up to 250 VAC



Ring illumination
blue



Area illumination
blue



Point Illumination
red

See below:

Approvals and Compliances

Description

- Mechanical switch with stroke in different versions LA (Latching) and MO (Momentary)
- Single-/ or multicolor illumination
- With torsion protection for easier handling
- Equipped with flat plug in terminals to permit fast connection

Unique Selling Proposition

- Attractive tactile feedback
- High quality materials
- Long life span
- Color marking

Characteristics

- Housing material in high-quality stainless steel or aluminium
- Variety of design options regarding size, colour, illumination, connection or lettering
- Switching voltage from 30 VDC to 250 VAC
- Switching current from 0.1 A to 16 A
- Actuator: aluminium/ stainless steel/ ceramics
- For use in harsh environments

References

Further versions on request (MOQ 500 St.)

Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [CAD-Drawings](#), [Product News](#), [Detailed request for product](#)

Technical Data

Electrical Data

Supply Voltage LED	see table of variants
Micro Switch	see table of variants
Impulse Withstand Voltage (ESD)	2 kV

Mechanical Data

Actuating Force (MO/LA)	4.5 N / 10 N
Actuating Travel (MO/LA)	1.0 mm / 5.2 mm
Lifetime	1.5 million actuations
Shock Protection	IK07 to IK10
Mounting screw torque Plastic Nut	max. 3.5 Nm

Climatical Data

Operating Temperature	-25 to 85 °C
Storage Temperature	-25 to 85 °C
Salt Spray Test (acc. to DIN 50021-SS)	24 h / 48 h / 96 h Residence Time

Material

Housing	Aluminium / Stainless Steel
Actuator	Aluminium / Stainless Steel / Ceramics
Seal Ring	NBR70
Plastic Nut	PA, UL94

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.


Compliances

The product complies with following Guide Lines


Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UKCA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]


MSM 19 LA PI double-pole




MSM 19 LA RI double-pole




MSM 19 LA AI double-pole




MSM 22 LA PI double-pole



MSM 22 LA RI double-pole




MSM 22 LA Al double-pole




Legend to MSM Latching

B	Actuating Area
C	Sealing
D	Nut
E	Anti-rotation protection
L	Illuminated Area


MSM MO AI double-pole




MSM MO RI single-pole




MSM MO RI double-pole



MSM MO PI single-pole



MSM MO PI double-pole




Legend to MSM Momentary

Diameter in mm	16	19	22	30
A	20	24	26	24.5
B	19	22	25	34
C	M16x1	M19x0.75	M22x1	M30x1.5
D	1.74	1.75	1.74	2.04
E	10	10.5	10	11
F Operating area / illumination area	12.8	15.8	18	25
G	AF19	AF22	AF24	AF32
H	-	5.9	5.9	7.9
I	O-Ring			
J	Nut			
K	Anti-rotation lock			
L	Lighting ring			
M	Point illumination			

Tolerance Range


Actuator Tolerance Range




The mounting tolerance range of the actuator varies from 0.2 mm projection length and 0.2 mm short length to the housing edge. The slanting position of the actuator can range within this tolerance.

Dimension

With torsion protection




Without torsion protection




Diameter in mm	A	B
16	15.15+0.05	16.1 +0.1
19	18.15+0.05	19.1 +0.1
22	21.15+0.05	22.1 +0.1
30	28.85+0.05	30.1 +0.1

Assembly Instructions



During assembly, the protruding bars of the holder should not be pressed together.



- I Housing
- II Flat Pin Terminal (Illumination)
- III O-Ring gasket
- IV Nut (Nut type see Dimensions)
- V Module Switching Contact

Installation Instruction:


1. Place the gasket accurately on the actuator housing. Then mount the actuator housing assembly into the panel.
2. Tighten the screw nut according to the torque instructions.
3. Clasp the module switching contact into the micro switch holder of the actuator housing.

Installation information:


- The power supply and the configuration of the flat pin terminals have to be installed correctly for the illumination and micro switch function.
- Insulate the terminals as required. Fully insulated plug-in sleeves are recommended.
- Installation instructions according to VDE-standard DIN VDE 0100-100 or alternatively IEC 60354 standard.
- During assembly, the protruding bars of the holder should not be pressed together.

Diagrams


Point illumination double-pole




Area illumination single-pole



Point Illumination single-pole



Ring illumination double-pole




Illumination options for RGB

Lighting type	Wire red	Wire green	Wire blue	Resulting Color
Multicolor Singlecolor	x			Red
Multicolor Singlecolor		x		Green
Multicolor Singlecolor			x	Blue
Multicolor RGB Additive 2	x	x		Yellow
Multicolor RGB Additive 2	x		x	Magenta
Multicolor RGB Additive 2		x	x	Cyan
Multicolor RGB Additive 3	x	x	x	White

MSM RI / 24 V RGB

terminal assignment with resistors for 24 VDC



Point Illumination

Operating Data	Forward Current max.	Forward Voltage at 10 mA	Forward Voltage max.
LED red	30 mA	1.9 VDC	3.0 VDC
LED green	30 mA	2.4 VDC	3.0 VDC
LED yellow	30 mA	2.4 VDC	3.0 VDC
LED blue	20 mA	3.8 VDC	4.5 VDC
LED red/green	25 mA	2.0 VDC	2.5 VDC

Attention: Switches with point illumination (PI) are delivered without series resistor.

Micro Switch

Micro Switch	Contact Material	Switching Voltage	Switching current	Rated Switching Capacity	Lifetime	Contact Resistance	Insulation Resistance	Duration of Bounce
0.1 A, IP40	Au	max. 30 VDC	max. 0.1 A	3 W	0.2 Mio.	< 50 mΩ	> 100 MΩ	< 5 ms
0.1 A, IP67		max. 250 VDC	max. 0.1 A	25 W	0.05 Mio.			
5 A / 125 VAC bzw. 3 A / 250 VAC, IP40	Ag	max. 125 / 250 VAC	max. 5 / 3 A	750 W	0.2 Mio.	< 30 mΩ	> 100 MΩ	< 5 ms
6 A, IP67		max. 250 VDC	max. 5 A	1250 W	0.01 Mio.			
10 A, IP40	Ag	max. 250 VAC	max. 10 A	2500 W	0.05 Mio.	< 30 mΩ	> 100 MΩ	< 5 ms
10 A, IP67		max. 250 VAC	max. 10 A	2500 W	0.01 Mio.			
12 A, IP40	Ag	max. 250 VAC	max. 12 A	3000 W	0.05 Mio.	< 100 mΩ		
16 A, IP40	Ag	max. 250 VAC	max. 16 A	4000 W	0.04 Mio.	< 100 mΩ	> 100 MΩ	

Marking

The last three digits in the order number define the lettering:

000	No Lettering
001-074	Standard Lettering
101-	Customized Lettering

Order Index Lettering

Laser Marking

001 = A	021 = U	041 = ÷	061 = EIN
002 = B	022 = V	042 = *	062 = AUS
003 = C	023 = W	043 = =	063 = AUF
004 = D	024 = X	044 = #	064 = AB
005 = E	025 = Y	045 = ↔	065 = ON
006 = F	026 = Z	046 = †	066 = OFF
007 = G	027 = 0	047 = →	067 = UP
008 = H	028 = 1	048 = ←	068 = DOWN
009 = I	029 = 2	049 = ↓	069 = HIGH
010 = J	030 = 3	050 = ↑	070 = LOW
011 = K	031 = 4	051 = %	071 = ON/OFF
012 = L	032 = 5	052 = √	072 = START
013 = M	033 = 6	053 = CTRL	073 = RESET
014 = N	034 = 7	054 = RETURN	074 = 
015 = O	035 = 8	055 = SHIFT	075 = 
016 = P	036 = 9	056 = LOCK	076 = 
017 = Q	037 = +	057 = STOP	077 = 
018 = R	038 = -	058 = ENTER	
019 = S	039 = .	059 = BACK	
020 = T	040 = x	060 = LINE	

Please note that the font size depends on the number of characters

Order number key

M	S	M	-	19	-	MO	NX	A10	-	B	-	A	A0	-	A	-	PI	0GN	00R	0	A0	-	S0	NC	B	-	S0	NC	NF	-	0	000	-	C
				1		2	3	4		5		6	7		8		9	10	11	12	13		14	15	16		17	18	19		20	21		22

Diameter **1**

16 mm	=	16
19 mm	=	19
22 mm	=	22
30 mm	=	30

Switch type **2**

Latching	=	LA
Momentary	=	MO

Switch function **3**

Change over contact	=	NX
Normally open	=	NO

Switching current **4**

100mA	=	A10
5A	=	05A
6A	=	06A
10A	=	10A
12A	=	12A
16A	=	16A

Contact configuration **5**

SPST	=	A
SPDT	=	B
DPST	=	C
DPDT	=	D

Contact material **6**

Gold	=	A
Silver	=	B

Terminal switch **7**

QC 2.8 x 0.5	=	A0
QC 6.3 x 0.5	=	A1
QC 4.8 x 0.8	=	A4
Cable - 200 mm	=	B0
Cable - 500 mm	=	B1
Wire harness	=	F1

Switch IP specification **8**

None	=	0
IP40	=	A
IP67	=	B

Illumination type **9**

Area illumination	=	AI
Ring illumination	=	RI
Point illumination	=	PI
Ring illumination	=	RD

(Dead Front)

Illumination color **10**

Red	=	0RD
Green	=	0GN
Blue	=	0BL
Yellow	=	0YL
White	=	0WT
Orange	=	0OR
Violet	=	0VT
Multicolor	=	RGB
Red-Green	=	0RG
Green-Yellow	=	0GY

Supply voltage illumination **11**

5 V	=	005
12 V	=	012
24 V	=	024
W/O (without) resistors	=	00R

Illumination sub type **12**

Standard	=	0
Bright	=	1
Scaled	=	2
Homogen-scaled	=	4
Homogen	=	3
Bright-homogen	=	5
Bright-homogen-scaled	=	7

Terminal illumination **13**

None	=	00
Switch integrated	=	C0

Housing material **14**

Stainless steel	=	S0
Aluminum	=	A0

Switches | **SCHURTER** | 13 |
ELECTRONIC COMPONENTS

All Variants

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number	
16	MO	10 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-102-620	
16	MO	100 mA	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-102-621	
16	MO	10 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-102-623	
16	MO	100 mA	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-102-624	
16	MO	10 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-102-626	
16	MO	100 mA	SPDT	IP40	RI homogeneous	yellow	Stainless Steel	3-102-627	
16	MO	10 A	SPDT	IP40	RI homogeneous	yellow	Stainless Steel	3-102-629	
16	MO	100 mA	SPDT	IP40	RI homogeneous	white	Stainless Steel	3-102-630	
16	MO	10 A	SPDT	IP40	RI homogeneous	white	Stainless Steel	3-102-632	
16	MO	100 A	SPDT	IP40	Area illumination	red	Stainless Steel	3-102-633	
16	MO	5 A	SPDT	IP40	Area illumination	red	Stainless Steel	3-102-634	
16	MO	10 A	SPDT	IP40	Area illumination	red	Stainless Steel	3-102-635	
16	MO	100 A	SPDT	IP40	Area illumination	green	Stainless Steel	3-102-636	
16	MO	5 A	SPDT	IP40	Area illumination	green	Stainless Steel	3-102-637	
16	MO	10 A	SPDT	IP40	Area illumination	green	Stainless Steel	3-102-639	
16	MO	100 A	SPDT	IP40	Area illumination	blue	Stainless Steel	3-102-640	
16	MO	5 A	SPDT	IP40	Area illumination	blue	Stainless Steel	3-102-641	
16	MO	10 A	SPDT	IP40	Area illumination	blue	Stainless Steel	3-102-642	
16	MO	100 A	SPDT	IP40	Area illumination	yellow	Stainless Steel	3-102-643	
16	MO	5 A	SPDT	IP40	Area illumination	yellow	Stainless Steel	3-102-644	
16	MO	10 A	SPDT	IP40	Area illumination	yellow	Stainless Steel	3-102-645	
16	MO	100 A	SPDT	IP40	Area illumination	white	Stainless Steel	3-102-646	
16	MO	5 A	SPDT	IP40	Area illumination	white	Stainless Steel	3-102-647	
16	MO	10 A	SPDT	IP40	Area illumination	white	Stainless Steel	3-102-648	
16	MO	5 A	SPDT	IP40	Ring Illumination	white	Aluminum	3-137-051	
19	LA	12 A	SPST	IP40	Point Illumination	red	Stainless Steel	1241.6823.1111000	
19	LA	12 A	SPST	IP40	Area illumination	red	Stainless Steel	1241.8544	
19	LA	12 A	SPST	IP40	Point Illumination	green	Stainless Steel	1241.6823.1112000	
19	LA	12 A	SPST	IP40	Point Illumination	blue	Stainless Steel	1241.6823.1114000	
19	LA	12 A	SPST	IP40	Area illumination	green	Stainless Steel	1241.8545	
19	LA	12 A	SPST	IP40	RI dotted	red	Stainless Steel	1241.6824.1111000	
19	LA	12 A	SPST	IP40	RI dotted	green	Stainless Steel	1241.6824.1112000	
19	LA	12 A	SPST	IP40	Area illumination	blue	Stainless Steel	1241.8547	
19	LA	12 A	SPST	IP40	RI dotted	blue	Stainless Steel	1241.6824.1114000	
19	LA	12 A	SPST	IP40	RI dotted	white	Stainless Steel	1241.6824.1115000	
19	LA	12 A	SPST	IP40	Area illumination	white	Stainless Steel	1241.8548	
19	LA	12 A	DPST	IP40	Point Illumination	red	Stainless Steel	1241.6823.1121000	
19	LA	12 A	DPST	IP40	Point Illumination	green	Stainless Steel	1241.6823.1122000	
19	LA	12 A	DPST	IP40	Point Illumination	blue	Stainless Steel	1241.6823.1124000	
19	LA	12 A	DPST	IP40	RI dotted	red	Stainless Steel	1241.6824.1121000	
19	LA	12 A	DPST	IP40	RI dotted	green	Stainless Steel	1241.6824.1122000	
19	LA	12 A	DPST	IP40	RI dotted	blue	Stainless Steel	1241.6824.1124000	
19	LA	12 A	DPST	IP40	Area illumination	red	Stainless Steel	1241.8550	
19	LA	12 A	DPST	IP40	Area illumination	green	Stainless Steel	1241.8551	
19	LA	12 A	DPST	IP40	Area illumination	blue	Stainless Steel	1241.8553	
19	LA	12 A	DPST	IP40	Area illumination	white	Stainless Steel	1241.8554	
19	MO	100 mA	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6623.1111000	
19	MO	100 mA	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6623.1112000	
19	MO	5 A	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6623.1121000	
19	MO	5 A	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6623.1122000	
19	MO	5 A	SPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6623.1124000	

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number
19	M0	10 A	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6623.1131000
19	M0	10 A	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6623.1132000
19	M0	100 mA	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6624.1111000
19	M0	100 mA	SPDT	IP40	RI dotted	red	Stainless Steel	
19	M0	100 mA	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6624.1112000
19	M0	100 mA	SPDT	IP40	RI dotted	yellow	Stainless Steel	1241.6624.1113000
19	M0	100 mA	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6624.1114000
19	M0	100 mA	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6624.1114074
19	M0	5 A	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6624.1121000
19	M0	5 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6624.1122000
19	M0	5 A	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6624.1124000
19	M0	5 A	SPDT	IP40	RI dotted	white	Stainless Steel	1241.6624.1125000
19	M0	10 A	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6624.1131000
19	M0	10 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6624.1132000
19	M0	10 A	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6624.1134000
19	M0	6 A	SPDT	IP67	RI dotted	red	Stainless Steel	1241.6624.1181000
19	M0	6 A	SPDT	IP67	RI dotted	green	Stainless Steel	1241.6624.1182000
19	M0	5 A	DPDT	IP40	Point Illumination	red	Stainless Steel	1241.6923.1121000
19	M0	5 A	DPDT	IP40	Point Illumination	green	Stainless Steel	1241.6923.1122000
19	M0	5 A	DPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6923.1124000
19	M0	5 A	DPDT	IP40	RI dotted	red	Stainless Steel	1241.6924.1121000
19	M0	5 A	DPDT	IP40	RI dotted	green	Stainless Steel	1241.6924.1122000
19	M0	5 A	DPDT	IP40	RI dotted	blue	Stainless Steel	1241.6924.1124000
19	M0	100 A	SPDT	IP40	Area illumination	red	Stainless Steel	1241.8412
19	M0	100 A	SPDT	IP40	Area illumination	green	Stainless Steel	1241.8413
19	M0	100 A	SPDT	IP40	Area illumination	blue	Stainless Steel	1241.8415
19	M0	100 A	SPDT	IP40	Area illumination	white	Stainless Steel	1241.8416
19	M0	10 A	SPDT	IP40	Area illumination	red	Stainless Steel	1241.8448
19	M0	10 A	SPDT	IP40	Area illumination	green	Stainless Steel	1241.8449
19	M0	10 A	SPDT	IP40	Area illumination	blue	Stainless Steel	1241.8451
19	M0	10 A	SPDT	IP40	Area illumination	white	Stainless Steel	1241.8452
19	LA	12 A	SPST	IP40	Area illumination	yellow	Stainless Steel	1241.8546
19	LA	12 A	SPST	IP40	Area illumination	orange	Stainless Steel	1241.8549
19	LA	12 A	DPST	IP40	Area illumination	yellow	Stainless Steel	1241.8552
19	LA	12 A	DPST	IP40	Area illumination	orange	Stainless Steel	1241.8555
19	LA	16 A	SPST	IP40	RI dotted	red	Stainless Steel	3-100-990
19	LA	16 A	SPST	IP40	RI dotted	green	Stainless Steel	3-100-991
19	LA	16 A	DPST	IP40	RI dotted	blue	Stainless Steel	3-100-999
19	LA	16 A	SPST	IP40	RI dotted	blue	Stainless Steel	3-101-002
19	LA	16 A	DPST	IP40	RI dotted	red	Stainless Steel	3-101-003
19	LA	16 A	DPST	IP40	RI dotted	green	Stainless Steel	3-101-004
19	LA	16 A	SPST	IP40	Area illumination	red	Stainless Steel	3-101-005
19	LA	16 A	SPST	IP40	Area illumination	green	Stainless Steel	3-101-007
19	LA	16 A	SPST	IP40	Area illumination	blue	Stainless Steel	3-101-009
19	LA	16 A	DPST	IP40	Area illumination	blue	Stainless Steel	3-101-010
19	LA	16 A	DPST	IP40	Area illumination	white	Stainless Steel	3-101-011
19	LA	16 A	SPST	IP40	Area illumination	white	Stainless Steel	3-101-022
19	LA	16 A	DPST	IP40	Area illumination	red	Stainless Steel	3-101-023
19	LA	16 A	DPST	IP40	Area illumination	green	Stainless Steel	3-101-024
19	M0	5 A	SPDT	IP40	Point Illumination	green / yellow	Stainless Steel	3-101-515
19	M0	100 mA	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-708

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number	
19	MO	10 A	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-772	
19	MO	100 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-788	
19	MO	5 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-789	
19	MO	10 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-790	
19	MO	100 mA	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-945	
19	MO	5 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-946	
19	MO	10 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-947	
19	MO	100 mA	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-948	
19	MO	5 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-949	
19	MO	10 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-950	
19	MO	5 A	DPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-951	
19	MO	100 mA	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-952	
19	MO	5 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-953	
19	MO	10 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-954	
19	MO	5 A	DPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-962	
19	MO	5 A	DPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-963	
19	MO	5 A	SPDT	IP40	Area illumination	green	Stainless Steel	3-120-088	
19	MO	5 A	SPDT	IP40	Area illumination	blue	Stainless Steel	3-120-089	
19	MO	5 A	SPDT	IP40	Area illumination	red	Stainless Steel	3-120-103	
19	MO	6 A	SPDT	IP67	Area illumination	red	Stainless Steel	3-120-115	
19	MO	5 A	SPDT	IP40	Ring Illumination	white	Aluminum	Kopie von 3-102-618	
19	MO	5 A	SPDT	IP40	Ring Illumination	RGB	Aluminum	3-137-085	
22	MO	100 A	SPDT	IP40	Area illumination	red	Stainless Steel	1241.8484	
22	MO	100 A	SPDT	IP40	Area illumination	green	Stainless Steel	1241.8485	
22	MO	100 A	SPDT	IP40	Area illumination	blue	Stainless Steel	1241.8487	
22	MO	100 A	SPDT	IP40	Area illumination	white	Stainless Steel	1241.8488	
22	MO	10 A	SPDT	IP40	Area illumination	red	Stainless Steel	1241.8520	
22	MO	10 A	SPDT	IP40	Area illumination	green	Stainless Steel	1241.8521	
22	MO	10 A	SPDT	IP40	Area illumination	blue	Stainless Steel	1241.8523	
22	MO	10 A	SPDT	IP40	Area illumination	white	Stainless Steel	1241.8524	
22	LA	12 A	SPST	IP40	Point Illumination	red	Stainless Steel	1241.6833.1111000	
22	LA	12 A	SPST	IP40	Point Illumination	green	Stainless Steel	1241.6833.1112000	
22	LA	12 A	SPST	IP40	Point Illumination	blue	Stainless Steel	1241.6833.1114000	
22	LA	12 A	SPST	IP40	RI dotted	red	Stainless Steel	1241.6834.1111000	
22	LA	12 A	SPST	IP40	RI dotted	green	Stainless Steel	1241.6834.1112000	
22	LA	12 A	SPST	IP40	RI dotted	blue	Stainless Steel	1241.6834.1114000	
22	LA	12 A	DPST	IP40	Point Illumination	red	Stainless Steel	1241.6833.1121000	
22	LA	12 A	DPST	IP40	Point Illumination	green	Stainless Steel	1241.6833.1122000	
22	LA	12 A	DPST	IP40	Point Illumination	blue	Stainless Steel	1241.6833.1124000	
22	LA	12 A	DPST	IP40	RI dotted	red	Stainless Steel	1241.6834.1121000	
22	LA	12 A	DPST	IP40	RI dotted	green	Stainless Steel	1241.6834.1122000	
22	LA	12 A	DPST	IP40	RI dotted	blue	Stainless Steel	1241.6834.1124000	
22	LA	12 A	SPST	IP40	Area illumination	red	Stainless Steel	1241.8556	
22	LA	12 A	SPST	IP40	Area illumination	green	Stainless Steel	1241.8557	
22	LA	12 A	SPST	IP40	Area illumination	blue	Stainless Steel	1241.8559	
22	LA	12 A	SPST	IP40	Area illumination	white	Stainless Steel	1241.8560	
22	LA	12 A	DPST	IP40	Area illumination	red	Stainless Steel	1241.8562	
22	LA	12 A	DPST	IP40	Area illumination	green	Stainless Steel	1241.8563	
22	LA	12 A	DPST	IP40	Area illumination	blue	Stainless Steel	1241.8565	
22	LA	12 A	DPST	IP40	Area illumination	white	Stainless Steel	1241.8566	
22	MO	100 mA	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6633.1111000	

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number
22	M0	100 mA	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6633.1112000
22	M0	100 mA	SPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6633.1114000
22	M0	5 A	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6633.1121000
22	M0	5 A	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6633.1122000
22	M0	5 A	SPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6633.1124000
22	M0	5 A	SPDT	IP40	Point Illumination	red / green	Stainless Steel	1241.6633.1126000
22	M0	10 A	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6633.1131000
22	M0	10 A	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6633.1132000
22	M0	10 A	SPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6633.1134000
22	M0	100 mA	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6634.1111000
22	M0	100 mA	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6634.1112000
22	M0	100 mA	SPDT	IP40	RI dotted	yellow	Stainless Steel	1241.6634.1113000
22	M0	100 mA	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6634.1114000
22	M0	5 A	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6634.1121000
22	M0	5 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6634.1122000
22	M0	5 A	SPDT	IP40	RI dotted	yellow	Stainless Steel	1241.6634.1123000
22	M0	5 A	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6634.1124000
22	M0	5 A	SPDT	IP40	RI dotted	white	Stainless Steel	1241.6634.1125000
22	M0	10 A	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6634.1131000
22	M0	10 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6634.1132000
22	M0	6 A	SPDT	IP67	RI dotted	red	Stainless Steel	1241.6634.1181000
22	M0	6 A	SPDT	IP67	RI dotted	green	Stainless Steel	1241.6634.1182000
22	M0	6 A	SPDT	IP67	RI dotted	blue	Stainless Steel	1241.6634.1184000
22	M0	5 A	SPDT	IP40	Point Illumination	red	Stainless Steel	1241.6693.1121000
22	M0	5 A	SPDT	IP40	Point Illumination	green	Stainless Steel	1241.6693.1122000
22	M0	5 A	DPDT	IP40	Point Illumination	red	Stainless Steel	1241.6933.1121000
22	M0	5 A	DPDT	IP40	Point Illumination	green	Stainless Steel	1241.6933.1122000
22	M0	5 A	DPDT	IP40	Point Illumination	blue	Stainless Steel	1241.6933.1124000
22	M0	5 A	DPDT	IP40	RI dotted	red	Stainless Steel	1241.6934.1121000
22	M0	5 A	DPDT	IP40	RI dotted	green	Stainless Steel	1241.6934.1122000
22	M0	5 A	DPDT	IP40	RI dotted	blue	Stainless Steel	1241.6934.1124000
22	LA	16 A	DPST	IP40	RI dotted	green	Stainless Steel	3-100-912
22	LA	16 A	SPST	IP40	RI dotted	red	Stainless Steel	3-101-013
22	LA	16 A	SPST	IP40	RI dotted	green	Stainless Steel	3-101-014
22	LA	16 A	SPST	IP40	RI dotted	blue	Stainless Steel	3-101-015
22	LA	16 A	DPST	IP40	RI dotted	red	Stainless Steel	3-101-016
22	LA	16 A	DPST	IP40	RI dotted	blue	Stainless Steel	3-101-018
22	LA	16 A	SPST	IP40	Area illumination	blue	Stainless Steel	3-101-029
22	LA	16 A	SPST	IP40	Area illumination	white	Stainless Steel	3-101-030
22	LA	16 A	DPST	IP40	Area illumination	red	Stainless Steel	3-101-031
22	LA	16 A	SPST	IP40	Area illumination	red	Stainless Steel	3-101-032
22	LA	16 A	SPST	IP40	Area illumination	green	Stainless Steel	3-101-033
22	LA	16 A	DPST	IP40	Area illumination	green	Stainless Steel	3-101-039
22	LA	16 A	DPST	IP40	Area illumination	blue	Stainless Steel	3-101-040
22	LA	16 A	DPST	IP40	Area illumination	white	Stainless Steel	3-101-041
22	M0	100 mA	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-773
22	M0	100 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-774
22	M0	5 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-775
22	M0	10 A	SPDT	IP40	Area illumination	RGB	Stainless Steel	3-102-776
22	M0	10 A	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-784
22	M0	100 mA	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-955

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number	
22	MO	5 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-956	
22	MO	10 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-957	
22	MO	100 mA	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-958	
22	MO	5 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-959	
22	MO	10 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-960	
22	MO	100 mA	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-961	
22	MO	5 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-972	
22	MO	10 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-973	
22	MO	5 A	DPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-974	
22	MO	5 A	DPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-975	
22	MO	5 A	DPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-976	
22	MO	100 mA	SPDT	IP67	RI homogeneous	RGB	Stainless Steel	3-109-580	
22	MO	5 A	SPDT	IP40	Area illumination	blue	Stainless Steel	3-120-106	
22	MO	5 A	SPDT	IP40	Area illumination	white	Stainless Steel	3-120-107	
22	MO	5 A	SPDT	IP40	Area illumination	red	Stainless Steel	3-120-119	
22	MO	5 A	SPDT	IP40	Area illumination	green	Stainless Steel	3-120-124	
22	MO	5 A	SPDT	IP40	Ring illumination	red	Aluminum	3-137-083	
22	MO	5 A	SPDT	IP40	Ring illumination	RGB	Aluminum	3-137-086	
22	MO	5 A	SPDT	IP40	Ring illumination	green	Aluminum	3-137-088	
22	MO	5 A	SPDT	IP40	Ring illumination	blue	Aluminum	3-137-089	
22	MO	5 A	SPDT	IP40	Ring illumination	yellow	Aluminum	3-137-090	
22	MO	100 mA	SPDT	IP40	Ring illumination	white	Aluminum	3-137-091	
22	MO	5 A	SPDT	IP40	Ring illumination	white	Aluminum	3-137-092	
22	MO	10 mA	SPDT	IP40	Ring illumination	white	Aluminum	3-137-093	
22	MO	100 mA	SPDT	IP40	Ring illumination	RGB	Aluminum	3-137-094	
22	MO	10 A	SPDT	IP40	Ring illumination	RGB	Aluminum	3-137-095	
30	MO	100 mA	SPDT	IP40	Point illumination	red	Stainless Steel	1241.6663.1111000	
30	MO	100 mA	SPDT	IP40	Point illumination	blue	Stainless Steel	1241.6663.1114000	
30	MO	5 A	SPDT	IP40	Point illumination	red	Stainless Steel	1241.6663.1121000	
30	MO	5 A	SPDT	IP40	Point illumination	green	Stainless Steel	1241.6663.1122000	
30	MO	5 A	SPDT	IP40	Point illumination	blue	Stainless Steel	1241.6663.1124000	
30	MO	5 A	SPDT	IP40	Point illumination	white	Stainless Steel	1241.6663.1125000	
30	MO	10 A	SPDT	IP40	Point illumination	green	Stainless Steel	1241.6663.1132000	
30	MO	5 A	SPDT	IP40	Point illumination	red	Aluminum	1241.6663.3121	
30	MO	100 mA	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6664.1111000	
30	MO	100 mA	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6664.1112000	
30	MO	100 mA	SPDT	IP40	RI dotted	yellow	Stainless Steel	1241.6664.1113000	
30	MO	100 mA	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6664.1114000	
30	MO	5 A	SPDT	IP40	RI dotted	red	Stainless Steel	1241.6664.1121000	
30	MO	5 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6664.1122000	
30	MO	5 A	SPDT	IP40	RI dotted	yellow	Stainless Steel	1241.6664.1123000	
30	MO	5 A	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6664.1124000	
30	MO	5 A	SPDT	IP40	RI dotted	white	Stainless Steel	1241.6664.1125000	
30	MO	10 A	SPDT	IP40	RI dotted	green	Stainless Steel	1241.6664.1132000	
30	MO	10 A	SPDT	IP40	RI dotted	blue	Stainless Steel	1241.6664.1134000	
30	MO	5 A	DPDT	IP40	Point illumination	red	Stainless Steel	1241.6963.1121000	
30	MO	5 A	DPDT	IP40	Point illumination	green	Stainless Steel	1241.6963.1122000	
30	MO	5 A	DPDT	IP40	Ring illumination	red	Stainless Steel	1241.6964.1121000	
30	MO	5 A	DPDT	IP40	Ring illumination	green	Stainless Steel	1241.6964.1122000	
30	MO	5 A	DPDT	IP40	Ring illumination	blue	Stainless Steel	1241.6964.1124000	

Diameter	Switch type	Switching current [A]	Electrical contact	IP specification backside	Illumination	Illumination color	Housing material	Order Number
30	M0	100 mA	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-785
30	M0	10 A	SPDT	IP40	RI homogeneous	RGB	Stainless Steel	3-102-787
30	M0	100 mA	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-964
30	M0	5 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-965
30	M0	10 A	SPDT	IP40	RI homogeneous	red	Stainless Steel	3-108-966
30	M0	100 mA	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-967
30	M0	5 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-968
30	M0	10 A	SPDT	IP40	RI homogeneous	green	Stainless Steel	3-108-969
30	M0	100 mA	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-977
30	M0	5 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-978
30	M0	10 A	SPDT	IP40	RI homogeneous	blue	Stainless Steel	3-108-979
30	M0	5 A	SPDT	IP40	Ring Illumination	white	Aluminum	3-137-084
30	M0	5 A	SPDT	IP40	Ring Illumination	RGB	Aluminum	3-137-087

Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 10 pcs. In box or packed in air cushion bags



The nut with gasket and micro switch are enclosed in the box.

Accessories

Description



Power Supply

Power Supply IP42 for LED- and Illumination applications indoor 90~264 VAC => 24 VDC 0.34 A 8 W