


TABLE 1		INSERTION LOSS (MAX dB)		VSWR
MODEL NUMBER	LENGTH	20GHz	50GHz	DC ~ 50GHz
415-0536-MM100	100mm +4/-0	-0.6	-1.0	1.3
415-0536-MM200	200mm +5/-0	-1.0	-1.6	1.3
415-0536-MM500	500mm +10/-0	-2.2	-3.1	1.3
415-0536-M1.0	1000mm +15/-0	-3.6	-5.5	1.3

REV	ECO	DATE
1	INITIAL RELEASE	9-23-2021



- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
 2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.

 This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	Model No: 415-0536-MXXXX		JOHNSON	
	RoHS ☒ (EU)/2015/863 COMPLIANT	Cage Code 34078	Title: CABLE ASSY, METRIC, STR 2.4MM PLUG TO STR 2.4MM PLUG, .096" FLEXIBLE, LOW LOSS CABLE	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH .XX ± .01 .XXX ± .003 .XXXX ± .0010 ANGLE ± 2°	3RD ANGLE PROJECTION Drawn by: TOMMY REN Date: 9-23-2021	Drawing No. 415-0536-MXXXX	REV. 1
	Size A	DO NOT SCALE DRAWING	Workmanship Std: NONE	Sheet 1 OF 1