



WARNING

All Drawings and Specifications are and remain our Property and must be returned to us. All Specifications and Drawings are confidential and are not to be disclosed to any persons other than those to whom they are sent. Unauthorized reproduction in any form of this Drawing in part or full is prohibited.

ISSUE NO.	ENG. REL. NO.	REV. NO.	DATE	APP. BY.
01	ORIGINAL	-	22.09.22	SPK



PART CODE.	Ø C	L	Ø D	Ø A
MS3420-3	9.50	73.02	5.33	3.30
MS3420-4	12.80	69.80	7.70	5.60
MS3420-6	15.600	66.680	10.850	7.920
MS3420-8	18.770	63.500	14.020	11.100
MS3420-10	21.950	60.330	15.620	14.270
MS3420-12	26.900	57.150	18.800	15.880
MS3420-16	33.380	53.980	23.550	19.050
MS3420-20	40.410	50.800	31.500	23.800
MS3420-24	46.790	47.620	34.670	31.750
MS3420-28	53.000	44.450	41.000	34.900
MS3420-40	72.000	38.100	60.050	47.600

NOTE:

- 1.LESS THAN 0.5MM RAISED PARTLINE(FLASH) IS ACCEPTABLE
- 2.MATERIAL:NEOPRENE IN ACCORDANCE WITH AMS3208, BLACK 40 TO+100° C(-40 TO +212°F)
- 3.HARDNESS:-50±5 DUROMETER

SL.NO.	DRG.NO.	FINISH

Amphenol**Amphenol Interconnect India Pvt. Ltd.**
BANGALORE - 560 100

Mat.Spec.

--

TITLE

MS RUBBER BUSHING
OUT LINE DWGDwg. Size **A4**

Dwg.No.

B75889All Dimensions are in
MM/INCHES

Sheet 1 OF 1

	NAME	DATE
Drawn by	NANDA	22.09.22
Checked by	JAGAN	22.09.22
App. by	SPK	22.09.22

TOLERANCES

DECIMALS : ±0.10

ANGLES : ±2°

Scale:- **NTS**

SURFACE AREA: N/A

QF-DEV-83 REV.NO. :03

DO NOT SCALE THIS DRAWING