





NOTES:

RATED VOLTAGE: MAX. 63V AC/DC
RATED CURRENT: MAX. 16A at 40°C (derating has to be considered)
IP RATING: IP67 (mated and locked condition)
TEMPERATURE RANGE: -25°C TO +85°C

CABLE PRINTING (sequence as shown below):

- MOLEX engineering no. (see page 2)
- MOLEX material no. (see page 2)
- MOLEX MAX. 63V AC/DC MAX. 16 A USR
- MOLEX AND DATE OF MANUFACTURING (YY=YEAR; WW=WEEK): MXYWW
- Not for current interrupting
- PROFINET 24V Power 4x2,5 + FE

PART ACCORDING PRODUCT SPEC: 1205010169

PACKAGING ACCORDING PACKAGING SPEC: 1201202000

TABLE 1

POS	DESCRIPTION	MATERIAL	FINISH
1	NUT M12 FE	BRASS	Ni
2	CONTACT 15 MA	BRASS	Au
3	CONTACT 15 FE	BRASS	Au
4	INSERT	PA	GREY
5	OVERMOLD	TPE	BLACK
6	CABLE 5x2.5 D11.3 WSOR	PUR	GREY
7	GASKET OR 8.2X1.25	FKM	BLACK
OPTIONAL 8	ID-CARRIER	-	-

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED ATTRIBUTE TO GENERAL MARKET IN ECTR			molex										
	mm		2:1															
	GENERAL TOLERANCES (UNLESS SPECIFIED)																	
	ANGULAR TOL ± 1.0°																	
	4 PLACES		±		EC NO: 735577 DRWN: MARUTD 2023/01/12 CHK'D: RSILLER 2023/01/19 APPR: RSILLER 2023/01/19			CSE M12 5P LC FE STR WSOR GY XM UNSH										
	3 PLACES		±															
	2 PLACES		± 0.05															
	DIVISIONAL SYMBOLS	1 PLACE		± 0.3		INITIAL REVISION: DRWN: FDAERNER 2020/01/24 APPR: RSILLER 2021/03/15			DOCUMENT NUMBER 1205000200		DOC TYPE PSD	DOC PART 000	REVISION A1					
		0 PLACES		± 0.5														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING									SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
					A3-SIZE	120500	SEE TABLE 2	GENERAL MARKET	1 OF 2									

ENGINEERING NO - NUMERICAL CODE (Available parts see PART LIST table. Other parts available upon request).




TABLE 2

NOMINAL SECTION 2,5mm²			
MATERIAL NO.	ENGINEERING NO.	L [mm]	TOLERANCE [mm]
1205000200	L0P5000B63M010	1000	+40
1205000201	L0P5000B63M020	2000	+60
1205000202	L0P5000B63M030	3000	+60
1205000203	L0P5000B63M050	5000	+60
1205000204	L0P5000B63M100	10000	+80
1205000205	L0P5000B63M150	15000	+140
1205000206	L0P5000B63M200	20000	+140

DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19	11:13:08
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED ATTRIBUTE TO GENERAL MARKET IN ECTR				molex							
	mm		1:1													
	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	ANGULAR TOL ± 1.0°				EC NO: 735577 DRWN: MARUTD 2023/01/12 CHK'D: RSILLER 2023/01/19 APPR: RSILLER 2023/01/19				CSE M12 5P LC FE STR WSOR GY XM UNSH							
	4 PLACES		±													
	3 PLACES		±													
	2 PLACES		± 0.05		INITIAL REVISION: DRWN: FDAFERNER 2020/01/24 APPR: RSILLER 2021/03/15				DOCUMENT NUMBER 1205000200		DOC TYPE PSD	DOC PART 000	REVISION A1			
	1 PLACE		± 0.3													
	0 PLACES		± 0.5													
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
							A3-SIZE		120500				GENERAL MARKET		2 OF 2	