




NOTES:

- 1. RESISTANCE @ 25°C : 50KΩ ± 1%
- 2. BETA VALUE (0/50°C) : 4035K ± 1%
- 3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
- 4. THERMAL TIME CONSTANT : 15SEC IN WATER
- 5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
- 6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
- 7. DISSIPATION FACTOR : 1mW/°C.
- 8. LASER MARKING "MOLEX-DATE CODE(MM/YY)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		NTS												
	0 1 2	GENERAL TOLERANCES (UNLESS SPECIFIED)				GLASS NTC PROBE A -50K±1%,B4035,L100									
ANGULAR TOL ± °															
DIVISIONAL SYMBOLS	4 PLACES		±	EC NO: 718518		2022/08/04		PRODUCT CUSTOMER DRAWING							
	3 PLACES		±	DRWN: NANDAK											
	2 PLACES		±	CHK'D: RBBHASKAR											
	1 PLACE		±	APPR: RBBHASKAR		2022/08/24		DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION		
	0 PLACES		±	INITIAL REVISION:		2022/08/24									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		218537		2185373907		GENERAL MARKET		1 OF 2	

