





NOTES:

1. RESISTANCE @ 25°C : 10KΩ ± 1%
2. BETA VALUE (0/50°C) : 4035K ± 1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
4. THERMAL TIME CONSTANT : 15SEC IN WATER
5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
7. DISSIPATION FACTOR : 1mW/°C.
8. LASER MARKING "MOLEX-DATE CODE(MM/YY)"

SS HOUSING DETAILS:



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex			
	mm		NTS								
	GENERAL TOLERANCES (UNLESS SPECIFIED)				GLASS NTC MOUNTING -10K±1%,B4035,L300						
	ANGULAR TOL ± °										
	4 PLACES		±	PRODUCT CUSTOMER DRAWING							
	3 PLACES		±								
	2 PLACES		±								
	1 PLACE		±								
	0 PLACES		±	DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
DIVISIONAL SYMBOLS		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER	
F_A = 0											
F_E = 0											
F_E = 0											

