





REV	ECN	APP'D
C	3937	JT



MOUNTING HARDWARE
(3 EACH SUPPLIED)



- NOTES:
1. SOCKET DESIGNED TO ACCEPT RELAYS PER MIL-R-6106 AND MS27743.
 2. MATERIALS:
 - A. INSULATOR - POLYETHERIMIDE, COLOR: GREEN.
 - B. CONTACTS - BERYLLIUM COPPER, HEAT TREATED.
PLATING: MATING AREA - 50 MICROINCH GOLD PER MIL-G-45204
OVER 30 MICROINCH NICKEL PER QQ-N-290.
SOLDER TAILS - 100 MICROINCH TIN-LEAD PER MIL-P-81728.
 - C. HARDWARE -
STUD & NUT - CORROSION RESISTANT STEEL TYPE 300
OR A286, PASSIVATED PER QQ-P-35.
WASHER - CRES, PASSIVATE.
 3. MOUNTING HARDWARE SUPPLIED IN SEPARATE BAG WITHIN UNIT PACKAGE.
 4. RECOMMENDED HOLE DIAMETERS FOR SOLDER PINS AS FOLLOWS:
FOR .050 DIA PIN: .057-.067 DIA (2 PLCS).
FOR .080 DIA PIN: .095-.105 DIA (9 PLCS).
 5. RECOMMENDED HOLE DIAMETER FOR MOUNTING STUD: .150-.160 DIA (3 PLCS).

DIMENSIONS	TOLERANCES	PROJECTION	SPECIFICATION DRAWING		TITLE			
			ENGR	CHKD		SIZE	DWG NO.	REV
ANSI Y14.5M UNITS: INCHES ACAD FILE	.XX ±.01 .XXX ±.005 ANGLES ±2°		M. CALLA 11/14/89		RELAY SOCKET - 3 POLE	B	RSN112010	C
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		APPD	D. SWAFFIELD 8/10/90	CODE: 58982	SCALE: NONE	SHEET 1 OF 1	