





ELECTRICAL DATA:		
TESTS	CONDITIONS	ACCEPTANCE CRITERIA
I _{ex}	@ 8.5V, 200Hz, PIN 1 - PIN 3	65mA Max.
Sec. N.L.V	@ 8.5V, 200Hz, PIN 1 - PIN 3	
	PIN 1 - PIN 2 = PIN 2 - PIN 3 =	4.250V $\pm 2\%$
	PIN 4 - PIN 5 = PIN 5 - PIN 6 =	2.125V $\pm 2\%$
DCR	@ 20°C, PIN 1 - PIN 3 =	46.00 Ω $\pm 15\%$
	@ 20°C, PIN 4 - PIN 6 =	10.30 Ω $\pm 15\%$
HIPOT	PRIMARY - SECONDARY	250V, 60Hz, 1 SEC

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™			
0	RELEASED. C.I.	06/20/19	ELECTRONIC DIVISION			
			52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181 FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: AUDIO	DWG. NO.
			DATE: 06/20/19	APP'D. BY:	TRANSFORMER	104SL
			DIMENSIONS: IN(X) MM()			