




13	12	11	10	9	8	7	6	5	4	3	2	1
TABLE OF CONTENTS												
SHEET NO.	SHEET DESCRIPTION											
1	NOTES AND BOM											
2	CONFIGURATIONS											
3	ADAPTOR DETAIL											



1X3 C.S.



2X4



2X8/2X10

ADAPTOR NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

a. APPLICATION SPECIFICATION SEE: 1600730001-AS REV C

-DESIGNED TO MATE WITH BACKSHELL

AS SPECIFIED IN THE BOM

-COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY. SEE

GM DRAWING 13109960 REV 006 FOR CONDUIT SPECIFICATIONS

b. PRODUCT SPECIFICATION: TBD

c. PACKAGING SPECIFICATION SEE: TBD

d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR

PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300

e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS

(COMPANY ID#13255)

f. FOLLOWING PRODUCTION CODES TO BE PRESENT

-DATE CODE

-MOLD CAVITY CODE

-MOLEX LOGO

-RECYCLE CODE

2. DESIGN - MATERIALS:

a. PA66 0% GLASS FILLED

b. BLACK

3. DESIGN GEOMETRY:

a. THIS IS A 100% CAD GENERATED PART. THE CAD MATHEMATICAL DATA

IS THE MASTER FOR THIS PART. FOR DIMENSIONAL OR ANY INFORMATION

NOT SHOWN ON THIS DRAWING, ANALYZE THE CAD MODEL.

b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 2009.

c. CORNERS SHOWN AS SHARP TO BE R 0.1.

d. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (CLASS B).

e. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (CLASS C)

FOR SPECIFIED AREAS ON THE ADAPTOR.

f. ALLOWABLE FLASH, PARTING LINES MISMATCH, EJECTOR PINS MARK, AND GATE

VESTIGE TO BE +0.30 MAX PROTUSION.

BILL OF MATERIALS (BOM)							
DESCRIPTION	PART NUMBER	CIRCUIT SIZE	COLOR	RIBS	MATING DRAWING	CONVOLUTE SIZE	STATUS
1X3 C.S., WITH RIB	204351-0304	1X3 C.S.	BLACK	YES	2043510301 PSD	AD 10 SOFANOUE VARIANT 1	SALEABLE
2X4, WITH RIB	34951-0831	2X4	BLACK	YES	SD-34951-0001	NW 12 SCHLEMMER	SALEABLE
					SD-34950-0001		
2X4, WITHOUT RIB	34951-0841	2X4	BLACK	NO	SD-34951-0001	NW 12 SCHLEMMER	SALEABLE
					SD-34950-0001		
2X8/2X10, WITH RIB	34951-1631	2X8/2X10	BLACK	YES	SD-34951-0001	NW 16 SCHLEMMER	SALEABLE
					SD-34950-0001		
2X8/2X10, WITHOUT RIB	34951-1641	2X8/2X10	BLACK	NO	SD-34951-0001	NW 16 SCHLEMMER	SALEABLE
					SD-34950-0001		

A10	CHANGED TOLERANCE ON DIM C FROM 0.12 TO 0.10 TO MATCH PDD
A9	CHANGED PARTS STATUS TO SALEABLE
A8	UPDATED RIB FEATURES AND CONTROLS
A7	UPDATE TOLERANCES FOR MANUFACTURING
A6	UPDATE TOLERANCES FOR MANUFACTURING
A5	UPDATE REV DESCRIPTION TABLE
A4	UPDATE NOTE 1.a FOR CONDUIT DEFINITION
A3	RELEASE P/N 204351-0304 FOR SALEABLE
A2	UPDATED CHARTS AND BALLOON NUMBERS
A1	MODIFIED SETTING IN PLM
A	DRAWING RELEASE
REV	DESCRIPTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 632862

DRWN: PPALLAN

CHKD: MVANSLAMBROU

APPR: MVANSLAMBROU

2020/02/25

2020/02/26

2020/02/26

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.1

1 PLACE ± 0.2

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS

mm

SCALE

1:1

DRWN BY

DATE

DDEB

2017/12/08

CHK'D BY

DATE

APPR BY

DATE


MVANSLAMBROU

2017/12/20

DRAWING SIZE

THIRD ANGLE PROJECTION

A2



PRODUCT CUSTOMER DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

34951

DOCUMENT NUMBER

349510001

DOC TYPE

PSD

DOC PART






000

SHEET NUMBER

1 OF 4

INSPECTION NUMBER LOG												
LAST NUMBER: 53												
ADDED: 41,51,43,53,45,48,27,28,14,25,17,19,15,27												
REMOVED: 1,2,3,4,5,43,53												


RELEASE STATUS	P1	RELEASE DATE	2020/02/26	00:51:12								
13	12	11	10	9	8	7	6	5	4	3	2	1

13	12	11	10	9	8	7	6	5	4	3	2	1
SHEET DESCRIPTION												
CONFIGURATIONS												
WITH RIB						WITHOUT RIB						
												
1X3 C.S.												
												
2X4						2X4						
												
2X8 / 2X10						2X8 / 2X10						


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
EC NO: 632862 DRWN: PPALLAN CHKD: MVANSLAMBROU APPR: MVANSLAMBROU	2020/02/25 2020/02/26 2020/02/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE		molex MX150 90° ADAPTOR							
				mm	2:1									
		ANGULAR TOL ± °		DRWN BY		DATE								
		4 PLACES ±		DDEB		2017/12/08								
		3 PLACES ±		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING						
		2 PLACES ± 0.1		APPR BY		DATE								
		1 PLACE ± 0.2		MVANSLAMBROU		2017/12/20								
		0 PLACES ±												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER				
A10	REV			A2				34951						
RELEASE STATUS		P1	RELEASE DATE		2020/02/26 00:51:12		DOCUMENT NUMBER		349510001		DOC TYPE PSD		DOC PART 000	SHEET NUMBER 2 OF 4

13	12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	----	---	---	---	---	---	---	---	---	---


SHEET DESCRIPTION
DUAL ROW ADAPTOR DETAIL



WITH RIB




WITHOUT RIB




DUAL ROW

* = SEE ADAPTOR NOTES - 3.e.




DETAIL D
SCALE 3:1




DETAIL F
SCALE 3:1

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	P	R	C	D	E
2X4 WITH RIB	1.35	16.10	0.80	N/A	N/A
2X4 W/O RIB	N/A	16.10	N/A	3.60	5.10
2X8/2X10 WITH RIB	1.45	19.30	0.80	N/A	N/A
2X8/2X10 W/O RIB	N/A	19.30	N/A	3.60	5.10



SECTION E-E





FOR WITH RIB AND WITHOUT RIB

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
EC NO: 632862 DRWN: PPALLAN CHKD: MVANSLAMBROU APPR: MVANSLAMBROU	2020/02/25 2020/02/26 2020/02/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex MX150 90° ADAPTOR			
		ANGULAR TOL ± °		mm	2:1				
		4 PLACES ±		DRWN BY	DATE				
		3 PLACES ±		DDEB	2017/12/08	PRODUCT CUSTOMER DRAWING			
		2 PLACES ± 0.1		CHK'D BY	DATE				
		1 PLACE ± 0.2		APPR BY	DATE	SERIES MATERIAL NUMBER CUSTOMER			
		0 PLACES ±		MVANSLAMBROU	2017/12/20	34951			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	DOCUMENT NUMBER 349510001 DOC TYPE PSD DOC PART 000 SHEET NUMBER 3 OF 4			
A10	REV			A2					

SHEET DESCRIPTION
SINGLE ROW ADAPTOR DETAIL

CHARTED DIMENSION			
DESCRIPTION	DIMENSIONS		
	A	B	C
1X3 C.S. WITH RIB	7.1	9.95	0.75




* = SEE ADAPTOR NOTES - 3.e.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		Material: Heat treat:			molex								
mm		5:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				Finish:			MX150 90° ADAPTOR								
ANGULAR TOL ± °				CURRENT REV DESC:											
4 PLACES		±		EC NO: 632862 DRWN: PPALLAN 2020/02/25 CHK'D: MVANSLAMBROU 2020/02/26 APPR: MVANSLAMBROU 2020/02/26 ORIG DRWN BY: DDEB 2017/12/08			PRODUCT CUSTOMER DRAWING								
3 PLACES		±													
2 PLACES		± 0.1													
1 PLACE		± 0.2													
0 PLACES		±													
TOOL NUMBER				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A2-SIZE		34951						4 OF 4	





DOCUMENT STATUS	P1	RELEASE DATE	2020/02/26 00:51:12
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
BLADE CONNECTOR ASSEMBLY	

DESCRIPTION	DIMENSIONS		
	A	B	C
2X2	TBD	TBD	TBD
2X3	TBD	TBD	TBD
2X4	12.46	1.75	27.9
2X6	15.96	1.75	32.7
2X8	TBD	TBD	TBD
2X10	22.97	1.75	46.4




LASER MARKING ON THIS SURFACE
SEE NOTE 3g.



PRIMARY LOCK REINFORCER (PLR) SHOWN
IN PRE-STAGE POSITION

SECTION Z-Z



PRIMARY LOCK REINFORCER (PLR) SHOWN
IN FINAL-LOCK POSITION

SECTION Y-Y


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex				
	mm		3:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
	ANGULAR TOL ± 3.0 °													
	4 PLACES		±							PRODUCT CUSTOMER DRAWING				
	3 PLACES		±											
	2 PLACES		± 0.1							DOCUMENT NUMBER SD-160011-0001				
	1 PLACE		± 0.2											
	0 PLACES		±		MATERIAL NUMBER A1-SIZE 160011					CUSTOMER GENERAL MARKET		SHEET NUMBER 5 OF 11		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
	THIRD ANGLE PROJECTION				DRAWING		SERIES							

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------


SHEET DESCRIPTION
BACKSHELL NOTES

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED


1. GENERAL:
- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY
 - SPECIFIED IN MOLEX DRAWING SD-33482-0001
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX

- CUSTOMER MODEL COMPONENTS
- 0 - SCHLEMMER BACKSHELL ONLY
 - 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
 - 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
 - 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
 - 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
 - 5 - MOLEX BACKSHELL ONLY
 - 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
 - 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
 - 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
 - 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

- BACKSHELL FEATURES
- 1 - WITH RIBS
 - 2 - WITHOUT RIBS
 - 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20

BLADE SEALED ASSEMBLY

BACKSHELL (BKS)







90° ADAPTOR

SCALE 1.5:1

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex														
	mm		1.5:1																					
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL														
 = 0																								
 = 0	ANGULAR TOL		± 3.0 °		DRWN: PMANJUNATHAC 2018/01/01					PRODUCT CUSTOMER DRAWING														
 = 0	4 PLACES		±																					
 = 0	3 PLACES		±		CHK'D: MVANSLAMBROU 2018/02/16					DOCUMENT NUMBER					DOC TYPE	DOC PART	REVISION							
 = 0	2 PLACES		± 0.1												APPR: MVANSLAMBROU 2018/02/16					SD-160011-0001			PSD	001
 = 0	1 PLACE		± 0.2		INITIAL REVISION:					THIRD ANGLE PROJECTION													DRAWING	
 = 0	0 PLACES		±												DRWN: KBORUSZEWSKI 2014/02/19					GENERAL MARKET				
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				APPR: VKOSHY 2014/03/05																			
 = 0																								

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	









Partial A-A
SCALE 7:2

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex								
	mm		3.5:1															
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL								
 = 0																		
ANGULAR TOL ± 3.0 °																		
 = 0	4 PLACES		±															
 = 0	3 PLACES		±															
 = 0	2 PLACES		± 0.1		INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05					PRODUCT CUSTOMER DRAWING								
 = 0	1 PLACE		± 0.2															
 = 0	0 PLACES		±															
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
 = 0							A1-SIZE		160011		SD-160011-0001		PSD		001		A5	
 = 0							A1-SIZE		160011		MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
 = 0							A1-SIZE		160011				GENERAL MARKET				8 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
MOLEX BACKSHELL	





SECTION B-B

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05				molex MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	= 0	mm		1:1											
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)								PRODUCT CUSTOMER DRAWING					
	= 0	ANGULAR TOL		± 3.0 °											
	= 0	4 PLACES		±						DOCUMENT NUMBER		DOC TYPE		DOC PART	
	= 0	3 PLACES		±		SD-160011-0001				PSD		001		A5	
	= 0	2 PLACES		± 0.1											
	= 0	1 PLACE		± 0.2		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
	= 0	0 PLACES		±											
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES					
	= 0							A1-SIZE		160011					

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------



MOLEX BACKSHELL CONFIGURATIONS

CHARTED DIMENSIONS												
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.29	94.34	93.98	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
2X10	STANDARD	STANDARD	132.54	102.79	102.78	84.07	36.10	45.44	45.44	42.65	45.44	68.18





(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL





(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH BLADE BACKSHELL





(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE

BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




(ØDIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
	= 0	mm												1:1			
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	= 0	ANGULAR TOL ± 3.0°															
	= 0	4 PLACES		±		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				PRODUCT CUSTOMER DRAWING							
	= 0	3 PLACES		±													
	= 0	2 PLACES		± 0.1													
	= 0	1 PLACE		± 0.2		INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
	= 0	0 PLACES		±						SD-160011-0001		PSD		001		A5	
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
	= 0							A1-SIZE		160011				GENERAL MARKET		11 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:24
-----------------	----	--------------	------------	----------

MX150 GEN 2 BLADE 2X4 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	SPS/NYLON GF20
B-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	SPS/NYLON GF20
C-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	SPS/NYLON GF20
D-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR-1	PLR-1	NATURAL	SPS/NYLON GF20
PLR-3	PLR-3	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-160011-0001																				
ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS								STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION										BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8							
KEY A, BLACK, WITH CLIPSLOT	160011-4001	A-BLK-CLIP	GCO	PLR-1	M-R										PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-4002	B-LG-CLIP	GCO	PLR-1	M-R										PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160011-4003	C-DG-CLIP	GCO	PLR-1	M-R										PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160011-4004	D-SG-CLIP	GCO	PLR-1	M-R										PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4007	A-BLK-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8		PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-4008	B-LG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8		PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160011-4009	C-DG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8		PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160011-4010	D-SG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8		PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4013	A-BLK-CLIP	GCP	PLR-1	M-R				4	5					PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4014	A-BLK-CLIP	GCP	PLR-1	M-R					5	6		8		PLANNED OBSOLECSENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4015	A-BLK-CLIP	GCP	PLR-1	M-R				4	5			8		SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4801	A-BLK-CLIP	GCO	PLR-3	M-B										OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-4802	B-LG-CLIP	GCO	PLR-3	M-B										OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4811	A-BLK-CLIP	GCP	PLR-3	M-B				4	5					OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4832	A-BLK-CLIP	GCP	PLR-3	M-B					5	6		8		OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4834	A-BLK-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8		OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-4847	B-LG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8		OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160121-4852	C-DG-CLIP	GCO	PLR-3	M-B										OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160121-4853	D-SG-CLIP	GCO	PLR-3	M-B										OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4854	A-BLK-CLIP	GCP	PLR-3	M-B				4	5			8		OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841

MX150 GEN 2 BLADE 2X6 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	SPS/NYLON GF20
B-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	SPS/NYLON GF20
C-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	SPS/NYLON GF20
D-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR-1	PLR-1	NATURAL	SPS/NYLON GF20
PLR-3	PLR-3	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-160011-0001


ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK, WITH CLIPSLOT	160011-6001	A-BLK-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-6002	B-LG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160011-6003	C-DG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160011-6004	D-SG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160011-6007	A-BLK-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-6008	B-LG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160011-6009	C-DG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160011-6010	D-SG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENSE		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160121-6201	A-BLK-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-6202	B-LG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160121-6227	A-BLK-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-6228	B-LG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160121-6261	C-DG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160121-6262	D-SG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160121-6263	C-DG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160121-6264	D-SG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220




ECN NO.: 687417	DOCUMENT NO.: SD-160011-0002	REV
DATE:12/7/2021		PAY

SHEET DESCRIPTION


CONFIGURATIONS




2X2 - STD.
2X2 - TRNS. - SILICONE FREE †




2X2 - STD. - WITH CLIPSLOT *




† 2X2 - UL V0




2X2 - STD. - LENGTHENED




2X3 - STD.
2X3 - TRNS. - CONTAINS SILICONE †




2X3 - STD. - WITH CLIPSLOT *




2X4 - STD.




2X4 - STD. - WITH CLIPSLOT *




† 2X4 - UL V0




† 2X4 - UL V0-WITH CLIPSLOT*




2X6 - STD.
C1 † 2X6 - TRNS.




2X6 - STD. - WITH CLIPSLOT *
C1 † 2X6 - TRNS. - WITH CLIPSLOT *




† 2X6 - UL V0




2X8 - STD.




2X8 - STD. - WITH CLIPSLOT *



2X10 - STD.



2X10 - STD. - WITH CLIPSLOT *



† 2X10 - UL V0


* WITH CLIPSLOT CONFIGURATION DOES NOT
MEET THE USCAR PACKAGING FRAME REQUIREMENTS
† MINOR GEOMETRY DIFFERENCE THAN STANDARD CONFIGURATION
SEE NOTES 1a & 2a-b FOR MORE INFORMATION

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
		DIMENSION UNITS		SCALE		CURRENT REV DESC:									
	= 0	mm		1:1		molex MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL									
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	= 0	ANGULAR TOL ± 1.0 °													
	= 0	4 PLACES		±								EC NO: 171650			
	= 0	3 PLACES		±								DRWN: DDEB 2018/01/19			
	= 0	2 PLACES		± 0.1		CHK'D: MVANSLAMBROU 2018/02/16									
	= 0	1 PLACE		± 0.2		APPR: MVANSLAMBROU 2018/02/16									
	= 0	0 PLACES		±		INITIAL REVISION:									
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES					
	= 0							A1-SIZE		33472					
	= 0					DOCUMENT NUMBER		DOC TYPE		DOC PART					
	= 0					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
						SD-33472-0001		PSD		001					
								GENERAL MARKET		2 OF 11					
								C2							


SHEET DESCRIPTION

KEY CONFIGURATIONS


2X2




KEY A



KEY B




KEY C




KEY D


2X3




KEY A



KEY B




KEY C




KEY D


2X4




KEY A



KEY B



KEY C





KEY D

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
▽ = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC:										molex											
▽ = 0		mm		1:1																							
▽ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650										MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL											
▽ = 0																											
▽ = 0		ANGULAR TOL ± 1.0 °				DRWN: DDEB 2018/01/19										PRODUCT CUSTOMER DRAWING											
▽ = 0		4 PLACES ±																									
▽ = 0		3 PLACES ±				CHK'D: MVANSLAMBROU 2018/02/16										DOCUMENT NUMBER SD-33472-0001						DOC TYPE PSD		DOC PART 001		REVISION C2	
▽ = 0		2 PLACES ± 0.1																									
▽ = 0		1 PLACE ± 0.2				INITIAL REVISION: DRWN: APROFFITT 2014/05/14										APPR: VKOSHY 2014/06/27											
▽ = 0		0 PLACES ±																									
▽ = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION				DRAWING A1-SIZE		SERIES 33472		MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 3 OF 11									









SHEET DESCRIPTION

RECEPTACLE CONNECTOR ASSEMBLY




B APPLIES TO 2X2 - STD. - WITH CLIPSLOT ONLY

DESCRIPTION	DIMENSIONS						
	A	B	C	D	E	F	J
2X2 W/O CLIPSLOT	18.58	1.75	25.45	24.81	37.65	N/A	2.75±0.50
2X2 W/ CLIPSLOT	18.58	1.75	27.65	24.81	37.65	N/A	2.75±0.50
2X2 LENGTHENED	18.58	1.75	25.45	24.81	42.25	N/A	2.75±0.50
2X3 W/ CLIPSLOT	22.25	3.5	30.50	N/A	37.65	27.96	4.0±0.4
2X3 W/O CLIPSLOT	22.25	3.5	26.24	24.90	37.65	N/A	4.0±0.4
2X4 W/ CLIPSLOT	25.75	1.75	31.50	N/A	37.65	28.00	2.75±0.50
2X4 W/O CLIPSLOT	25.75	1.75	29.19	24.81	37.65	N/A	2.75±0.50
2X6 W/ CLIPSLOT	32.75	1.75	35.58	N/A	37.65	27.76	2.75±0.50
2X6 W/O CLIPSLOT	32.75	1.75	35.58	24.90	37.65	N/A	2.75±0.50
2X6 W/O CLIPSLOT V0	32.75	1.75	35.58	25.0	37.65	N/A	2.75±0.50
2X8 W/O CLIPSLOT	39.80	1.75	42.25	24.90	37.65	N/A	4.0±0.4
2X8 W/ CLIPSLOT	39.80	1.75	42.25	N/A	37.65	27.80	4.0±0.4
2X10 W/O CLIPSLOT	46.75	1.75	49.95	24.90	37.65	N/A	2.75±0.50
2X10 W/ CLIPSLOT	46.75	1.75	49.95	N/A	37.65	27.80	2.75±0.50



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION Y-Y



SECTION Z-Z

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex			
	mm	1:1									
	= 0			GENERAL TOLERANCES (UNLESS SPECIFIED)				MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL			
	= 0										
	= 0	ANGULAR TOL ± 1.0 °		EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				PRODUCT CUSTOMER DRAWING			
	= 0	4 PLACES ±									
	= 0	3 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27				DOCUMENT NUMBER SD-33472-0001 DOC TYPE PSD DOC PART 001 REVISION C2			
	= 0	2 PLACES ± 0.1									
	= 0	1 PLACE ± 0.2		THIRD ANGLE PROJECTION 				MATERIAL NUMBER CUSTOMER GENERAL MARKET SHEET NUMBER 5 OF 11			
	= 0	0 PLACES ±									
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:25
-----------------	----	--------------	------------	----------

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33472-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34951-0001.

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34951-XXXX

CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR


MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20

RECEPTACLE SEALED ASSEMBLY

BACKSHELL (BKS)






SCALE 2:1

90° ADAPTOR




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27 THIRD ANGLE PROJECTION DRAWING A1-SIZE SERIES 33472						

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




V


V



Partial V-V
SCALE 4:1

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex							
		mm		4:1															
		GENERAL TOLERANCES (UNLESS SPECIFIED)										MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL							
		ANGULAR TOL ± 1.0 °																	
 = 0		4 PLACES		±		EC NO: 171650													
 = 0		3 PLACES		±		DRWN: DDEB 2018/01/19													
 = 0		2 PLACES		± 0.1		CHK'D: MVANSLAMBROU 2018/02/16													
 = 0		1 PLACE		± 0.2		APPR: MVANSLAMBROU 2018/02/16													
 = 0		0 PLACES		±		INITIAL REVISION:													
 = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
 = 0								A1-SIZE		33472		SD-33472-0001		PSD		001		C2	
 = 0												MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
 = 0														GENERAL MARKET		7 OF 11			

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:25
-----------------	----	--------------	---------------------



SHEET DESCRIPTION	
MOLEX BACKSHELL	



DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:25
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27 THIRD ANGLE PROJECTION A1-SIZE 33472				mo lex MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-33472-0001 DOC TYPE PSD DOC PART 001 REVISION C2 MATERIAL NUMBER CUSTOMER GENERAL MARKET SHEET NUMBER 8 OF 11					
	mm		3:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	ANGULAR TOL ± 1.0 °													
	4 PLACES		±											
	3 PLACES		±											
	2 PLACES		± 0.1											
	1 PLACE		± 0.2											
	0 PLACES		±											
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													

18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

SHEET DESCRIPTION			
SCHLEMMER BACKSHELL CONFIGURATIONS			

CHARTED DIMENSIONS	
DESCRIPTION	DIMENSIONS
	H
2X3 W/ CLIPSLOT	N/A
2X3 W/O CLIPSLOT	28.50
2X4 W/ CLIPSLOT	N/A
2X4 W/O CLIPSLOT	30.75
2X6 W/ CLIPSLOT	N/A
2X6 W/O CLIPSLOT	35.83



RECEPTACLE SEALED ASSEMBLY WITH RECEPTACLE BACKSHELL

QUALITY SYMBOLS

FA

= 0

FB

= 0

FC

= 0

FV

= 0

CC

= 0

XC

= 0

CS

= 0

CV

= 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 171650

DRWN: DDEB

CHKD: MYANSLAMBROU

APPR: MYANSLAMBROU

2018/01/19

2018/02/16

2018/02/16

REV

C2

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.1

1 PLACE ± 0.2

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION UNITS

mm

SCALE

4:1

DRWN BY

DATE

APPROFIT

2014/05/14

CHK'D BY

DATE

KBORUSZEWSKI

2014/06/16

APPR BY

DATE

VKOSHY

2014/06/27

DRAWING SIZE

THIRD ANGLE PROJECTION

A1

molex®

MX150 RCPT

DUAL ROW SEALED ASSEMBLY MAT SEAL

PRODUCT CUSTOMER DRAWING

SERIES

33472

MATERIAL NUMBER

SD-33472-0001

CUSTOMER

GENERAL MARKET

DOCUMENT NUMBER

DOC TYPE

DOC PART

SHEET NUMBER


SD-33472-0001

PSD


001

9 OF 11


18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1




KEYING OPTION A
SCALE 4:1




KEYING OPTION B
SCALE 4:1




KEYING OPTION C
SCALE 4:1




KEYING OPTION D
SCALE 4:1




DETAIL A
SCALE 10:1



SECTION A-A




SECTION B-B




DETAIL C
SCALE 20:1

APPLIES 2X
SEE KEYING OPTION VIEWS
FOR POSITIONS



PACKAGE FRAME



MATING INTERFACE NOTES: VALID UNLESS OTHERWISE SPECIFIED

- GENERAL:
 - DESIGNED TO MATE WITH MOLEX CONNECTOR 33472-2XXX & 160008-0XXX & 160074-0XXX
A FULL SHROUD ON THE MATING CONNECTOR IS REQUIRED TO INSURE THAT THE CONNECTOR-HEADER POLARIZATION FEATURES (OPTIONS A THRU D) WILL FUNCTION. THE FULL SHROUD ALSO PREVENTS SCOOP DAMAGE TO THE HEADER PINS. REFER TO 'SAE/USCAR-12 CONNECTOR DESIGN GUIDE LINES' FOR ADDITIONAL INFORMATION
 - PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: ES-40000-5016
 - FLAMMABILITY REQUIREMENT: PER ISO3795 OR GM3191
 - BURN RATE 100mm/MIN MAXIMUM
 - MATERIAL MUST BE SELF EXTINGUISHING
- MATERIALS:
 - MATERIAL: SPS/NYLON GF20, REGRIND 20% MAX BY WEIGHT
 - STANDARD COLORS FOR POLARIZATION (SEE KEYING OPTIONS TABLE).
DEVIATION REQUIRES APPROVAL OF AUTHORIZED PERSON
 - FOR BLADE BASE MATERIAL, PLATING AND PROCESS LUBRICANT:
 - TIN: - BASE MATERIAL: COPPER ALLOY, CONDUCTIVITY >=60% IACS AT 20°C;
TENSILE STRENGTH >= 410 N/mm² - BARRIER MATERIAL: NICKEL DEPOSIT FROM NICKEL SULFAMATE
PLATING SOLUTION W/O ANY ADDITIVES
THICKNESS: 1.25 - 2.25 MICROMETERS
- TOP LAYER: 100% ELECTRO-DEPOSITED TIN, MATTE FINISH
THICKNESS: 2.5 - 4.0 MICROMETERS
 - SILVER: - BARRIER MATERIAL: ELECTRO-DEPOSITED DUCTILE SULPHAMATE NICKEL
THICKNESS: 1.25 - 2.25 MICROMETERS
- TOP LAYER: ELECTRO-DEPOSITED SEMI-BRIGHT PURE SILVER
(0.5% MAX IMPURITIES) OVER NICKEL ANTI-TARNISH TREATMENT
EVERBRIGHT WS
THICKNESS: 1.9 - 3.3 MICROMETERS
 - BLADES MUST CONFORM TO ES-40000-5007, EXCEPT FOR SPECULAR REFLECTIVITY - SECTION 6.0
 - ANY PROCESS LUBRICANT REMAINING ON THE TERMINAL MUST NOT VARNISH OR DEGRADE IT'S ELECTRICAL PERFORMANCE UP TO A MAXIMUM CLASS AMBIENT TEMPERATURE PER SAE USCAR-2 FOR 1008 HOURS, PROCESS LUBRICANTS SHOULD BE APPROVED BY THE RESPONSIBLE ENGINEER
 - INFORMATION FOR BLADE DESIGN WAS DEVELOPED FROM EWCAP DWG: EWCAP-001
- GEOMETRY:
 - THIS IS A 100% CAD GENERATED PART. THE CAD MATHEMATICAL DATA IS THE MASTER FOR THIS PART. FOR DIMENSIONAL OR ANY INFORMATION NOT SHOWN ON THIS DRAWING, ANALYZE THE CAD MODEL.
 - GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994
 - GENERAL TOLERANCES: SEE TITLE BLOCK
 - EDGES AND UNDIMENSIONED DETAILS PER ISO13715
- MANUFACTURING:
 - DRAFT TO BE WITHIN TOLERANCE.
PLUS DRAFT - INDICATES A DIMENSION REPRESENTS THE SMALLEST SIZE OF A FEATURE. DRAFT WILL ADD MATERIAL.
MINUS DRAFT - INDICATES A DIMENSION REPRESENTS THE LARGEST SIZE OF A FEATURE. DRAFT WILL REMOVE MATERIAL.
 - ALLOWABLE FLASH MAX 0.20 HIGH BY MAX 0.13 THICK.
 - ALLOWABLE SPLIT/PARTING LINE MISMATCH 0.2 MAX.
 - VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B)
 - NO EXTERNAL MOLD RELEASE AGENT ALLOWED DURING MANUFACTURING
 - NO PARTING LINES, NO DRAFT, MISMATCHES OR EJECTOR MARKS PERMISSIBLE WITHIN SEALING SURFACE. SEALING SURFACE TOOLING TO BE PROCESSED

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
= 0		DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: EC NO: 171650 DRWN: DDEB 2018/01/19 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/05/14 APPR: VKOSHY 2014/06/27 THIRD ANGLE PROJECTION DRAWING A1-SIZE SERIES 33472				molex MX150 RCPT DUAL ROW SEALED ASSEMBLY MAT SEAL					
= 0		GENERAL TOLERANCES (UNLESS SPECIFIED)													
= 0		ANGULAR TOL ± 1.0 °													
= 0		4 PLACES ±													
= 0		3 PLACES ±													
= 0		2 PLACES ± 0.1				PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-33472-0001 DOC TYPE PSD DOC PART 001 REVISION C2									
= 0		1 PLACE ± 0.2													
= 0		0 PLACES ±				MATERIAL NUMBER CUSTOMER SHEET NUMBER GENERAL MARKET 11 OF 11									
= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													

150-S-020-2-D02	D	STONE GRAY
150-S-020-2-C02	C	DK GRAY
150-S-020-2-B02	B	LT GRAY
150-S-020-2-A02	A	BLACK

P/N	OPTION	MATING CONNECTOR COLOR

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:25
-----------------	----	--------------	------------	----------

TABLE OF CONTENTS

SHEET NO.	SHEET DESCRIPTION
1	NOTES AND BOM
2	CONFIGURATIONS
3-4	KEY CONFIGURATIONS
5	BLADE SEALED ASSEMBLY
6	SYSTEM PACKAGING
7	BACKSHELL NOTES
8	BACKSHELL
9	BACKSHELL CONFIGURATIONS

2X2

2X3

2X4

2X6

2X8

2X10

INSPECTION NUMBER LOG

LAST NUMBER: 9	
ADDED:	
REMOVED:	

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:	molex				
= 0	DIMENSION UNITS	SCALE	EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				
= 0	mm	1.5:1					
= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)						
= 0	ANGULAR TOL ± 1.0 °						
= 0	4 PLACES ±						
= 0	3 PLACES ±	THIRD ANGLE PROJECTION 					
= 0	2 PLACES ± 0.1						
= 0	1 PLACE ± 0.2						
= 0	0 PLACES ±						
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
= 0			A1-SIZE	33482		GENERAL MARKET	1 OF 11

NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

a. APPLICATION SPECIFICATION SEE: AS-33472-100

-CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, CONNECTOR ASSEMBLY, PACKAGING INFORMATION, CONNECTOR MATING, SERVICE INSTRUCTIONS, ELECTRICAL CONTINUITY CHECKING, CRIMPING, AND TROUBLESHOOTING.

-DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY AS SPECIFIED IN THE MATING CONNECTOR DRAWINGS CHART.

*DENOTES DRAWINGS THAT CAN BE ACCESSED AT <http://ewcap.uscarteams.org/>.

-ASSEMBLY SHIPPED WITH PLR IN PRE-LOCK POSITION (SEE PLR PRE-LOCK VIEW SHEET 5).

b. PRODUCT SPECIFICATION SEE:

-STANDARD CONFIGURATION: PS-33472-000

-UL V0 CONFIGURATION: TBD

CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, RATINGS (CURRENT, TEMPERATURE, SEALING, AND FLAMMABILITY), TERMINALS, WIRE DIAMETER RANGE, PRODUCT VALIDATION, AND PRODUCT DEVIATIONS.

c. PACKAGING SPECIFICATION PER MOLEX DRAWING: PK-31300-635

d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300

e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)

2. DESIGN - MATERIALS:

a. FOR BILL OF MATERIALS SEE:

-STANDARD CONFIGURATION: SD-33482-0002

-UL V0 CONFIGURATION: SD-160084-0002

3. DESIGN - GEOMETRY:

a. THE 3-D CAD DATA IS BASIC (WITHOUT TOLERANCE) AND MASTER FOR THIS PART WITH THE EXCEPTION OF UNDERLINED DIMENSIONS. DIMENSIONAL INFORMATION NOT SHOWN ON THIS DRAWING IS DEFINED BY THE DATA FILE AT ITS LATEST REVISION.

b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M-2009

c. EDGES AND UNDIMENSIONED DETAILS PER ISO13715

d. CORNERS SHOWN AS SHARP TO BE R 0.2 MAX.

e. LETTERING SHALL BE 0.15 MAX RAISED IN 0.25 MAX RECESS PAD. THIS INCLUDES RECYCLING CODE, CAVITY ID, VENDOR IDENTIFICATION, AND CUSTOMER MATERIAL NUMBER.

f. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B).

g. LASER MARKING:

1. PART NUMBER

2. DAY OF THE YEAR

3. SHIFT

4. YEAR

FOR ADDITIONAL INFORMATION SEE SECTION 5 UNDER PROCEDURES IN ES-34735-008.

MATING CONNECTOR DRAWINGS

DESCRIPTION	MOLEX INLINE
2X2	SD-33472-0001
2X3	SD-33472-0001
2X4	SD-33472-0001
2X6	SD-33472-0001
2X8	SD-33472-0001
2X10	SD-33472-0001










DOCUMENT STATUS


P1

RELEASE DATE

2018/02/16 22:02:26









SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	
DOCUMENT STATUS	P1	RELEASE DATE
		2018/02/16 22:02:26




UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																											
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex																		
	mm		1.5:1																									
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16										MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL													
 = 0																												
 = 0	ANGULAR TOL		± 1.0 °		PRODUCT CUSTOMER DRAWING																							
 = 0	4 PLACES		±												INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14													
 = 0	3 PLACES		±		DOCUMENT NUMBER																				DOC TYPE	DOC PART	REVISION	
 = 0	2 PLACES		± 0.1																						SD-33482-0001			
 = 0	1 PLACE		± 0.2																									
= 0	0 PLACES		±		THIRD ANGLE PROJECTION					DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER										
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									A1-SIZE		33482		GENERAL MARKET		2 OF 11												
= 0																												

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



APPENDIX




100




KEY D


2X10




KEY A



KEY B



KEY C










KGY 1

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		3:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
ANGULAR TOL ± 1.0°											
4 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER SD-33482-0001		DOC TYPE PSD	DOC PART 001	REVISION E2	
3 PLACES ±											
2 PLACES ± 0.1		THIRD ANGLE PROJECTION 				MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 4 OF 11	
1 PLACE ± 0.2											
0 PLACES ±		DRAWING A1-SIZE		SERIES 33482							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05




PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN FINAL-LOCK POSITION



SECTION V-V

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		DIMENSION UNITS		SCALE		CURRENT REV DESC:											
 = 0		mm		3:1		molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL											
 = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)										PRODUCT CUSTOMER DRAWING					
 = 0																	
 = 0																	
 = 0																	
 = 0		ANGULAR TOL ± 1.0 °		EC NO: 171650													
 = 0		4 PLACES ±		DRWN: PMANJUNATHAC 2018/01/03													
 = 0		3 PLACES ±		CHK'D: MVANSLAMBROU 2018/02/16													
 = 0		2 PLACES ± 0.1		APPR: MVANSLAMBROU 2018/02/16													
 = 0		1 PLACE ± 0.2		INITIAL REVISION:													
= 0		0 PLACES ±		DRWN: APROFFITT 2014/04/28													
= 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				APPR: VKOSHY 2014/05/14											
= 0						THIRD ANGLE PROJECTION											
= 0				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
= 0				A1-SIZE		33482				GENERAL MARKET		5 OF 11					

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
SYSTEM PACKAGING

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
</										

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX


CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20




90° ADAPTOR

BLADE SEALED ASSEMBLY






BACKSHELL (BKS)

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL										
	mm		1.5:1															
	GENERAL TOLERANCES (UNLESS SPECIFIED)							PRODUCT CUSTOMER DRAWING										
	ANGULAR TOL ± 1.0 °																	
	4 PLACES		±								DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
	3 PLACES		±															
	2 PLACES		± 0.1								SD-33482-0001		PSD		001		E2	
	1 PLACE		± 0.2															
	0 PLACES		±								MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																	
THIRD ANGLE PROJECTION		DRAWING		SERIES		GENERAL MARKET		7 OF 11										
		A1-SIZE		33482														

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------


SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




SECTION A-A





SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL								
	mm		3.5:1													
	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	ANGULAR TOL ± 1.0 °															
		4 PLACES		±		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			PRODUCT CUSTOMER DRAWING							
		3 PLACES		±												
		2 PLACES		± 0.1												
		1 PLACE		± 0.2												
		0 PLACES		±		DOCUMENT NUMBER SD-33482-0001			DOC TYPE PSD	DOC PART 001	REVISION E2					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 				DRAWING A1-SIZE		SERIES 33482		MATERIAL NUMBER GENERAL MARKET		CUSTOMER GENERAL MARKET	





SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex					
	= 0	mm		2:1		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14						MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	= 0	ANGULAR TOL ± 1.0 °										PRODUCT CUSTOMER DRAWING					
	= 0	4 PLACES ±														DOCUMENT NUMBER	
	= 0	3 PLACES ±										SD-33482-0001		PSD		001	E2
	= 0	2 PLACES ± 0.1				THIRD ANGLE PROJECTION 		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
	= 0	1 PLACE ± 0.2						GENERAL MARKET		10 OF 11							
	= 0	0 PLACES ±															
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															


MOLEX BACKSHELL CONFIGURATIONS

CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL

(ØDIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL

(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL

(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL

(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE



ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED





(ØDIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
= 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC: GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03CHK'D: MVANSLAMBROU 2018/02/16APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28APPR: VKOSHY 2014/05/14											
		mm		1:1													
		4 PLACES		±													
		3 PLACES		±													
		2 PLACES		± 0.1													
		1 PLACE		± 0.2													
		0 PLACES		±													
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								A1-SIZE		33482				GENERAL MARKET		11 OF 11	


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL DETAIL	


CHARTED DIMENSION						
PART NUMBER	DIMENSIONS					
	A	B	C	D	E	F
2X3, WITH RIB	56.00	13.20	9.80	3.90	0.65	2.70
2X3, WITHOUT RIB	56.00	13.20	N/A	N/A	N/A	N/A
2X4, WITH RIB	TBD	TBD	TBD	TBD	TBD	TBD
2X4, WITHOUT RIB	TBD	TBD	TBD	TBD	TBD	TBD
2X6, WITH RIB	56.00	17.70	13.6	4.2	0.83	3.10
2X6, WITHOUT RIB	56.00	17.70	N/A	N/A	N/A	N/A



PARTIAL SECTION A-A
SCALE 5:1
WITH RIBS




PARTIAL SECTION B-B
SCALE 5:1
WITHOUT RIBS




QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FA = 0 FE = 0 FD = 0 FT = 0 FC = 0 FX = 0 FM = 0 FT = 0	EC NO: 638031 DRWN: PPALLAN CHKD: MYANSLAMBROU REV/ APPR: MYANSLAMBROU	2020/05/20 2020/05/22 2020/05/22	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® MX150 DUAL ROW BLADE BACKSHELLS PRODUCT CUSTOMER DRAWING									
					mm		2:1											
			ANGULAR TOL ± 3.0 °		DRWN BY		DATE		SERIES 34950									
			4 PLACES ±		DAHALL		2013/03/19											
			3 PLACES ±		CHK'D BY		DATE		DOCUMENT NUMBER SD-34950-0001									
			2 PLACES ± 0.1		APPR BY		DATE											
			1 PLACE ± 0.2		VKOSHY		2013/04/08						DOC TYPE PSD		DOC PART 001		SHEET NUMBER 3 OF 4	
			0 PLACES ±		DRAWING SIZE		THIRD ANGLE PROJECTION						GENERAL MARKET					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A1													
					B11		REV											







SHEET DESCRIPTION	
MOLEX BACKSHELL DETAIL	




98 99
DIM. R ±0.15
ALL AROUND



CHARTED DIMENSION							
DESCRIPTION	DIMENSION						
	H	J	K	L	M	S	R
2X4, WITH RIB	53.56	16.10	0.80	N/A	N/A	16.10	1.35
2X4, WITHOUT RIB	53.56	16.10	N/A	3.60	5.10	16.10	N/A
2X8, WITH RIB	62.01	19.30	0.80	N/A	N/A	19.30	1.45
2X8, WITHOUT RIB	62.01	19.30	N/A	3.60	5.10	19.30	N/A
2X10, WITH RIB	62.01	19.30	0.80	N/A	N/A	19.30	1.45
2X10, WITHOUT RIB	62.01	19.30	N/A	3.60	5.10	19.30	N/A



PARTIAL SECTION C-C
SCALE 5:1
WITH RIBS



PARTIAL SECTION D-D
SCALE 5:1
WITHOUT RIBS


QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
FA F E ▼ C ☒ ■ ✓	2020/05/20 2020/05/22 2020/05/22 EC NO: 638031 DRWN: PPALLAN CHKD: MYANSLAMBROU APPR: MYANSLAMBROU REV: B11	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® MX150 DUAL ROW BLADE BACKSHELLS PRODUCT CUSTOMER DRAWING							
		ANGULAR TOL ± 3.0 °		mm		2:1									
		4 PLACES ±		DRWN BY		DATE									
		3 PLACES ±		DAHALL		2013/03/19		SERIES 34950 DOCUMENT NUMBER SD-34950-0001				MATERIAL NUMBER		CUSTOMER GENERAL MARKET	
		2 PLACES ± 0.1		CHK'D BY		DATE									
		1 PLACE ± 0.2		APPR BY		DATE									
		0 PLACES ±		VKOSHY		2013/04/08									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION									
		A1													

TABLE OF CONTENTS	
SHEET NO.	SHEET DESCRIPTION
1	NOTES AND BOM
2	CONFIGURATIONS
3	SCHLEMMER BACKSHELL DETAIL
4	MOLEX BACKSHELL DETAIL

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:
- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY AS SPECIFIED IN SD-33472-0001.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY
- b. MOLEX PRODUCT SPECIFICATION SEE: TBD
- BACKSHELL DESIGN IS OWNED BY MOLEX.
- c. OUTSOURCED MFG PRODUCT SPECIFICATION
- BACKSHELL DESIGN IS OWNED BY SCHLEMMER.
 - THESE PRODUCTS ARE ONE TIME USE ONLY.
 - REMOVAL FORCE OF THE BACKSHELL FROM THE MOLEX CONNECTOR TO BE 100N MIN.
 - REMOVAL FORCE OF SLIT CONVOLUTE FROM THE WITH RIB OPTION BACKSHELLS TO BE 100N MIN.
 - REMOVAL FORCE OF UNSLIT CONVOLUTE FROM THE WITH RIB OPTION BACKSHELLS TO BE 100N MIN.
- d. PACKAGING SPECIFICATION: SEE BOM
- e. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300
- f. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)
- g. FOLLOWING PRODUCTION CODES TO BE PRESENT
- DATE CODE
 - MOLD CAVITY CODE
 - MOLEX LOGO
 - RECYCLE CODE
 - SUPPLIER PART NUMBER - SCHLEMMER PARTS ONLY
- h. CONNECTOR MUST HAVE CLIPSLOT FEATURE FOR USE WITH MOLEX BACKSHELLS



2. DESIGN - MATERIALS:

- a. PA66 0% GLASS FILLED
- b. BLACK



3. DESIGN GEOMETRY:

- a. THIS IS A 100% CAD GENERATED PART. THE CAD MATHEMATICAL DATA IS THE MASTER FOR THIS PART. FOR DIMENSIONAL OR ANY INFORMATION NOT SHOWN ON THIS DRAWING, ANALYZE THE CAD MODEL.
- b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 2009.
- c. CORNERS SHOWN AS SHARP TO BE R 0.1.
- d. VISUAL DEFECTS SHALL MEET COSMETEIC STANDARD PS-45499-002 (CLASS C).
- e. ALLOWABLE FLASH, PARTING LINES MISMATCH, EJECTOR PINS MARK, AND GATE VESTIGE TO BE +0.30 MAX PROTUSION.



BILL OF MATERIALS (BOM)								
DESCRIPTION	PART NUMBER	CIRCUIT SIZE	COLOR	RIBS	CONVOLUTE SIZE	PACKAGING DRAWING NUMBER	STATUS	MANUFACTURER
2X3, WITH RIB	34951-0610	2X3	BLACK	YES	9 mm DELPHI	PK-31302-118	SALEABLE	OUTSOURCED MFG
2X3, WITHOUT RIB	34951-0620	2X3	BLACK	NO	9 mm DELPHI	PK-31302-118	SALEABLE	OUTSOURCED MFG
2X4, WITH RIB	34951-0811	2X4	BLACK	YES	NW 12 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX
2X4, WITHOUT RIB	34951-0821	2X4	BLACK	NO	NW 12 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX
2X6, WITH RIB	34951-1210	2X6	BLACK	YES	13 mm DELPHI	PK-31302-118	SALEABLE	OUTSOURCED MFG
2X6, WITHOUT RIB	34951-1220	2X6	BLACK	NO	13 mm DELPHI	PK-31302-118	SALEABLE	OUTSOURCED MFG
2X8, WITH RIB	34951-1611	2X8	BLACK	YES	NW 16 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX
2X8, WITHOUT RIB	34951-1621	2X8	BLACK	NO	NW 16 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX
2X10, WITH RIB	34951-2011	2X10	BLACK	YES	NW 16 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX
2X10, WITHOUT RIB	34951-2021	2X10	BLACK	NO	NW 16 SCHLEMMER	349509000 PDD	SALEABLE	MOLEX





2X3 RECEPTACLE





2X4 RECEPTACLE



2X6 RECEPTACLE




2X8 RECEPTACLE




2X10 RECEPTACLE

B10	ADDED BALLOON NUMBER TO PAGE 3 -SCHLEMMER PAGE
B9	CHANGED PARTS STATUS TO SALEABLE
B8	ADDED BALLOON NO. 90
B7	UPDATED BALLON NUMBERS
B6	UPDATED RIB AND WEDGE FEATURES
B3	UPDATED TOLERANCES
B2	ADDED BALLOONS & UPDATED BOM
B1	ADDED MOLEX PART NUMBERS
B	MIGRATION
A6	UPDATED BILL OF MATERIALS
A5	UPDATED STATUS COLUMN
A4	MINOR NOMENCLATURE CLEAN UP
A3	UPDATED VIEWSET & NOTES
A2	UPDATED REFERENCE DRAWINGS
A1	UPDATED NOTES
A	INITIAL RELEASE
REV	REV DESCRIPTION








INSPECTION NUMBER LOG	
LAST NUMBER: 1 - 5	
ADDED: 40 42 44 46 48 49 89 90	
50 67	
REMOVED: 40 44	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
EC NO: 632862 DRWN: PPALLAN CHKD: MYANSLAMBROU APPR: MYANSLAMBROU	2020/02/20 2020/02/26 2020/02/26	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®							
					mm		1:1									
		ANGULAR TOL ± 3.0 °			DAHALL		2013/03/27									
		4 PLACES ±			CHK'D BY		DATE		MX150 DUAL ROW RECPT BACKSHELLS							
		3 PLACES ±														
		2 PLACES ± 0.1			APPR BY		DATE		PRODUCT CUSTOMER DRAWING							
		1 PLACE ± 0.2			VKOSHY		2013/04/08									
		0 PLACES ±			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER			CUSTOMER		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A1				34951					GENERAL MARKET		
		B10		REV						DOCUMENT NUMBER			DOC TYPE		DOC PART	
								SD-34951-0001			PSD		001		1 OF 4	




SHEET DESCRIPTION	
SCHLEMMER BACKSHELL DETAIL	

CHARTED DIMENSION						
DESCRIPTION	DIMENSIONS					
	A	B	C	D	E	F
2X3, WITH RIB	50.00	13.20	9.75	3.93	0.65	2.74
2X3, WITHOUT RIB	50.00	13.20	N/A	N/A	N/A	N/A
2X4, WITH RIB	TBD	TBD	TBD	TBD	TBD	TBD
2X4, WITHOUT RIB	TBD	TBD	TBD	TBD	TBD	TBD
2X6, WITH RIB	50.00	17.70	13.60	3.50	0.83	3.10
2X6, WITHOUT RIB	50.00	17.70	N/A	N/A	N/A	N/A





PARTIAL SECTION A-A
SCALE 5:1
WITH RIBS






PARTIAL SECTION B-B
SCALE 5:1
WITHOUT RIBS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
EC NO: 632862 DRWN: PPALLAN CHKD: MYANSLAMBROU APPR: MYANSLAMBROU	2020/02/20 2020/02/26 2020/02/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
				mm		3:1							
		ANGULAR TOL ± 3.0 °		DRWN BY		DATE		MX150 DUAL ROW RECPT BACKSHELLS					
				DAHALL		2013/03/27							
		4 PLACES ±		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
		3 PLACES ±											
		2 PLACES ± 0.1		APPR BY		DATE							
		1 PLACE ± 0.2		VKOSHY		2013/04/08							
		0 PLACES ±		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A1				34951				GENERAL MARKET			
B10	REV					DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
						SD-34951-0001		PSD		001		3 OF 4	


SHEET DESCRIPTION	
MOLEX BACKSHELL DETAIL	



SECTION E-E




PARTIAL SECTION C-C
SCALE 5:1
WITH RIBS



PARTIAL SECTION D-D
SCALE 5:1
WITHOUT RIBS

DESCRIPTION	CHARTED DIMENSION							
	DIMENSIONS							
	V	H	J	K	L	M	N	Z
2X4, WITH RIB	16.10	36.80	48.11	16.10	0.80	N/A	N/A	1.35
2X4, WITHOUT RIB	16.10	36.80	48.11	16.10	N/A	3.60	5.10	N/A
2X8, WITH RIB	19.30	45.60	56.91	19.30	0.80	N/A	N/A	1.45
2X8, WITHOUT RIB	19.30	45.60	56.91	19.30	N/A	3.60	5.10	N/A
2X10, WITH RIB	19.30	45.60	56.91	19.30	0.80	N/A	N/A	1.45
2X10, WITHOUT RIB	19.30	45.60	56.91	19.30	N/A	3.60	5.10	N/A



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
EC NO: 632862 DRWN: PPALLAN CHKD: MYANSLAMBROU APPR: MYANSLAMBROU	2020/02/20 2020/02/26 2020/02/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex MX150 DUAL ROW RECPT BACKSHELLS			
		ANGULAR TOL ± 3.0 °		mm	2:1				
		4 PLACES ±		DRWN BY	DATE				
		3 PLACES ±		DAHALL	2013/03/27				
		2 PLACES ± 0.1		CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING			
		1 PLACE ± 0.2		APPR BY	DATE	SERIES MATERIAL NUMBER CUSTOMER			
		0 PLACES ±		VKOSHY	2013/04/08	34951			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER			
B10	REV			A1		SD-34951-0001 PSD 001 4 OF 4			