



| P | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|---|-----|---------------|-----------|-----|------|
|   | A   | ECR-18-008642 | 05JUN2018 | TD  | TD   |
|   | A1  | ECN-21-101658 | 30MAR2021 | GTG | PK   |
|   |     |               |           |     |      |
|   |     |               |           |     |      |





SCALE 1:1 NOTES:

1. NO DAMAGE, SINK MARKS, CAVITIES OR FLOW LINES PERMITTED.
- 2 MATERIAL:  
SEAL: 30 DUROMETER INHERENTLY LUBRICATED SILICONE  
HOUSING: PA66 35% GF
- 3 MATERIAL:  
SEAL: 30 DUROMETER INHERENTLY LUBRICATED SILICONE HIGHER TEAR STRENGTH.  
HOUSING: PA66 35% GF
- 4 THIS AREA MUST BE KEPT FREE OF SCRATCHES,BURRS,AND OTHER DEFECTS.
- 5 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
- 6 THIS PART HAS NOT COMPLETED VALIDATION TESTING.



SECTION B - B



|   |   |            |               |      |       |       |             |             |
|---|---|------------|---------------|------|-------|-------|-------------|-------------|
| 6 | 3 | GREY       | DARK BLUE     | 9.60 | 10.20 | 10.50 | SIZE D      | I-2840876-4 |
|   | 2 | YELLOW     | DARK BLUE     | 9.60 | 10.20 | 10.50 | SIZE D      | 2840876-4   |
| 5 | 3 | RED        | BLACK         | 9.00 | 9.60  | 9.90  | SIZE C      | I-2840876-3 |
| 5 | 2 | BLUE       | BLACK         | 9.00 | 9.60  | 9.90  | SIZE C      | 2840876-3   |
|   | 3 | PURPLE     | ORANGE        | 8.00 | 8.60  | 8.90  | SIZE B      | I-2840876-2 |
|   | 2 | RUST RED   | ORANGE        | 8.00 | 8.60  | 8.90  | SIZE B      | 2840876-2   |
|   | 3 | LT. BLUE   | DARK GREY     | 5.40 | 6.10  | 6.30  | SIZE A      | I-2840876-1 |
|   | 2 | GREEN      | DARK GREY     | 5.40 | 6.10  | 6.30  | SIZE A      | 2840876-1   |
|   |   | SEAL COLOR | PLASTIC COLOR | MIN  | MAX   | E     | DESCRIPTION | PART NO     |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T. DEWITTE 05SEP2017  
CHK T. DEWITTE 05SEP2017  
APVD T. DEWITTE 05SEP2017



CABLE SEAL, OVERMOLDED, PCON12

| DIMENSIONS: | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                    |
|-------------|---------------------------------------------------------------------------|
| mm          |                                                                           |
|             | 0 PLC ±<br>1 PLC ±0.15<br>2 PLC ±0.25<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±2° |
| MATERIAL    | FINISH                                                                    |
| 2 3         | -                                                                         |

PRODUCT SPEC -  
APPLICATION SPEC -  
WEIGHT -

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|------|-----------|------------|---------------|
| A3   | -         | C-2840876  |               |

CUSTOMER DRAWING SCALE 2:1 SHEET 1 OF 1 REV A1