




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	NEW PROPOSAL	DEC07/22	KELVIN




FRONT VIEW




SIDE VIEW



BOTTOM VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED P.C.B LAYOUT
(TOLERANCE: ±0.05[±0.002])
(COMPONENT SIDE OF PC BOARD)

NOTES:





- MATERIALS:**
CONTACTS: PHOSPHOR BRONZE, 0.35MM THICKNESS, PLATING: GOLD FLASH PLATING ON MATING SURFACE, 50μ "[1.27 MICRONS] MIN. NICKEL OVERALL. GOLD FLASH ON PCB TAILS
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, FLAMMABILITY RATING UL 94V-0 COLOR - BLACK.
HOLD DOWN BRACKET: COPPER ALLOY WITH TIN PLATED.
 - COPLANARITY SPECIFICATION:**
 ALL SOLDER TAILS ARE COPLANAR WITHIN 0.10[0.004].
 - RECOMMENDED SOLDERING TEMPERATURE:**
 REFLOW SOLDERING PEAKED AT 260°C FOR 10 SECONDS MAXIMUM.
- AMPHENOL PART NUMBER: RJLSE-40881-01T

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN RONNIE.C	DEC07/22
PRIMARY UNITS MILLIMETERS	CHECKED KELVIN.T	DEC07/22
SECONDARY INCHES	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APP'D	
1 DECIMAL PLACE ±0.30	ENG. REL. NO.	
2 DECIMAL PLACES ±0.20	REF.	
3 DECIMAL PLACES ±0.13	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
ANGULAR DEGREES ±2.0°		

Amphenol Canada Corp. Commercial Products	
SINGLE PORT, SURFACE MOUNT MODULAR JACK, 8 POSITION, 8 CONTACTS, UNSHIELD, WITH HOLD DOWN BRACKET T&R PACKAGE—RoHS COMPLIANT	
DWG NO.	P-RJLSE-40881-01T
CODE ID NO. 03554	DWG SIZE X SCALE N/A SHEET 1 OF 2

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	NEW PROPOSAL	DEC07/22	KELVIN



PACKAGING NOTES:

1. A FULLY LOADED REEL SHOULD CONTAIN 110 PCS OF CONNECTORS.
2. A FULLY LOADED CARTON SHOULD CONTAIN 6 REELS (660 PCS) OF CONNECTORS.



UNLESS SPECIFIED OTHERWISE	DRAWN	RONNIE.C	DEC07/22
PRIMARY UNITS MILLIMETERS	CHECKED	KELVIN.T	DEC07/22
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APP'D		
1 DECIMAL PLACE ±0.30	ENG. REL. NO.		
2 DECIMAL PLACES ±0.20	REF.		
3 DECIMAL PLACES ±0.13	THIRD ANGLE PROJECTION		
ANGULAR DEGREES ±2.0°	DO NOT SCALE DRAWING		

Amphenol Canada Corp. Commercial Products			
SINGLE PORT, SURFACE MOUNT MODULAR JACK, 8 POSITION, 8 CONTACTS, UNSHIELDED, WITH HOLD DOWN BRACKET T&R PACKAGE—RoHS COMPLIANT			
DWG NO.	P-RJLSE-40881-01T		REV A
CODE ID NO. 03554	DWG SIZE X	SCALE N/A	SHEET 2 OF 2

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.