




NOTE 1 APPLICABLE WIRE
: AWG#24~30(INSULATION DIA 1.15 MAX).
2 CRIMPING CONDITION AS CRIMP HEIGHT IS
SPECIFIED INDIVIDUALLY DEPENDING ON
WIRE USED.

1	PHOSPHOR BRONZE	SILVER PLATING(N=10000)	2	CARTON	(REEL)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED
		H. Kawaguchi	H. Kishida		M. Ogasawara
		96.8.22	96.8.23		96.8.29
DRAWING NO. EDC3-021032		PART NO. RP19-SC-222			
SCALE 5:1		CODE NO. CL113-0266-2			
UNITS mm					

TO
R