





REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL DRAWING	MAR19/22	L.CHAN
B	ADD GOLD FLASH PLATING OPTION	DEC29/22	L.CHAN



RECOMMENDED PANEL CUTOUT



RECOMMENDED PCB LAYOUT.
(COMPONENT SIDE OF BOARD)



NOTES:

PLASTIC HOUSING: HIGH TEMP ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0,
COLOR:BLACK

CONTACTS: PHOSPHOR BRONZE
PLATING: REFER PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACES.
50 μ " [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 μ " [2.54 MICRONS]
MIN. MATTE-TIN OR GOLD FLASH ON
CONTACT TAILS.

RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING AT 260 °C MAXIMUM FOR 5-8 SEC.

PACKAGING: TRAY PACKAGING.

AMPHENOL PART NUMBER: RJE05-166-0X10-H

GOLD PLATING
1 = 6 μ "
2 = 15 μ "
3 = 30 μ "
4 = 50 μ "
5 = GOLD FLASH

UNLESS SPECIFIED OTHERWISE		DRAWN	MAR20/22	Amphenol Canada Corp. Commercial Products	
PRIMARY UNITS: MILLIMETERS		CHECKED	MAR20/22		
SECONDARY		M.E. APP'D			
REFERENCE IN PARENTHESES		Q.A. APP'D			
GENERAL TOLERANCES		DWG APPR.	MAR20/22	RJE05 SERIES, MODULAR JACK, 6P6C, UNSHIELD, ULTRA LOW PROFILE -RoHS COMPLIANT	
1 DECIMAL PLACE		ENG. REL. NO.			
2 DECIMAL PLACES		REF.			
3 DECIMAL PLACES		THIRD ANGLE PROJECTION			
ANGULAR DEGREES				P-RJE05-166-0X10-H	
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.		DO NOT SCALE DRAWING		CODE ID NO. 03554	REV B
				DWG SIZE: X	1 OF 1
				SCALE: 6:1	
				SHEET	