






211 M 0007

SCALE 10:1



211 M 0008



SCALE 10:1



AUTRES COTES IDEM 211 M 0007
OTHER DIMENSIONS AS 211 M 0007

211 M 0012

SCALE 10:1



AUTRES COTES IDEM 211 M 0007
OTHER DIMENSIONS AS 211 M 0007

NOTA :
DIAMETRE ISOLANT: POUR INFORMATION,
VOIR TABLEAU Ø DES FILS QUALIFIES SUR LES PLANS DES CONTACTS.
NOTE:
WIRE DIAMETER: FOR INFORMATION
SEE TABLE ON TERMINAL DRAWINGS FOR VALIDATED WIRES

				SANCTION REQUIREMENT
EFFORT D'INSERTION DES BOUCHONS PLUGS INSERTION FORCE				<0U>= 15 N
RESISTANCE MAXIMUM DES BOUCHONS A LA PRESSION PLUG MAXIMUM PRESSURE RESISTANCE				>0U>= 0.30 BAR
CAHIER DE MISE EN ŒUVRE CONNECTIQUE DES BOUCHONS D'ALVEOLE USER'S MANUAL CAVITIES PLUGS				PU 106

MVL		DELPHI		COULEUR COLOR	TAUX D'HUILE RATE OF OIL	DURETE Shore A: TOUGHNESS Shore A:	PRESSION D'ETANCHEITE SEALING PRESSURE (BAR)	DIAMETRE ISOLANT WIRE DIAMETER (mm)		MASSE WEIGHT (g)
REF.PIECE PART NUM	INDICE REVISION	REF.PIECE PART NUM	INDICE REVISION					MIN	MAX	
211 M 0007	E	10736278	01	JAUNE YELLOW	2% ± 0.10%	54 ± 4	0.3	(1.25)	(1.90)	0.061
211 M 0008	E	10736279	01	VERT GREEN	2% ± 0.10%	54 ± 4	0.3	(1.75)	(3.00)	0.058
211 M 0012	F	10787316	01	BLANC WHITE	2%	51 ± 4	0.3	BOUCHON PLUG		0.075

DWG STATUS				ZONE	REVISION HISTORY		AUTH	DR	AP'D 1	AP'D 2
DATE	STG	REV	N/P							
30JUL14	R	01	-	-	FILE TRANSLATED FROM MVL SYSTEM. SEE REV "X" FOR PREVIOUS CHANGE				DGL	DGL
30JUL14	R	02	-	-	FILE TRANSLATED FROM MVL SYSTEM. SEE REV "X" FOR PREVIOUS CHANGE				DGL	DGL
20AUG15	R	03	-	-	REPAIR IN MVL. DIMENSION 12 ADDED. STARLIN P/N COLUMN REMOVED			V.RAN	P.MEN	P.MEN

DWG TIP
CUSTOMER PART DRAWING

WEIGHT (LBI)
SEE TABLE

VOLUME (LBI)
ROUTING

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
±0.1
±0.2

GD&T
ACCORDING TO:

REFERENCE
MVL DWG 211FT0433

FIRST ANGLE PROJECTION

DO NOT
SCALE

USE MATH
DATA

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH

COPYRIGHT 2013 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.
REVISED 2014

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CAD DATA,
AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIETE DE DELPHI CORPORATION ET CONTIENT DES
INFORMATION PROPRIETAIRES (P.C.) A REPRODUCTION, LA DISTRIBUTION
ET UTILISATION DE CE DOCUMENT OU DE SES DONNEES HYDROLOGIQUES CAD,
AINS QUE LA COMMUNICATION DE TOUT CONTENU A AUTRUI SANS AUTORISATION
EXPRESSE EST INTERDITE.

DR	ISAMBERT	DATE	07MY02
AP'D1	F FAURIE		11MR13
AP'D2	S LACOTE		11MR13
AP'D3	PASCAL MENARD		14MR13
AP'D4			
AP'D5			

SUBSTANCES OF CONSENT AND RECYCLED CONTENT PER DELPHI 10949001
MATERIES PROPOSEES ET CONTENU RECYCLABLE SELON
DELPHI 10949001

MATERIAL
SILICONE

DRAWING NAME
SICMA 1.5 RANGE 1 & 2 SWS
SINGLE WIRE SEAL & PLUG

DRAWING NUMBER
10858315

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	10:1	1 OF 1	1 OF 1	1	03	-