


6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM						
A	5023800800	1.25 W/B Single Plg Hsg 8Ckt		1	PC						
B	5023810000	1.25 W/B Single Plg Term W/Plt		8	PC						
C	--	WHITE PART ID LABEL		1	PC						

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X26AWG DISC BK	BLACK
A2	--	1X26AWG DISC BK	BLACK
A3	--	1X26AWG DISC BK	BLACK
A4	--	1X26AWG DISC BK	BLACK
A5	--	1X26AWG DISC BK	BLACK
A6	--	1X26AWG DISC BK	BLACK
A7	--	1X26AWG DISC BK	BLACK
A8	--	1X26AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240921082	CLIK-Mate 1.25 R-S 8ckt 150mm disc Sn	150±5	15
2240921083	CLIK-Mate 1.25 R-S 8ckt 300mm disc Sn	300±5	15
2240921084	CLIK-Mate 1.25 R-S 8ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.65 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	C	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/05/05 16:46:44

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
$\frac{F}{A} = 0$	mm	NTS
$\frac{F}{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)	
$\frac{F}{P} = 0$	ANGULAR TOL ± °	
DIVISIONAL SYMBOLS	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
THIRD ANGLE PROJECTION		DRAWING
SERIES		MATERIAL NUMBER
CUSTOMER		SHEET NUMBER
CURRENT REV DESC:		DOCUMENT NUMBER
EC NO: 745876		DOC TYPE
DRWN: THANUB		DOC PART
CHK'D: RDOMZALS		REVISION
APPR: RDOMZALS		
INITIAL REVISION:		
DRWN: THANUB		
APPR: SKUMAR07		
A4-SIZE		
224092		
SEE TABLE		
GENERAL MARKET		
1 OF 1		