




DIMENSIONS:	
A	1.200" ±0.063
B	1.700" ±0.063
C	1.650" MAX.
D	1.320" ±0.031
G	#6-32 MTG. STUDS



NOTE: ALL LEADS 6.0" MIN. OUT.



ELECTRICAL DATA:			
TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 17.78V, 60Hz, BLK - WHT	0.5mA	Max.
Sec. N.L.V	@ 17.78V, 400Hz, BLK - WHT		
	BLU - RED =	18.15V	±2%
	@ 17.78V, 400Hz, BRN - ORG		
	GRY - YEL =	18.15V	±2%
DCR	@ 20°C, BLK - WHT =	2417 Ω	±20%
	@ 20°C, BRN - ORG =	2417 Ω	±20%
	@ 20°C, BLU - RED =	2017 Ω	±20%
	@ 20°C, GRY - YEL =	2017 Ω	±20%
HIPOT	PRIMARY - SECONDARY	250V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™			
0	RELEASED.	C.I. 12/09/15	ELECTRONIC DIVISION			
			52 RANKIN PLACE,			
			WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181			
			FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: AUDIO TRANSFORMER	DWG. NO. 850QA
			DATE: 12/09/15	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		