




1		2		3		4			
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
△				..	△				..




DETAIL OF MOUNTING GUIDE




MAIN GUIDE




PANEL CUTOUT
(PANEL THICKNESS 0.7 TO 2)




DIP LOCATION DIMENSION FROM CONNECTOR INTERFACE



MAIN GUIDE



M8 x 0.5




POST DIA (φ 0.55)

NOTE: ① THE RECOMMENDED TIGHTEN TORQUE OF REF.NO. ⑥: 1.5 N · m.
ADHESIVE LOCTITE 242, HENKEL JAPAN LOCTITE OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ⑥ FROM LOOSENING.

3	POLYAMIDE	(BLUE)	6	BRASS	NICKEL PLATED
2	STAINLESS STEEL		5	PHOSPHOR BRONZE	NICKEL PLATED
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	4	BRASS	OVERPLATING : GOLD 0.2μm min UNDERPLATING : NICKEL 2.0μm min
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	T.SUZUKI	Y. Yamashita	H. Gawa	M. Saito	
	06.07.22	06.07.22	06.07.22	06.07.22	

 SCALE 2 : 1 UNITS mm	DRAWING NO.	PART NO.
	EDC4-025293-73	HR10-7R-6PA(73)
 HRS HIROSE ELECTRIC CO., LTD.	CODE NO.	
	CL110-0061-0-73	1/1