




- Notes 1 Applicable crimp contact:
Contact No. 1,3 to 10 : RP17-PC-222/CL113-0508-0 (Applicable cable size : awg#24 to #28.
Cable jacket outer diameter shall be $\phi 1.2\text{mm}$ or less.)
Contact No. 2,11,12 : RP17-PC-212/CL113-0507-7 (Applicable cable size : awg#18 to #22.
Cable jacket outer diameter shall be $\phi 1.7\text{mm}$ or less.)
2 Applicable cable crimping tool : RP17-TC-01/CL150-0042-5
3 Extraction tool : RP6-SC-TP/CL150-0039-0
④ The tightening torque of Ref No. ③ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ③, use LOCTITE 243, HENKEL JAPAN or equivalent.
5 Shall be disassembled when delivered.
6 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure, please confirm before the use.

5	Brass					
4	Polycarbonate	(BLACK) UL94V-0	9	Brass		
3	Polycarbonate	(BLACK) UL94V-0	8	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4	
2	Stainless steel		7	Steel	Nickel plating	
1	Polycarbonate	(BLACK) UL94V-0	6	Polyvinylchloride	(BLACK)	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm		SCALE 2 : 1	COUNT ④ 2	DESCRIPTION OF REVISIONS DIS-C-00009784	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI
DATE 20220214		APPROVED : MO. SATOH		DRAWING NO. EDC-025906-71-71		
F		CHECKED : MO. SATOH		PART NO. RP17A-13P-12PC(71)		
		DESIGNED : EM. YUMINO		CODE NO. CL0113-0551-9-71		
		DRAWN : MM. ISHII				