



DIMENSIONS:

A	5.281" ±0.063
B	5.721" ±0.125
C	6.361" ±0.063
D	4.250" ±0.063
E	4.125" ±0.063
G	0.281" x 0.750" ±0.015



FOR 117V: CONNECT WHT & BRN TOGETHER AND BLK & BLU TOGETHER
 INPUT: WHT - BLK
 FOR 234V: CONNECT BLK & BRN TOGETHER
 INPUT: WHT - BLU

ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 117V, 60Hz, WHT - BLK	376mA	Max.
Sec. N.L.V	@ 117V, 60Hz, WHT - BLK		
	BRN - BLU =	117.0V	±2%
	RED - RED =	3086.5V	±2%
	RED - RED/YEL = RED/YEL - RED =	1543.2V	±2%
DCR	@ 20°C, WHT - BLK =	0.395 Ω	±20%
	@ 20°C, BRN - BLU =	0.435 Ω	±20%
	@ 20°C, RED - RED =	173.7 Ω	±20%
HIPOT	PRIMARY - SECONDARY	4500V, 60Hz, 1 SEC	

NOTE: ALL LEADS 9.0" LONG MIN. STRIP 0.5".

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	C.I. 09/17/18	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181 FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: PLATE TRANSFORMER	DWG. NO. 735A
			DATE: 09/17/18	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		