




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE PER ECN-21-103877	19MAY2021	DFS	JB





2356408-2
KEY B




2356408-3
KEY C



2356408-4
KEY D



ISOMETRIC VIEWS SHOWN FOR REFERENCE ONLY



NOTES:

1. MATERIALS:

HOUSING:
GENERIC TYPE = NYLON 35%GF
COLOR = (SEE TABLE)
SEAL:
GENERIC TYPE = SILICONE RUBBER
COLOR = BLACK
THREADED INSERTS:
GENERIC TYPE = BRASS

2. THIS PART MATES WITH 4 WAY PLUG 2338212-X.
SEE VIEWS ABOVE FOR KEY ARRANGEMENTS.

3. HEADER NOT SEALED IN THE UNMATED STATE.

4. NOT TOOLED FOR PRODUCTION


5. REFER TO AS16 COAX PRODUCT GROUP DRAWING:
2381263 FOR INFORMATION REGARDING MATING
COMPONENTS, ACCESSORIES, AND APPLICATION
TOOLING.

4	BEIGE	2356408-4
4	SIGNAL BLUE	2356408-3
4	CLARET VIOLET	2356408-2
	WATER BLUE	2356408-1
	HOUSING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LOCONDRO 29AUG2019	TE Connectivity	
DIMENSIONS: mm		CHK K. DEBOCK 29AUG2019		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. BARTH 13MAY2021	NAME 4P, COAX, HDR ASSY, 180DEG, SHORT AS16 COAX	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-94799 APPLICATION SPEC 114-94667 WEIGHT 14.3 g	SIZE A2	
MATERIAL 1		RESTRICTED CUSTOMER	CAGE CODE 00779	DRAWING NO C-2356408
		SCALE 2:1	SHEET 1 OF 3	REV A



P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

RECOMMENDED PRINTED CIRCUIT BOARD LAYOUT
SHOWN FROM CONNECTOR SIDE



ADDITIONAL NOTES REGARDING PANEL AND PCB FITMENT:






- 10 FLANGE CLEARANCE REGION ON SEALED SIDE OF ENCLOSURE, NECESSARY FOR PROPER ASSEMBLY AND SEALING.
- 11 SEALING SURFACE WITHIN CLEARANCE REGION, NO BURRS, SCRATCHES OR TOOL MARKS ALLOWED.
- 12 SURFACE ROUGHNESS APPLIES WITHIN CLEARANCE REGION.
- 13 X_BASIC AND Y_BASIC TO BE DEFINED BY CUSTOMER.
- 14 REMOVE SHARP EDGES. R0.3MM MAX
- 15 MINIMUM PANEL THICKNESS WILL DEPEND UPON THE STRENGTH OF THE PANEL MATERIAL.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29 AUG 2019 CHK J. LOCONDRO K. DEBOCK 29 AUG 2019		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD J. BARTH 13 MAY 2021 PRODUCT SPEC 108-94799 APPLICATION SPEC 114-94667	
		WEIGHT 14.3 g		NAME 4P, COAX, HDR ASSY, 180DEG, SHORT AS16 COAX SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-2356408	
MATERIAL - -		RESTRICTED CUSTOMER		SCALE 2:1 SHEET 2 OF 3 REV A	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



KEYWAY CLEARANCE DETAIL
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LOCONDRO 29AUG2019	TE Connectivity		
DIMENSIONS: mm		CHK K. DEBOCK 29AUG2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. BARTH 13MAY2021	NAME 4P, COAX, HDR ASSY, 180DEG, SHORT AS16 COAX		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-94799 APPLICATION SPEC 114-94667 WEIGHT 14.3 g	SIZE A2	CAGE CODE 00779	DRAWING NO C-2356408
MATERIAL -		RESTRICTED CUSTOMER		SCALE 2:1	SHEET 3 OF 3
				REV A	