




4

3

2

REV. A

SHEET 2 OF 3

CF-020400-56X

DOCUMENT NO. CF-020400-56X

SHEET 2 OF 3

REV. A

DETAIL A

OCTONET PIN POSITION

SCALE 8.000

PIN CONTACT
OCTONET
21-032906-001
OR EQUIVALENT
4 PLACES

PIN CONTACT
SIZE 22D
10-497628-225
OR EQUIVALENT
14 PLACES

MAIN KEYWAY

10

DETAIL B

J3 CONNECTOR

SCALE 3.000

SEE SHEET 3

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Dec. 21 2022, 12:49:12 PM

DOCUMENT NO. CF-020400-56X

SHEET 2 OF 3

REV. A

J1 CONNECTOR

ID	DESCRIPTION
B-1	CH1_A_1GBASE-T_P
B-2	CH1_A_1GBASE-T_N
B-3	CH1_B_1GBASE-T_P
B-4	CH1_B_1GBASE-T_N
B-5	CH1_C_1GBASE-T_P
B-6	CH1_C_1GBASE-T_N
B-7	CH1_D_1GBASE-T_P
B-8	CH1_D_1GBASE-T_N
B-GND	GND
F-1	CH2_A_1GBASE-T_P
F-2	CH2_A_1GBASE-T_N
F-3	CH2_B_1GBASE-T_P
F-4	CH2_B_1GBASE-T_N
F-5	CH2_C_1GBASE-T_P
F-6	CH2_C_1GBASE-T_N
F-7	CH2_D_1GBASE-T_P
F-8	CH2_D_1GBASE-T_N
F-GND	GND
K-1	CH3_A_1GBASE-T_P
K-2	CH3_A_1GBASE-T_N
K-3	CH3_B_1GBASE-T_P
K-4	CH3_B_1GBASE-T_N
K-5	CH3_C_1GBASE-T_P
K-6	CH3_C_1GBASE-T_N
K-7	CH3_D_1GBASE-T_P
K-8	CH3_D_1GBASE-T_N
K-GND	GND
P-1	CH4_A_1GBASE-T_P
P-2	CH4_A_1GBASE-T_N
P-3	CH4_B_1GBASE-T_P
P-4	CH4_B_1GBASE-T_N
P-5	CH4_C_1GBASE-T_P
P-6	CH4_C_1GBASE-T_N
P-7	CH4_D_1GBASE-T_P
P-8	CH4_D_1GBASE-T_N
P-GND	GND

J2 CONNECTOR

ID	DESCRIPTION
1	CHASSIS_GND
2	CHASSIS_GND
3	CHASSIS_GND
4	CHASSIS_GND
5	28VDC
6	28VDC_RTN

J3 CONNECTOR

ID	DESCRIPTION
B-1	CH5_A_1GBASE-T_P
B-2	CH5_A_1GBASE-T_N
B-3	CH5_B_1GBASE-T_P
B-4	CH5_B_1GBASE-T_N
B-5	CH5_C_1GBASE-T_P
B-6	CH5_C_1GBASE-T_N
B-7	CH5_D_1GBASE-T_P
B-8	CH5_D_1GBASE-T_N
B-GND	GND
F-1	CH6_A_1GBASE-T_P
F-2	CH6_A_1GBASE-T_N
F-3	CH6_B_1GBASE-T_P
F-4	CH6_B_1GBASE-T_N
F-5	CH6_C_1GBASE-T_P
F-6	CH6_C_1GBASE-T_N
F-7	CH6_D_1GBASE-T_P
F-8	CH6_D_1GBASE-T_N
F-GND	GND
K-1	CH7_A_1GBASE-T_P
K-2	CH7_A_1GBASE-T_N
K-3	CH7_B_1GBASE-T_P
K-4	CH7_B_1GBASE-T_N
K-5	CH7_C_1GBASE-T_P
K-6	CH7_C_1GBASE-T_N
K-7	CH7_D_1GBASE-T_P
K-8	CH7_D_1GBASE-T_N
K-GND	GND
P-1	CH8_A_1GBASE-T_P
P-2	CH8_A_1GBASE-T_N
P-3	CH8_B_1GBASE-T_P
P-4	CH8_B_1GBASE-T_N
P-5	CH8_C_1GBASE-T_P
P-6	CH8_C_1GBASE-T_N
P-7	CH8_D_1GBASE-T_P
P-8	CH8_D_1GBASE-T_N
P-GND	GND

REV. A

SHEET 2 OF 3

CF-020400-56X

DOCUMENT NO. CF-020400-56X

SHEET 2 OF 3

REV. A

SIZE C

CAGE CODE 77820

DOCUMENT NO. CF-020400-56X

REV. A

SCALE: 1.5

REF: CF-020400-52X

SHEET 2 OF 3

RELEASED / Dec. 21 2022, 12:49:12 PM

3

2

1

4		3		2		CF-020400-56X DOCUMENT NO. SHEET 3 OF 3 REV. A	
CF-020400-56X DOCUMENT NO. SHEET 3 OF 3 REV. A		C		B		A	
12. OPERATING TEMPERATURE: -40°C TO 70°C STORAGE TEMPERATURE: -55°C TO 85°C		11. MATING CONNECTOR REFERENCE: J1 MATING CONNECTOR: TV06RQW-19-18S(LC) OR EQUIVALENT J1 MATING CONTACT: 21-032905-021 OCTONET FOR PIC E6A3824 CABLE OR EQUIVALENT J2 MATING CONNECTOR: TV06RW-9-35S OR EQUIVALENT		10. FOR INSERT ARRANGEMENT, SEE FOLLOWING DOCUMENTS. J1 CONNECTOR: LQ-21818-18 J2 CONNECTOR: L-21808-35 J3 CONNECTOR: LQ-21818-18		9. J1, J2 AND J3 CONNECTOR DESIGNATORS SHALL BE STAMPED IN CONTRASTING COLOR PER 9-3856-5. LOCATION OF DESIGNATORS SHALL BE APPROXIMATELY AS SHOWN.	
8. PROCESS SPEC: 9-3856-5, 9-9172-3		7. CONVERTER HOUSING AND CONNECTOR SHELLS ARE OD CAD PLATED PLATED ALUMINUM ALLOY.		6. PACKAGE PER PRODUCTION PROCESS SHEET.		5. MARKING DATA MAY DIFFER FROM DRAWING BASED ON CUSTOMER SPECIFIC ORDER REQUIREMENTS.	
4. ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE (ESD) SENSITIVE COMPONENTS. ASSEMBLY SHALL BE HANDLED, PACKAGED, AND SHIPPED TO MEET REQUIREMENTS OF ANSI/ESD-S-20.20 AND IPC-A-610.		3. PROTECTIVE CAPS SHALL BE INSTALLED PRIOR TO SHIPPING.		2. PACKAGE LABEL SHALL CONTAIN THE SAME INFORMATION SHOWN IN NOTE 1.		1. MARK LABEL "AMPHENOL", PART NUMBER AND SEVEN DIGIT SERIAL NUMBER AND ATTACH ON INDICATED SURFACE. SERIAL NUMBER PER 9-9172-3.	
EXAMPLE: FOR NORMAL KEY CONVERTER NUMBER 8 BUILT ON AUG 19, 2022		AMPHENOL CF-020400-56N 2233008					
NOTES:							
THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.							
RELEASED / Dec. 21 2022, 12:49:12 PM							
DOCUMENT NO. CF-020400-56X		SHEET 3 OF 3		REV. A			
4		RELEASED / Dec. 21 2022, 12:49:12 PM		3		2	
						1	
						CF-020400-56X DOCUMENT NO. SHEET 3 OF 3 REV. A	
						Eng PDM Information For Reference Only REV. A VERSION 1	
						D	

FRONT ISOMETRIC VIEW
SCALE 1.000

REAR ISOMETRIC VIEW
SCALE 1.000