




ISS.	AMEND	DATE
1	ISSUED	18/06/09
2	MATERIAL TABLE ADD	20/07/12
3	UPDATE NEW TOOLING	16/04/20



DESCRIPTION	MATERIAL	FINISH	QTY
CONTACT PIN	BRASS	SILVER PLATE	5
EARTH TERMINAL	PHOSPHOR BRONZE	SILVER PLATE	1
REAR COVER	PBT 4815 (UL94 V-0)	BLACK	1
HOUSING	PBT 4815 (UL94 V-0)	BLACK	1

SPECIFICATION

- CURRENT RATING: 100V AC 1A max
12V DC 2A max
- CONTACT RESISTANCE (INITIAL): 30mΩ max @AC100mA(max) 1KHz
- INSULATION RESISTANCE (INITIAL): 50MΩ (MIN) @250V DC
- WITHSTAND VOLTAGE: 250V AC 60Hz FOR 1 MINUTE
- INSERTION FORCE (INITIAL): 4.5Kg max
- WITHDRAWAL FORCE: 0.5-3.0Kg
- LIFE TEST: 1000 CYCLES MIN. AFTER TESTING CONTACT RESISTANCE SHALL NOT EXCEED 100mΩ
- OPERATING TEMPERATURE -40°C TO +85°C

RoHS COMPLIANT
TOLERANCE NO DEC. PLACE ± 1 DEC. PLACE ± 2 DEC. PLACE ± HOLE Ø ± ANGLES ± UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: SEE TABLE

TITLE: 5 PIN DIN SOCKET 180°

FINISH: SEE TABLE

DRWG. No. **FC680805**

DRAWN: C.A.M.J.

APPROVED: R.W.T.

FORM: A4DRWG+