

REVISION AK

DO NOT SCALE FROM THIS PRINT

TABLE 1			
ENTRY STYLE	CONTACT	BODY	
-PE	SUB-HLE-PE-XX	RHLE-50-D	
-TE	C-132-09-XX	RHLE-50-D	
-PE-BE	SUB-HLE-PE-XX	RHLE-50-DBE	





(-PE: PASS THROUGH ENTRY)

(SHOWN WITH -LC OPTION)

NOTES:

1. © REPRESENTS A CRITICAL DIMENSION.
2. CUT ASSEMBLIES AFTER FILL. CUT FLASH TO BE .010 MAX WITH NO FLASH ALLOWED IN HOLES OR EXTENDING BELOW LEADS. WILL LOSE A POSITION FOR EVERY CUT.

3. TUBE POSITIONS 03 THRU 50. LAYER PACKAGE POSITION 02.

4. ENDWALL THICKNESS: .030 ± .005.

5. MINIMUM CONTACT RETENTION IN PLASTIC: 12 OUNCES 6. AFTER PLATING, PIN IS NAMED SUB-C-132-10-X. AFTER FORMING, PIN IS C-132-10-X.

©7. MAXIMUM VARIATION OF 3 DEGREES WITHIN 16 PINS.

8. MEASURE FROM BEND TO TIP OF PIN.

9. MEASURE FROM CONTACT BARB AREA TO TIP OF PIN 10. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT, SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.

11. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM

12. ATTACH LABEL TO EACH REEL

No OF POSITIONS -02 THRU -50 (PER ROW)

> LEAD STYLE -02

PLATING SPECIFICATION

-G: 10µ" LIGHT SELECTIVE GOLD IN CONTACT AREA, 3µ" GOLD ON TAIL

-L: 10µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

-S: 30µ" SELECTIVE GOLD IN CONTACT

AREA, MATTE TIN ON TAIL -F: 3u" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

-LM: 10u" LIGHT SELECTIVE GOLD IN CONTACT

AREA, MATTE TIN ON TAIL -SM: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL

NOT AVAILABLE WITH -TE) -LC: LOCKING CLIP (SEE NOTE 10) (USE LC-08-TM-01) AVAILABLE ON -PE STYLE ONLY) **ENTRY STYLE**

HLE-1XX-02-XX-DV-XE-XX-X-XX

-PE: PASS THROUGH ENTRY (SEE FIG 1) -TE: TOP ENTRY (SEE FIG 2)

PACKAGING

-TR: TAPE & REEL

BLANK: TUBES (SEE NOTE 3)

(2 - 29 POSITIONS ONLY) (-TE & -PE OPTIONS

ONLY) (SEE NOTE 11 & 12)

ONLY) (SEE NOTE 11 & 12)

-FR: FULL REEL QTYTAPE & REEL (2 - 29 POSITIONS ONLY)

(-TE & -PE OPTIONS

PICK & PLACE OPTION

-P: METAL PAD

(USE LMP-02)


(AVAILABLE ON -PE STYLE ONLY)

(SEE FIG 2)

ROW SPECIFICATION -DV: DOUBLE VERTICAL

OPTION

-BE: BOTTOM ENTRY



SECTION "A"-"A"

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND

PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED. IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DESCRIPTION

.100 C.L. SINGLE BEAM SOCKET STRIP

520 PARK EAST BLVD, NEW ALBANY, IN 47150

HLE-1XX-02-XX-DV-XE-XX-XX

BY: KEVIN B

10/27/99

SHEET 1 OF 2

DECIMALS **ANGLES** .XX: ±.01 2° .XXX: ±.005 .XXXX: ±.0020

BODY: VECTRA E130i

CONTACT: BeCu

COLOR: BLACK

MATERIAL:

DO NOT SCALE DRAWING

F:\DWG\MISC\MKTG\HLE-1XX-02-XX-DV-XE-XX-XX-MKT.SLDDRW

SHEET SCALE: 2:1

PHONE: 812-944-6733

e-Mail: info@SAMTEC.com

FAX: 812-948-5047







FIG 3 (BOTTOM ENTRY OPTION) (SAME AS FIG 1 EXCEPT AS SHOWN)



ENTRY STYLE	PACKAGING TUBE	PLUG
-PE	PT-1-24-05-38	TP-09
-TE	PT-1-24-01-60	TP-09
-TE-P	PT-HLE001-DV-TE-P	TP-09







PACKAGING VIEWS

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRETERY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMFEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR PERHODUCED, TRANSFERRED OR HOROPROATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMFEC, IN

F:\DWG\MISC\MKTG\HLE-1XX-02-XX-DV-XE-XX-X-XX-MKT.SLDDRW

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

SHEET SCALE: 2:1

DESCRIPTION:

BY: KEVIN B

.100 C.L. SINGLE BEAM SOCKET STRIP

HLE-1XX-02-XX-DV-XE-XX-XX

10/27/99 SHEET 2 OF 2