



DIMENSIONS:	
A	4.000" ± 0.063
B	2.210" ± 0.125
C	2.620" ± 0.063
D	3.563" ± 0.063
E	1.076" ± 0.063
F	3.076" ± 0.063
G	0.187" ± 0.015



NOTE: ALL LEADS 10" OUT MIN. STRIPPED 0.5"

ELECTRICAL DATA:		
TESTS	CONDITIONS	ACCEPTANCE CRITERIA
I _{ex}	@ 480V, 60Hz, BLK - BLK	62.4mA Max.
Sec. N.L.V	@ 480V, 60Hz, BLK - BLK	
	RED - RED =	25.83V $\pm 1\%$
DCR	@ 20°C, BLK - BLK =	138.2 Ω $\pm 20\%$
	@ 20°C, RED - RED =	0.371 Ω $\pm 20\%$
HIPOT	PRIMARY - SECONDARY	3000V, 60Hz, 1 SEC

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION		
0	RELEASED. C.I.	04/12/18	MANUFACTURING™ 52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5		
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: CONTROL TRANSFORMER
			DATE: 04/12/18	APP'D. BY:	DWG. NO. PHC50FGA
				DIMENSIONS: IN(X) MM()	

PH # (519) 886-6181
FAX # (519) 886-9540