






P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05





SECTION A-A
SCALE 1:1



BLACK	3.00	25.00	25.80	26.34	23.30	21.00	30	7-2394521-3	6-2394521-3
	1.50	17.50	18.30	18.84	15.80	13.50	20	7-2394521-2	6-2394521-2
NATURAL		10.00	10.80	11.34	8.30	6.00	10	7-2394521-1	6-2394521-1
	3.00	25.00	25.80	26.34	23.30	21.00	30	5-2394521-3	4-2394521-3
		17.50	18.30	18.84	15.80	13.50	20	5-2394521-2	4-2394521-2
	1.50	10.00	10.80	11.34	8.30	6.00	10	5-2394521-1	4-2394521-1
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1
								P/N	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021		TE Connectivity Ltd.					
		CHK Niki Shi 12APR2021							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —					
		APVD Niki Shi 12APR2021							
		PRODUCT SPEC							
		APPLICATION SPEC							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
NOTE 1		NOTE 2		A300779		C-2394521		—	
CUSTOMER DRAWING						SCALE	N/A	SHEET 2 OF 7	REV A1

P	LTR	DESCRIPTION	DATE	DWN	APV
	—	SEE SHEET 1	—	—	—




PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05


- NOTES:
1. MATERIAL:
 - 1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,UL94V-0.
COLOR:SEE PART NUMBER
 - 1.2 CONTACT: Boway ALLOY .
 - 1.3 FITTING NAIL: STAINLESS STEEL
 2. FINISH:
 - 2.1 CONTACT:
50u" MIN NICKEL UNDERPLATING OVERALL.
TYPE 1: 100u" MIN MATT TIN PLATING OVERALL
TYPE 2: GOLD FLASH ON CONTACT AND SOLDER
 - 2.2 FITTING NAIL:
50u" MIN NICKEL UNDER PLATING OVERALL
100u" MATT MIN TIN PLATING OVERALL
 3. REFLOW SOLDER CAPABLE TO 260°C





SECTION A-A
SCALE 1:1



BLACK	3.00	32.50	33.30	33.84	30.80	28.50	40	3-2394521-4	2-2394521-
NATURAL	3.00	32.50	33.30	33.84	30.80	28.50	40	1-2394521-4	2394521-4
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1
								P/N	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian 12APR2021		TE Connectivity Ltd.				
		CHK Niki Shi 12APR2021						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°		APVD Niki Shi 12APR2021		NAME		
				PRODUCT SPEC		1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —		
				APPLICATION SPEC				
				—				
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED	
NOTE 1		NOTE 2		WEIGHT N/A	A3	00779	©-2394521	—
CUSTOMER DRAWING						SCALE N/A	SHEET 3 of 7	REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



PCB PATTERN LAYOUT
GENERAL TOLERANCE ± 0.05


- NOTES:
1. MATERIAL:
 - 1.1 HOUSING: THERMOPLASTIC, HIGH TEMP.,UL94V-0.
COLOR:SEE PART NUMBER
 - 1.2 CONTACT: COPPER ALLOY BRASS.
 2. FINISH:
 - 2.1 CONTACT:
50u" MIN NICKEL UNDERPLATING OVERALL.
TYPE 1: 100u" MIN MATT TIN PLATING OVERALL
TYPE 2: GOLD FLASH ON CONTACT AND SOLDER
 3. REFLOW SOLDER CAPABLE TO 260°C



SECTION A-A
SCALE 1:1

BLACK	3.00	32.50	33.30	33.84	30.80	28.50	40	7-2394521-4	6-2394521-4
NATURAL	3.00	32.50	33.30	33.84	30.80	28.50	40	5-2394521-4	4-2394521-4
COLOR	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	Pos.No	TYPE 2	TYPE 1
								P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tommy Qian CHK Niki Shi APVD Niki Shi PRODUCT SPEC — APPLICATION SPEC — WEIGHT N/A		12APR2021 12APR2021 12APR2021		TE Connectivity Ltd.					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.1 4 PLC ± — ANGLES ± 2°		NAME 1.5mm PITCH WTB Conn. SMT R/A TYPE DOUBLE ROW —				RESTRICTED TO —			
											
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		REV	
NOTE 1		NOTE 2		A3		00779		C-2394521		A 1	
CUSTOMER DRAWING						SCALE		SHEET		REV	
						N/A		4 OF 7		A 1	




- NOTES:
- 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE,±0.20mm
 - CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
 - ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
 - MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
 - THICKNESS: 0.50 ± 0.05 mm.
 - PACKING LENGTH PER 13" REEL :7.5 METERS.
 - COMPONENT LOAD PER 13" REEL : 400 PCS.

24.4	11.65	9.06	6.96	24.00	11.50	10P	*-2394521-1
DIM D	DIM B2	DIM B1	DIM B0	DIM W	DIM F	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.25
2 PLC ± 0.15
3 PLC ± 0.1
4 PLC ± -
ANGLES ± 2°
FINISH -

DWN Tommy Qian 12APR2021
CHK Niki Shi 12APR2021
APVD Niki Shi 12APR2021
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT -

CUSTOMER DRAWING



TE Connectivity Ltd.

1.25mm PITCH WTB Conn.
SMT VERTICAL TYPE DOUBLE ROW

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2394521	-

SCALE	SHEET	REV
N/A	5 of 7	A1

