






MATING SIDE



NOTES:

RATED VOLTAGE: MAX. 63V AC/DC
RATED CURRENT: MAX. 16A at 40°C (derating has to be considered)
IP RATING: IP67 (mated and locked condition)
TEMPERATURE RANGE: -25°C TO +85°C

CABLE PRINTING (sequence as shown below):
- MOLEX engineering no. (see page 2)
- MOLEX material no. (see page 2)
- MOLEX MAX. 63V AC/DC MAX. 16 A USR
- MOLEX AND DATE OF MANUFACTURING (YY=YEAR; WW=WEEK): MXYWW
- Not for current interrupting
- PROFINET 24V Power 4x2,5

PART ACCORDING PRODUCT SPEC: 1205010169
PACKAGING ACCORDING PACKAGING SPEC: 1201202000

TABLE 1

POS	DESCRIPTION	MATERIAL	FINISH
1	NUT M12 MA	BRASS	Ni
2	CONTACT 15 MA	BRASS	Au
3	INSERT	PA	BLACK
4	OVERMOLD	TPE	BLACK
5	CABLE 4x2.5 D10.1 WSOR	PUR	BLACK
OPTIONAL 6	ID CARRIER	-	-

FUNCTIONAL SYMBOLS E A = 0 E = 0 E = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED ATTRIBUTE TO GENERAL MARKET IN ECTR			molex					
	mm		2:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)				CSE M12 4P LC MA RA WSOR BK XM UNSH								
	ANGULAR TOL ± 1.0 °												
	4 PLACES		±		EC NO: 735577 DRWN: NIKHIS3 2023/01/12 CHK'D: RSILLER 2023/01/19 APPR: RSILLER 2023/01/19			PRODUCT CUSTOMER DRAWING					
	3 PLACES		±										
	2 PLACES		± 0.05		INITIAL REVISION: DRWN: FDAFERNER 2020/05/13 APPR: RSILLER 2021/10/05			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
	1 PLACE		± 0.3					1205000249		PSD	000	A1	
	0 PLACES		± 0.5										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE	120500	SEE TABLE 2		GENERAL MARKET		1 OF 2	

ENGINEERING NO - NUMERICAL CODE (Available parts see PART LIST table. Other parts available upon request).




TABLE 2

NOMINAL SECTION 2,5mm ²			
MATERIAL NO.	ENGINEERING NO.	L [mm]	TOLERANCE [mm]
1205000249	L0P4007B65M010	1000	+40
1205000250	L0P4007B65M020	2000	+60
1205000251	L0P4007B65M030	3000	+60
1205000252	L0P4007B65M050	5000	+60
1205000253	L0P4007B65M100	10000	+80
1205000254	L0P4007B65M150	15000	+140
1205000255	L0P4007B65M200	20000	+140

DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19	11:13:31
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED ATTRIBUTE TO GENERAL MARKET IN ECTR			molex							
	mm		1:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL ± 1.0°		EC NO: 735577 DRWN: NIKHIS3 2023/01/12 CHK'D: RSILLER 2023/01/19 APPR: RSILLER 2023/01/19 INITIAL REVISION: DRWN: FDAERNER 2020/05/13 APPR: RSILLER 2021/10/05					CSE M12 4P LC MA RA WSOR BK XM UNSH							
	4 PLACES ±														
	3 PLACES ±														
	2 PLACES ± 0.05					PRODUCT CUSTOMER DRAWING									
	1 PLACE ± 0.3														
	0 PLACES ± 0.5														
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
					A3-SIZE		120500		SEE TABLE 2		GENERAL MARKET		2 OF 2		
								DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
								1205000249		PSD		000		A1	