





MATING SIDE
FEMALE CONNECTOR



MATING SIDE
MALE CONNECTOR



NOTES:

RATED VOLTAGE: MAX. 63V AC/DC
RATED CURRENT: MAX. 12A at 40°C (derating has to be considered)
IP RATING: IP67 (mated and locked condition)
TEMPERATURE RANGE: -25°C TO +85°C

CABLE PRINTING (sequence as shown below):
- MOLEX part number
- "Made in " COUNTRY OF ORIGIN
- MOLEX AND DATE OF MANUFACTURING (YY=YEAR; WW=WEEK): MXYWW
- Not for current interrupting

PART ACCORDING PRODUCT SPEC: 1205010169
PACKAGING ACCORDING PACKAGING SPEC: 1201202000

TABLE 1

POS	DESCRIPTION	MATERIAL	FINISH
1	NUT M12 FE	BRASS	Ni
2	NUT M12 MA	BRASS	Ni
3	CONTACT 15 MA	BRASS	Au
4	CONTACT 15 FE	BRASS	Au
5	INSERT FEMALE	PA	GREY
6	INSERT MALE	PA	GREY
7	OVERMOLD	TPE	BLACK
8	CABLE 5x1.5 D8.6 WSOR	PUR	GREY
9	GASKET OR 8.2X1.25	FKM	BLACK
OPTIONAL 10	ID CARRIER	-	-

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FUNCTIONAL SYMBOLS DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED ATTRIBUTE TO GENERAL MARKET IN ECTR				molex CSE M12 5P LC FE RA MA STR WSOR GY XM							
	mm		2:1		EC NO: 735577 DRWN: NIKHIS3 2023/01/12 CHK'D: RSILLER 2023/01/19 APPR: RSILLER 2023/01/19 INITIAL REVISION: DRWN: FDAFERNER 2020/08/19 APPR: RSILLER 2022/12/05											
	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	ANGULAR TOL ± 1.0 °															
	4 PLACES		±													
	3 PLACES		±													
DIVISIONAL SYMBOLS	2 PLACES		± 0.05		PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER 1205010208 DOC TYPE PSD DOC PART 000 REVISION A1											
	1 PLACE		± 0.3													
	0 PLACES		± 0.5													
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
							A2-SIZE		120501		SEE TABLE 2		GENERAL MARKET		1 OF 2	

ENGINEERING NO - NUMERICAL CODE (Available parts see PART LIST table. Other parts available upon request).




TABLE 2

NOMINAL SECTION 1,5mm²			
MATERIAL NO.	ENGINEERING NO.	L [mm]	TOLERANCE [mm]
1205010208	LLP5031B66M005	500	+40
1205010209	LLP5031B66M010	1000	+40
1205010210	LLP5031B66M020	2000	+60
1205010211	LLP5031B66M030	3000	+60
1205010212	LLP5031B66M050	5000	+60
1205010213	LLP5031B66M100	10000	+80
1205010214	LLP5031B66M150	15000	+140
1205010215	LLP5031B66M200	20000	+140

DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19	11:13:49
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS

FA

=

0

FE

=

0

FE

=

0

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.05

1 PLACE ± 0.3

0 PLACES ± 0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

120501

EC NO: 735577

DRWN: NIKHIS3

CHK'D: RSILLER

APPR: RSILLER

2023/01/12

2023/01/19

2023/01/19

INITIAL REVISION:

DRWN: FDAFERNER

APPR: RSILLER

2020/08/19

2022/12/05

DOCUMENT NUMBER

1205010208

DOC TYPE

PSD

DOC PART

000

REVISION

A1

MATERIAL NUMBER

SEE TABLE 2

CUSTOMER

GENERAL MARKET

SHEET NUMBER

2 OF 2