

EXAMPLE:

PART NUMBER: RJE36-188-1XXX-01

LED COLOR CODE

TYPICAL FOR SINGLE



(ANODE)+ (CATHODE)-

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	BLOCKED	BLOCKED	9	GREEN	BLOCKED	J	BiC RD/GR	YELLOW
1	YELLOW	GREEN	A	BiC GR/YE	BiC GR/YE	K	YELLOW	BiC GR/OR
2	BLOCKED	GREEN	B	BiC RD/GR	BiC RD/GR	L	BiC GR/YE	RED
3	YELLOW	BLOCKED	C	BiC RD/GR	BiC GR/YE	M	RED	YELLOW
4	GREEN	YELLOW	D	GREEN	BiC GR/YE	N	BiC GR/RD	BiC GR/YE
5	GREEN	GREEN	E	YELLOW	BiC GR/YE	P	GREEN	BiC RD/GR
6	YELLOW	YELLOW	F	BiC GR/YE	YELLOW	R	BiC GR/OR	GREEN
7	RED	GREEN	G	BiC GR/OR	BiC GR/OR	T	RED	RED
8	GREEN	RED	H	BiC GR/YE	GREEN	V	BiC RD/GR	GREEN
						W	ADDITIONAL	OPTIONS

EXAMPLE OF ADDITIONAL LED OPTIONS:


PART NUMBER RJE36-188-1XWX-X1

ADDITIONAL LED COLOR CODE

↑ DENOTES ADDITIONAL LED OPTIONS TO BE USED

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	DO NOT USE		5	BLOCKED	YELLOW	A	YELLOW	YELLOW
1	RED	BLOCKED	6	RED	BiC RD/GR	B	YELLOW	GREEN
2	BiC GR/OR	YELLOW	7	BLOCKED	BiC RD/GR	C	GREEN	YELLOW
3	YELLOW	RED	8	BiC RD/GR	BLOCKED	D	GREEN	GREEN
4	BLOCKED	RED	9	BiC GR/YE	BLOCKED	M	RED	YELLOW
						N	GREEN	BiC GR/OR
						E	GREEN	ORANGE
						F	ORANGE	GREEN

TYPICAL FOR BI-COLOR
GREEN



(GREEN/ORANGE, GREEN/YELLOW
AND GREEN/RED)

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAY10/18	L.CHAN
B	PROPOSAL	AUG23/18	L.CHAN
C	ADD LOW CURRENT NOTES	DEC05/18	L.CHAN

LED SPECIFICATIONS:

FORWARD VOLTAGE: 2.1 VOLTS TYP.

REVERSE VOLTAGE: 5.0 VOLTS MIN.

LUMINOUS INTENSITY: 0.5 mCd MIN.

(AT If=2mA)

STORAGE TEMPERATURE: -40° TO 85° C

LEAD SOLDERING TEMPERATURE: 260° C

(5 SEC, 1/16" FROM CASE)

PLATING ON TAILS: TIN OR TIN/COPPER

ALLOY OVER SILVER

PRIMARY COLOR FOR BI-COLOR

LEDS IN STANDARD ANODE/

CATHODE CONFIGURATION IS:

RED-GREEN= RED

RED-YELLOW= RED

GREEN-YELLOW= GREEN

GREEN-ORANGE= GREEN

LEGEND

BiC=BI-COLOR LED

LOWC=LOW CURRENT LED

YE=YELLOW

GR=GREEN

RD=RED

OR=ORANGE

NOTE:

THE TWO DIGITS PRECEDING THE
ADDITIONAL LED CODE MUST BE
USED IN THE PART NUMBER, WHEN
ORDERING ANY OF THE ADDITIONAL
LED OPTIONS.

UNLESS SPECIFIED OTHERWISE		DRAWN HANSON.C	DATE MAY10/18	Amphenol Canada Corp.	
PRIMARY UNITS MILLIMETER		CHECKED Lawrence.C	DATE MAY10/18	Commercial Products	
SECONDARY INCH		M.E. APP'D		TITLE	
REFERENCE IN PARENTHESES		Q.A. APP'D		LED OPTIONS FOR RJE36	
GENERAL TOLERANCES		DWG APPR.		DWG. NO.	
1 DECIMAL PLACE	±0.45	ENG. REL. NO.		P-RJE36-LEDs	
2 DECIMAL PLACES	±0.30	REF.		REV C	
3 DECIMAL PLACES	±0.15	THIRD ANGLE PROJECTION		CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	
ANGULAR DEGREES	±1.0°				