






LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
	A	ECN-22-175374			20SEP2022	VL	ZSH	
	A1	REVISED PER ECN-23-227269			09AUG2023	RY	SZ	



1-2385800-2 AS SHOWN
SCALE 4:1



1-2385800-2
SCALE 4:1



DETAIL A
SCALE 8:1

1. MATERIAL:
CAGE MATERIAL : 0.25 THICK STAINLESS STEEL.
SPRING MATERIAL: COPPER ALLOY

2.FINISH:
SPRING: NICKEL PLATING

3. NOTE DELETE

4. REFERENCE APPLICATION SPEC 114-60025 FOR RECOMMENDED DRILL
HOLE DIAMETER AND PLATING THICKNESS.


5. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.

6. MINIMUM PC BOARD THICKNESS : SINGLES SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN

7. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.

8. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN


9. MATES WITH QSFP DD MSA COMPATIBLE TRANSCEIVER.




CLOSED TOP	0	2-2385800-5
CLOSED TOP	2	2385800-1
HS OPENING	0	1-2385800-7
HS OPENING	2	1-2385800-2
REMARK	# REAR PINS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU CHK SUNY ZHAO APVD	26JAN2021 26JAN2021	 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	CAGE ASSEMBLY, QSFP112 STANDARD 1X1, WITH EMI SPRING FINGER
mm		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-60122 APPLICATION SPEC 114-60025		
MATERIAL	-	-	-	SIZE	CAGE CODE
	-	-	-	A1	-
	-	-	-	DRAWING NO	
	-	-	-	C=2385800_C	
	-	-	-	RESTRICTED TO	
	-	-	-	-	
CUSTOMER DRAWING				SCALE	2:1
				SHEET	1
				OF	6
				REV	A


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




1-2385800-2 AS SHOWN
WITH HS OPENING
AND 2 REAR PINS
SCALE 3:1



1-2385800-7 AS SHOWN
WITH HS OPENING
AND 0 REAR PINS
SCALE 3:1



2385800-1 AS SHOWN
WITH CLOSED TOP
AND 2 REAR PINS
SCALE 3:1



2-2385800-5 AS SHOWN
WITH CLOSED TOP
AND 0 REAR PINS
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 26JAN2021	 TE Connectivity	
		CHK SUNY ZHAO 26JAN2021		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME
mm		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-60122 APPLICATION SPEC 114-60025
MATERIAL		WEIGHT		RESTRICTED TO
-		-		-
CUSTOMER DRAWING		SCALE 2:1	SHEET 2	OF 6
		REV A1		





LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	

D

C

B

A




C


B

A


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 26JAN2021	TE Connectivity	
		CHK SUNY ZHAO 26JAN2021		
DIMENSIONS:		APVD	NAME	
mm		PRODUCT SPEC	CAGE ASSEMBLY, QSPF112 STANDARD 1X1, WITH EMI SPRING FINGER	
		108-60122		
		APPLICATION SPEC	SIZE	
		114-60025	A1	
MATERIAL		WEIGHT	CAGE CODE	
-		-	-	
		CUSTOMER DRAWING	DRAWING NO	
			C=2385800_C	
			RESTRICTED TO	
			-	
			SCALE	
			2:1	
			SHEET	
			3 OF 6	
			REV	
			A1	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26JAN2021 VINDY LIU CHK 26JAN2021 SUNY ZHAO		DET STE TE Connectivity SCALE 2:1	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.50 3 PLC ± 0.10 4 PLC $\pm .$ ANGLES $\pm .$		NAME CAGE ASSEMBLY, QSFP112 STANDARD 1X1, WITH EM1 SPRING FINGER	
		APVD PRODUCT SPEC 108-60122 APPLICATION SPEC 114-60025		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL -		FINISH -		WEIGHT - A1 - C=2385800.C -	
CUSTOMER DRAWING				SCALE 2:1 SHEET 4 of 6 REV A	



LOC		DIST		REVISIONS				
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		-	SEE SHEET 1			-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 26JAN2021	TE Connectivity	
		CHK SUNY ZHAO 26JAN2021		
DIMENSIONS:		APVD	NAME	
mm		PRODUCT SPEC		
		108-60122	SIZE	
		APPLICATION SPEC		
		114-60025		
		WEIGHT		
MATERIAL		-	C=2385800_C	
		CUSTOMER DRAWING	SCALE 2:1	
			SHEET 6 OF 6	
			REV A1	