

CIRCUIT CONFIGURATIONS




CIRCUITE SIZE

PLUG HOUSING ASSEMBLY




PLUG HOUSING ASSEMBLY WITH KEY ⓓ

PLUG HOUSING ASSEMBLY WITH KEY AND CLIP SLOT ⓓ




2 CKT




3 CKT






4 CKT





5 CKT



FUNCTIONAL SYMBOLS ⚠ = 0 ⚠ = 0 ⚠ = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.			molex				
	mm		5:1									
	GENERAL TOLERANCES (UNLESS SPECIFIED)											
	ANGULAR TOL ± °											
	4 PLACES		±		EC NO: 760095 DRWN: GOOLAM CHK'D: GOOLAM APPR: MRAMAKRISHNA 2023/08/02 2023/08/18 2023/08/18			PRODUCT CUSTOMER DRAWING				
	3 PLACES		±									
	2 PLACES		±									
	1 PLACE		± 0.3									
	0 PLACES		±		INITIAL REVISION: DRWN: MUM 2019/01/30 2019/07/03 APPR: NCSR			DOCUMENT NUMBER			DOC TYPE	DOC PART
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION				DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
				ⓓ		E-SIZE	207778	SEE TABLE	GENERAL MARKET	1 OF 4		



CKT SIZE	DIM. A
2	15.3
3	18.9
4	22.5



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																											
DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.					molex																			
	mm		5:1																										
	GENERAL TOLERANCES (UNLESS SPECIFIED)									PLUG ASSEMBLY SQUBA 3.6																			
	ANGULAR TOL ± °																												
	4 PLACES		±		EC NO: 760095 DRWN: GOOLAM 2023/08/02 CHK'D: GOOLAM 2023/08/18 APPR: MRAMAKRISHNA 2023/08/18					PRODUCT CUSTOMER DRAWING																			
	3 PLACES		±																										
	2 PLACES		±												DOCUMENT NUMBER 2077780000-SD DOC TYPE PSD DOC PART 000 REVISION D3														
	1 PLACE		± 0.3																										
0 PLACES		±		INITIAL REVISION: DRWN: MUM 2019/01/30 APPR: NCSR 2019/07/03					SHEET NUMBER 2 OF 4																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														THIRD ANGLE PROJECTION					DRAWING E-SIZE					SERIES 207778					

molex







PLUG ASSEMBLY
SQUBA 3.6

PRODUCT CUSTOMER DRAWING

DOC TYPE	DOC PART	REVISION
PSD	000	D3

DOCUMENT STATUS	P1	RELEASE DATE	2023/08/18	10:37:23
-----------------	----	--------------	------------	----------


KEYING CONFIGURATIONS D



CHARTED DIMENSIONS												
KEYS	KEY A RED		KEY B NATURAL		KEY C GRAY		KEY D YELLOW		KEY E BROWN		KEY F ORANGE	
DIMENSIONS	H	I	J	K	L	M	N	O	P	Q	R	S
CKT 2	8.56	8.56	8.23	8.56	8.94	8.56	8.23	8.56	8.94	8.56	8.94	8.23
CKT 3	10.10	10.10	9.61	10.10	10.75	10.10	9.61	10.10	10.75	10.10	10.75	9.61
CKT 4	11.58	11.58	10.88	11.58	12.54	11.58	10.88	11.58	12.54	11.58	12.54	10.88

NOTE: KEYING CONFIGURATIONS WILL REMAINS SAME IN 2 & 3 CKT.

DOCUMENT STATUS	P1	RELEASE DATE	2023/08/18	10:37:23
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.		molex							
		mm		1:1											
		GENERAL TOLERANCES (UNLESS SPECIFIED)						PLUG ASSEMBLY SQUBA 3.6							
		ANGULAR TOL ± °													
		4 PLACES		±											
		3 PLACES		±				PRODUCT CUSTOMER DRAWING							
		2 PLACES		±											
1 PLACE		± 0.3													
0 PLACES		±		INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
				DRWN: GOOLAM		2023/08/02		2077780000-SD		PSD		000		D3	
				CHK'D: GOOLAM		2023/08/18									
				APPR: MRAMAKRISHNA		2023/08/18									
				DRWN: MUM		2019/01/30									
				APPR: NCSR		2019/07/03									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								E-SIZE 207778		SEE TABLE		GENERAL MARKET		3 OF 4	

PART NUMBER DETAILS				
WITHOUT KEY P/N	WIRE STYLE	NO. OF CIRCUITS	KEYING CONFIGURATION	COLOR
2077780002	UL1007 / UL1061 OR EQUIVALENT	2	NA	BLACK
2077780003	UL1007 / UL1061 OR EQUIVALENT	3	NA	BLACK
2077780004	UL1007 / UL1061 OR EQUIVALENT	4	NA	BLACK
2077780005*	UL1007 / UL1061 OR EQUIVALENT	5	NA	BLACK
WITH KEY P/N (D)				
2077780102	UL1007 / UL1061 OR EQUIVALENT	2	1	RED
2077780202	UL1007 / UL1061 OR EQUIVALENT	2	2	NATURAL
2077780302	UL1007 / UL1061 OR EQUIVALENT	2	3	GRAY
2077780402	UL1007 / UL1061 OR EQUIVALENT	2	4	YELLOW
2077780502	UL1007 / UL1061 OR EQUIVALENT	2	5	BROWN
2077780602	UL1007 / UL1061 OR EQUIVALENT	2	6	ORANGE
2077780103	UL1007 / UL1061 OR EQUIVALENT	3	1	RED
2077780203	UL1007 / UL1061 OR EQUIVALENT	3	2	NATURAL
2077780303	UL1007 / UL1061 OR EQUIVALENT	3	3	GRAY
2077780403	UL1007 / UL1061 OR EQUIVALENT	3	4	YELLOW
2077780503	UL1007 / UL1061 OR EQUIVALENT	3	5	BROWN
2077780603	UL1007 / UL1061 OR EQUIVALENT	3	6	ORANGE
2077780104	UL1007 / UL1061 OR EQUIVALENT	4	1	RED
2077780204	UL1007 / UL1061 OR EQUIVALENT	4	2	NATURAL
2077780304	UL1007 / UL1061 OR EQUIVALENT	4	3	GRAY
2077780404	UL1007 / UL1061 OR EQUIVALENT	4	4	YELLOW
2077780504	UL1007 / UL1061 OR EQUIVALENT	4	5	BROWN
2077780604	UL1007 / UL1061 OR EQUIVALENT	4	6	ORANGE
WITH KEY AND CLIP SLOT P/N (D)				
2077781102	UL1007 / UL1061 OR EQUIVALENT	2	1	RED
2077781202	UL1007 / UL1061 OR EQUIVALENT	2	2	NATURAL
2077781302	UL1007 / UL1061 OR EQUIVALENT	2	3	GRAY
2077781402	UL1007 / UL1061 OR EQUIVALENT	2	4	YELLOW
2077781502	UL1007 / UL1061 OR EQUIVALENT	2	5	BROWN
2077781602	UL1007 / UL1061 OR EQUIVALENT	2	6	ORANGE
2077781103	UL1007 / UL1061 OR EQUIVALENT	3	1	RED
2077781203	UL1007 / UL1061 OR EQUIVALENT	3	2	NATURAL
2077781303	UL1007 / UL1061 OR EQUIVALENT	3	3	GRAY
2077781403	UL1007 / UL1061 OR EQUIVALENT	3	4	YELLOW
2077781503	UL1007 / UL1061 OR EQUIVALENT	3	5	BROWN
2077781603	UL1007 / UL1061 OR EQUIVALENT	3	6	ORANGE
2077781104	UL1007 / UL1061 OR EQUIVALENT	4	1	RED
2077781204	UL1007 / UL1061 OR EQUIVALENT	4	2	NATURAL
2077781304	UL1007 / UL1061 OR EQUIVALENT	4	3	GRAY
2077781404	UL1007 / UL1061 OR EQUIVALENT	4	4	YELLOW
2077781504	UL1007 / UL1061 OR EQUIVALENT	4	5	BROWN
2077781604	UL1007 / UL1061 OR EQUIVALENT	4	6	ORANGE

WITHOUT KEY P/N	WIRE STYLE	NO. OF CIRCUITS	KEYING CONFIGURATION	COLOR
2077780012	UL1015 / UL1230 OR EQUIVALENT	2	NA	BLACK
2077780013	UL1015 / UL1230 OR EQUIVALENT	3	NA	BLACK
2077780014	UL1015 / UL1230 OR EQUIVALENT	4	NA	BLACK
WITH KEY P/N 				
2077780112	UL1015 / UL1230 OR EQUIVALENT	2	1	RED
2077780212	UL1015 / UL1230 OR EQUIVALENT	2	2	NATURAL
2077780312	UL1015 / UL1230 OR EQUIVALENT	2	3	GRAY
2077780412	UL1015 / UL1230 OR EQUIVALENT	2	4	YELLOW
2077780512	UL1015 / UL1230 OR EQUIVALENT	2	5	BROWN
2077780612	UL1015 / UL1230 OR EQUIVALENT	2	6	ORANGE
2077780113	UL1015 / UL1230 OR EQUIVALENT	3	1	RED
2077780213	UL1015 / UL1230 OR EQUIVALENT	3	2	NATURAL
2077780313	UL1015 / UL1230 OR EQUIVALENT	3	3	GRAY
2077780413	UL1015 / UL1230 OR EQUIVALENT	3	4	YELLOW
2077780513	UL1015 / UL1230 OR EQUIVALENT	3	5	BROWN
2077780613	UL1015 / UL1230 OR EQUIVALENT	3	6	ORANGE
2077780114	UL1015 / UL1230 OR EQUIVALENT	4	1	RED
2077780214	UL1015 / UL1230 OR EQUIVALENT	4	2	NATURAL
2077780314	UL1015 / UL1230 OR EQUIVALENT	4	3	GRAY
2077780414	UL1015 / UL1230 OR EQUIVALENT	4	4	YELLOW
2077780514	UL1015 / UL1230 OR EQUIVALENT	4	5	BROWN
2077780614	UL1015 / UL1230 OR EQUIVALENT	4	6	ORANGE
WITH KEY AND CLIP SLOT P/N 				
2077781112	UL1015 / UL1230 OR EQUIVALENT	2	1	RED
2077781212	UL1015 / UL1230 OR EQUIVALENT	2	2	NATURAL
2077781312	UL1015 / UL1230 OR EQUIVALENT	2	3	GRAY
2077781412	UL1015 / UL1230 OR EQUIVALENT	2	4	YELLOW
2077781512	UL1015 / UL1230 OR EQUIVALENT	2	5	BROWN
2077781612	UL1015 / UL1230 OR EQUIVALENT	2	6	ORANGE
2077781113	UL1015 / UL1230 OR EQUIVALENT	3	1	RED
2077781213	UL1015 / UL1230 OR EQUIVALENT	3	2	NATURAL
2077781313	UL1015 / UL1230 OR EQUIVALENT	3	3	GRAY
2077781413	UL1015 / UL1230 OR EQUIVALENT	3	4	YELLOW
2077781513	UL1015 / UL1230 OR EQUIVALENT	3	5	BROWN
2077781613	UL1015 / UL1230 OR EQUIVALENT	3	6	ORANGE
2077781114	UL1015 / UL1230 OR EQUIVALENT	4	1	RED
2077781214	UL1015 / UL1230 OR EQUIVALENT	4	2	NATURAL
2077781314	UL1015 / UL1230 OR EQUIVALENT	4	3	GRAY
2077781414	UL1015 / UL1230 OR EQUIVALENT	4	4	YELLOW
2077781514	UL1015 / UL1230 OR EQUIVALENT	4	5	BROWN
2077781614	UL1015 / UL1230 OR EQUIVALENT	4	6	ORANGE

PART NUMBER LOGIC D

207778 - X X X X

↑
SERIES NUMBERS

↑
CIRCUITE SIZE

0 = UL1007/1061 COMPATIBLE
1 = UL1015 / UL1230 COMPATIBLE

↑
1 - 6 KEYS

↑
1 = CLIP SLOT / WITH PANEL MOUNT
0 = NON-CLIP SLOT / WITHOUT PANEL MOUNT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
FUNCTIONAL SYMBOLS A = 0 C = 0 P = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.		molex									
		mm		1:1													
		GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 760095 DRWN: GOOLAM CHK'D: GOOLAM APPR: MRAMAKRISHNA		PLUG ASSEMBLY SQUBA 3.6									
		ANGULAR TOL		± °													
		4 PLACES		±													
3 PLACES		±															
2 PLACES		±		INITIAL REVISION: DRWN: MUM APPR: MCSR		2023/08/02 2023/08/18 2023/08/18		PRODUCT CUSTOMER DRAWING									
1 PLACE		± 0.3															
0 PLACES		±															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						E-SIZE		207778		2077780000-SD		PSD		000		D3	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
										SEE TABLE		GENERAL MARKET				4 OF 4	