

CIRCUIT CONFIGURATIONS


CIRCUITE SIZE

PLUG HOUSING ASSEMBLY


PLUG HOUSING ASSEMBLY WITH KEY D

PLUG HOUSING ASSEMBLY WITH KEY AND CLIP SLOT D


2 CKT










3 CKT





4 CKT



5 CKT


[illegible]

DOCUMENT STATUS	P1	RELEASE DATE	2023/08/18	10:37:23
-----------------	----	--------------	------------	----------


[illegible]

D


KEY A, RED COLOR




KEY B, NATURAL COLOR




KEY C, GRAY COLOR




KEY D, YELLOW COLOR



KEY E, BROWN COLOR



KEY F, ORANGE COLOR



CHARTED DIMENSIONS												
KEYS	KEY A RED		KEY B NATURAL		KEY C GRAY		KEY D YELLOW		KEY E BROWN		KEY F ORANGE	
DIMENSIONS	H	I	J	K	L	M	N	O	P	Q	R	S
CKT 2	8.56	8.56	8.23	8.56	8.94	8.56	8.23	8.56	8.94	8.56	8.94	8.23
CKT 3	10.10	10.10	9.61	10.10	10.75	10.10	9.61	10.10	10.75	10.10	10.75	9.61
CKT 4	11.58	11.58	10.88	11.58	12.54	11.58	10.88	11.58	12.54	11.58	12.54	10.88

NOTE: KEYING CONFIGURATIONS WILL REMAINS SAME IN 2 & 3 CKT.

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
A = 0 C = 0 P = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.				molex PLUG ASSEMBLY SQUBA 3.6							
		mm		1:1													
		GENERAL TOLERANCES (UNLESS SPECIFIED)															
		ANGULAR TOL ± °															
		4 PLACES		±													
3 PLACES		±		EC NO: 760095				2023/08/02									
2 PLACES		±		DRWN: GOOLAM				2023/08/18									
1 PLACE		± 0.3		CHK'D: GOOLAM				2023/08/18									
0 PLACES		±		APPR: MRAMAKRISHNA				2023/08/18									
		INITIAL REVISION:															
		DRWN: MUM				2019/01/30											
		APPR: MCSR				2019/07/03											
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
								E-SIZE		207778		SEE TABLE		GENERAL MARKET		3 OF 4	

PART NUMBER DETAILS

WITHOUT KEY P/N	WIRE STYLE	NO. OF CIRCUITS	KEYING CONFIGURATION	COLOR
2077780002	UL1007 / UL1061 OR EQUIVALENT	2	NA	BLACK
2077780003	UL1007 / UL1061 OR EQUIVALENT	3	NA	BLACK
2077780004	UL1007 / UL1061 OR EQUIVALENT	4	NA	BLACK
2077780005*	UL1007 / UL1061 OR EQUIVALENT	5	NA	BLACK
WITH KEY P/N 				
2077780102	UL1007 / UL1061 OR EQUIVALENT	2	1	RED
2077780202	UL1007 / UL1061 OR EQUIVALENT	2	2	NATURAL
2077780302	UL1007 / UL1061 OR EQUIVALENT	2	3	GRAY
2077780402	UL1007 / UL1061 OR EQUIVALENT	2	4	YELLOW
2077780502	UL1007 / UL1061 OR EQUIVALENT	2	5	BROWN
2077780602	UL1007 / UL1061 OR EQUIVALENT	2	6	ORANGE
2077780103	UL1007 / UL1061 OR EQUIVALENT	3	1	RED
2077780203	UL1007 / UL1061 OR EQUIVALENT	3	2	NATURAL
2077780303	UL1007 / UL1061 OR EQUIVALENT	3	3	GRAY
2077780403	UL1007 / UL1061 OR EQUIVALENT	3	4	YELLOW
2077780503	UL1007 / UL1061 OR EQUIVALENT	3	5	BROWN
2077780603	UL1007 / UL1061 OR EQUIVALENT	3	6	ORANGE
2077780104	UL1007 / UL1061 OR EQUIVALENT	4	1	RED
2077780204	UL1007 / UL1061 OR EQUIVALENT	4	2	NATURAL
2077780304	UL1007 / UL1061 OR EQUIVALENT	4	3	GRAY
2077780404	UL1007 / UL1061 OR EQUIVALENT	4	4	YELLOW
2077780504	UL1007 / UL1061 OR EQUIVALENT	4	5	BROWN
2077780604	UL1007 / UL1061 OR EQUIVALENT	4	6	ORANGE
WITH KEY AND CLIP SLOT P/N 				
2077781102	UL1007 / UL1061 OR EQUIVALENT	2	1	RED
2077781202	UL1007 / UL1061 OR EQUIVALENT	2	2	NATURAL
2077781302	UL1007 / UL1061 OR EQUIVALENT	2	3	GRAY
2077781402	UL1007 / UL1061 OR EQUIVALENT	2	4	YELLOW
2077781502	UL1007 / UL1061 OR EQUIVALENT	2	5	BROWN
2077781602	UL1007 / UL1061 OR EQUIVALENT	2	6	ORANGE
2077781103	UL1007 / UL1061 OR EQUIVALENT	3	1	RED
2077781203	UL1007 / UL1061 OR EQUIVALENT	3	2	NATURAL
2077781303	UL1007 / UL1061 OR EQUIVALENT	3	3	GRAY
2077781403	UL1007 / UL1061 OR EQUIVALENT	3	4	YELLOW
2077781503	UL1007 / UL1061 OR EQUIVALENT	3	5	BROWN
2077781603	UL1007 / UL1061 OR EQUIVALENT	3	6	ORANGE
2077781104	UL1007 / UL1061 OR EQUIVALENT	4	1	RED
2077781204	UL1007 / UL1061 OR EQUIVALENT	4	2	NATURAL
2077781304	UL1007 / UL1061 OR EQUIVALENT	4	3	GRAY
2077781404	UL1007 / UL1061 OR EQUIVALENT	4	4	YELLOW
2077781504	UL1007 / UL1061 OR EQUIVALENT	4	5	BROWN
2077781604	UL1007 / UL1061 OR EQUIVALENT	4	6	ORANGE

PART NUMBER LOGIC D

207778 - X X X X

CIRCUITE SIZE


0 = UL1007/1061 COMPATIBLE
1 = UL1015 / UL1230 COMPATIBLE

- 1 - 6 KEYS

1 = CLIP SLOT / WITH PANEL MOUNT
0 = NON-CLIP SLOT / WITHOUT PANEL MOUNT

SERIES NUMBERS

WITHOUT KEY P/N	WIRE STYLE	NO. OF CIRCUITS	KEYING CONFIGURATION	COLOR
2077780012	UL1015 / UL1230 OR EQUIVALENT	2	NA	BLACK
2077780013	UL1015 / UL1230 OR EQUIVALENT	3	NA	BLACK
2077780014	UL1015 / UL1230 OR EQUIVALENT	4	NA	BLACK
WITH KEY P/N 				
2077780112	UL1015 / UL1230 OR EQUIVALENT	2	1	RED
2077780212	UL1015 / UL1230 OR EQUIVALENT	2	2	NATURAL
2077780312	UL1015 / UL1230 OR EQUIVALENT	2	3	GRAY
2077780412	UL1015 / UL1230 OR EQUIVALENT	2	4	YELLOW
2077780512	UL1015 / UL1230 OR EQUIVALENT	2	5	BROWN
2077780612	UL1015 / UL1230 OR EQUIVALENT	2	6	ORANGE
2077780113	UL1015 / UL1230 OR EQUIVALENT	3	1	RED
2077780213	UL1015 / UL1230 OR EQUIVALENT	3	2	NATURAL
2077780313	UL1015 / UL1230 OR EQUIVALENT	3	3	GRAY
2077780413	UL1015 / UL1230 OR EQUIVALENT	3	4	YELLOW
2077780513	UL1015 / UL1230 OR EQUIVALENT	3	5	BROWN
2077780613	UL1015 / UL1230 OR EQUIVALENT	3	6	ORANGE
2077780114	UL1015 / UL1230 OR EQUIVALENT	4	1	RED
2077780214	UL1015 / UL1230 OR EQUIVALENT	4	2	NATURAL
2077780314	UL1015 / UL1230 OR EQUIVALENT	4	3	GRAY
2077780414	UL1015 / UL1230 OR EQUIVALENT	4	4	YELLOW
2077780514	UL1015 / UL1230 OR EQUIVALENT	4	5	BROWN
2077780614	UL1015 / UL1230 OR EQUIVALENT	4	6	ORANGE
WITH KEY AND CLIP SLOT P/N 				
2077781112	UL1015 / UL1230 OR EQUIVALENT	2	1	RED
2077781212	UL1015 / UL1230 OR EQUIVALENT	2	2	NATURAL
2077781312	UL1015 / UL1230 OR EQUIVALENT	2	3	GRAY
2077781412	UL1015 / UL1230 OR EQUIVALENT	2	4	YELLOW
2077781512	UL1015 / UL1230 OR EQUIVALENT	2	5	BROWN
2077781612	UL1015 / UL1230 OR EQUIVALENT	2	6	ORANGE
2077781113	UL1015 / UL1230 OR EQUIVALENT	3	1	RED
2077781213	UL1015 / UL1230 OR EQUIVALENT	3	2	NATURAL
2077781313	UL1015 / UL1230 OR EQUIVALENT	3	3	GRAY
2077781413	UL1015 / UL1230 OR EQUIVALENT	3	4	YELLOW
2077781513	UL1015 / UL1230 OR EQUIVALENT	3	5	BROWN
2077781613	UL1015 / UL1230 OR EQUIVALENT	3	6	ORANGE
2077781114	UL1015 / UL1230 OR EQUIVALENT	4	1	RED
2077781214	UL1015 / UL1230 OR EQUIVALENT	4	2	NATURAL
2077781314	UL1015 / UL1230 OR EQUIVALENT	4	3	GRAY
2077781414	UL1015 / UL1230 OR EQUIVALENT	4	4	YELLOW
2077781514	UL1015 / UL1230 OR EQUIVALENT	4	5	BROWN
2077781614	UL1015 / UL1230 OR EQUIVALENT	4	6	ORANGE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
FUNCTIONAL SYMBOLS  = 0  = 0  = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS	SCALE	CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE. GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0.3 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	EC NO: 760095 DRWN: GOOLAM