

TERMINAL POSITION 2

TERMINAL POSITION 1

TERMINAL POSITION 4

TERMINAL POSITION 3

MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLACK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LIGHT GRAY	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BROWN	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GREEN	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DARK GRAY	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-STONE GRAY	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YELLOW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (STANDARD PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (STANDARD OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION							
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL					BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
MX150 ASSY BLD 2X2 BK A/4	334824001	A-BLACK	GCO	PLR	M	-	-	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 LG B/4	334824002	B-LIGHT GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BR C/4	334824003	C-BROWN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824103	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 GR D/4	334824004	D-GREEN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824104	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BK A/3	334824006	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 LG B/3	334824007	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BR C/3	334824008	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824105	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 GR D/3	334824009	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824106	N/A	N/A		
						-	-						
MX150 ASSY BLD 2X2 BK A/2	334824011	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 LG B/2	334824012	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 BR C/2	334824013	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824107	N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 GR D/2	334824014	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824108	N/A	N/A		
						3	-						
MX150 ASSY BLD 2X2 BK A/0	334824016	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 LG B/0	334824017	B-LIGHT GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 BR C/0	334824018	C-BROWN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824109	N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 GR D/0	334824019	D-GREEN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824110	N/A	N/A		
						3	4						
MX150 ASSY BLD 2X2 BK A/1	334824021	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A		
						3	-						

DATE 01/23/2023

DOCUMENT NO. 334820402










REVISION E
Page 1 of 2




MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL						
MX150 ASSY BLD 2X2 BK A/3	334824022	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824023	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/3	334824024	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 BK A/2	334824025	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/4	334824103	C-DARK GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/4	334824104	D-STONE GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/3	334824105	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/3	334824106	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/2	334824107	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 SG D/2	334824108	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/0	334824109	C-DARK GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 SG D/0	334824110	D-STONE GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/2	334824111	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 YW A/4	334824112	A-YELLOW	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 LG B/3	334824113	B-LIGHT GRAY	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/2	334824115	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/2	334824116	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/2	334824117	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/3	334824118	B-LIGHT GRAY	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824119	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/3	334824120	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/1	334824121	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/2	334824122	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						-	-				









SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	
DOCUMENT STATUS	P1	RELEASE DATE
		2018/02/16 22:02:26




UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex									
	mm		1.5:1																
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16										MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
 = 0																			
 = 0	ANGULAR TOL		± 1.0 °		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14										PRODUCT CUSTOMER DRAWING				
 = 0	4 PLACES		±																
 = 0	3 PLACES		±																
 = 0	2 PLACES		± 0.1																
 = 0	1 PLACE		± 0.2		DOCUMENT NUMBER SD-33482-0001 DOC TYPE PSD DOC PART 001 REVISION E2										PRODUCT CUSTOMER DRAWING				
= 0	0 PLACES		±																
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER				
= 0							A1-SIZE		33482				GENERAL MARKET		2 OF 11				

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



RESULTS




100




KEY D


2X10




KEY A




KEY B



KEY C










KEY D

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
mm		3:1											
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
ANGULAR TOL ± 1.0°		DRWN: PMANJUNATHAC 2018/01/03											
4 PLACES ±		CHK'D: MVANSLAMBROU 2018/02/16											
3 PLACES ±		APPR: MVANSLAMBROU 2018/02/16				PRODUCT CUSTOMER DRAWING							
2 PLACES ± 0.1		INITIAL REVISION:											
1 PLACE ± 0.2		DRWN: APROFFITT 2014/04/28				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
0 PLACES ±		APPR: VKOSHYY 2014/05/18				SD-33482-0001		PSD		001		E2	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A1-SIZE		33482				GENERAL MARKET		4 OF 11	


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN FINAL-LOCK POSITION

SECTION V-V



SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	3:1
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL	± 1.0°
	4 PLACES	±
	3 PLACES	±
	2 PLACES	± 0.1
	1 PLACE	± 0.2
	0 PLACES	±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
THIRD ANGLE PROJECTION		
DRAWING		
A1-SIZE		
SERIES		
33482		
MATERIAL NUMBER		
CUSTOMER		
GENERAL MARKET		
SHEET NUMBER		
5 OF 11		


CURRENT REV DESC:			
EC NO: 171650			
DRWN: PMANJUNATHAC	2018/01/03		
CHK'D: MVANSLAMBROU	2018/02/16		
APPR: MVANSLAMBROU	2018/02/16		
INITIAL REVISION:			
DRWN: APROFFITT	2014/04/28		
APPR: VKOSHY	2014/05/14		

molex	
MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL	
PRODUCT CUSTOMER DRAWING	
DOCUMENT NUMBER	DOC TYPE DOC PART REVISION
SD-33482-0001	PSD 001 E2

SHEET DESCRIPTION
SYSTEM PACKAGING

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
	mm		4:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)								PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-33482-0001 DOC TYPE PSD DOC PART 001 REVISION E2						
	ANGULAR TOL		± 1.0 °												
	4 PLACES		±												
	3 PLACES		±												
	2 PLACES		± 0.1												
	1 PLACE		± 0.2												
	0 PLACES		±												
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												THIRD ANGLE PROJECTION		DRAWING
						A1-SIZE		33482				GENERAL MARKET		6 OF 11	


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX


CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20




90° ADAPTOR

BLADE SEALED ASSEMBLY






BACKSHELL (BKS)

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex						
	mm		1.5:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
 = 0																
 = 0	ANGULAR TOL ± 1.0 °				PRODUCT CUSTOMER DRAWING											
 = 0	4 PLACES		±													
 = 0	3 PLACES		±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14											
 = 0	2 PLACES		± 0.1													
 = 0	1 PLACE		± 0.2		DOCUMENT NUMBER SD-33482-0001					DOC TYPE		DOC PART		REVISION		
 = 0	0 PLACES		±							PSD		001		E2		
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
= 0							A1-SIZE		33482				GENERAL MARKET		7 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------


SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	



SECTION A-A




SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
	mm		3.5:1									
	GENERAL TOLERANCES (UNLESS SPECIFIED)											
	ANGULAR TOL ± 1.0 °											
		4 PLACES		±		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			PRODUCT CUSTOMER DRAWING			
		3 PLACES		±								
		2 PLACES		± 0.1								
		1 PLACE		± 0.2								
		0 PLACES		±		DOCUMENT NUMBER SD-33482-0001			DOC TYPE PSD	DOC PART 001	REVISION E2	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											
	THIRD ANGLE PROJECTION				DRAWING A1-SIZE		SERIES 33482		MATERIAL NUMBER GENERAL MARKET		SHEET NUMBER 8 OF 11	





SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	= 0	DIMENSION UNITS	mm	SCALE	3:1	CURRENT REV DESC:					molex			
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)												
	= 0	ANGULAR TOL ± 1.0 °			EC NO: 171650					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
	= 0	4 PLACES	±	DRWN: PMANJUNATHAC 2018/01/03										
	= 0	3 PLACES	±	CHK'D: MVANSLAMBROU 2018/02/16										
	= 0	2 PLACES	± 0.1	APPR: MVANSLAMBROU 2018/02/16										
	= 0	1 PLACE	± 0.2	INITIAL REVISION:										
	= 0	0 PLACES	±	DRWN: APROFFITT 2014/04/28					PRODUCT CUSTOMER DRAWING					
	= 0	APPR: VKOSHY 2014/05/14												
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES	DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
	= 0						A1-SIZE	33482	SD-33482-0001		PSD	001	E2	
	= 0								MATERIAL NUMBER		CUSTOMER	SHEET NUMBER		
	= 0							GENERAL MARKET		9 OF 11				



SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------


SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
		DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex							
	= 0	mm		2:1		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)																
	= 0	ANGULAR TOL ± 1.0 °																
	= 0	4 PLACES		±														
	= 0	3 PLACES		±														
	= 0	2 PLACES		± 0.1		PRODUCT CUSTOMER DRAWING					DOCUMENT NUMBER SD-33482-0001					DOC TYPE PSD	DOC PART 001	REVISION E2
	= 0	1 PLACE		± 0.2														
	= 0	0 PLACES		±														
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
	= 0							A1-SIZE		33482				GENERAL MARKET		10 OF 11		




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE




ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED



(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

CHARTED DIMENSIONS

CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex							
	mm		1:1														
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
 = 0																	
 = 0	ANGULAR TOL ± 1.0 °				INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING							
 = 0	4 PLACES		±														
 = 0	3 PLACES		±														
 = 0	2 PLACES		± 0.1														
 = 0	1 PLACE		± 0.2		THIRD ANGLE PROJECTION					DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
 = 0	0 PLACES		±							SD-33482-0001		PSD		001		E2	
 = 0																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
= 0							A1-SIZE		33482				GENERAL MARKET		11 OF 11		