


Connector Location A





Connector Location B



X
male

Loading Plan
acc. to TIA/EIA 568B

Y
male



6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	Step	a [m] XXX

NOTE:

For lengths < 1.0m:

- relative positioning of the connectors to each other shall be as presented in the drawing, however with an admissible angular deviation around cable axis of ± 30°

For lengths ≥ 1.0m:

-relative positioning of the connectors to each other not obligatory

*Cat.6A 10 Gbit/s Ethernet transmission possible for lengths up to 45m

Temperature range:

- Fixed installation: -40°C ... +80°C
- Dynamic installation: -40°C ... +80°C

HARTING IE Cat.6A 4x2xAWG 26/7
PUR green

09484747744XXX

Type of cable

Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by 402676	Inspected by COSTEA	Standardisation MUNTEANV	Date 2022-11-28	State Final Release	
	Department HCS - RO	Gross	Costea	Muntean			
HARTING Customised Solutions		Title RJ1 DB Cat6a Cable Assembly PUR green				Doc-Key / ECM-Nr. 100802346/UGD/024/D 500000231313	
D-32339 Espelkamp		Type TB	Number 09484747744XXX			Rev. D	Page 1/1