



DIMENSIONS:

A	1.000" ±0.031
B	1.360" ±0.031
C	0.830" ±0.063
D	0.018" X 0.041" ±0.005
E	1.200" ±0.031
G	0.250" ±0.031



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 115V, 60Hz, PIN 1 - PIN 2	12mA	Max.
Sec. N.L.V	@ 115V, 60Hz, PIN 1 - PIN 2		
	PIN 3 - PIN 4 =	5.958V	±2%
	PIN 5 - PIN 6 =	5.958V	±2%
DCR	@ 20°C, PIN 1 - PIN 2 =	546.5 Ω	±20%
	@ 20°C, PIN 3 - PIN 4 =	5.083 Ω	±20%
	@ 20°C, PIN 5 - PIN 6 =	5.477 Ω	±20%
HIPOT	PRIMARY - SECONDARY	1500V, 60Hz, 1 SEC	

REV.#	REVISION		DATE	 HAMMOND MANUFACTURING™		ELECTRONIC DIVISION		
0	RELEASED.	C.I.	06/29/17			52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5		PH # (519) 886-6181 FAX # (519) 886-9540
				DWG. BY: C. ILIE		CHK'D BY:		TITLE: PC BOARD MOUNT POWER TRANSFORMER
				DATE: 06/29/17		APP'D. BY:		
						DIMENSIONS: IN(X) MM()		DWG. NO. 161D10

HAMMOND
MANUFACTURING

PH # (519) 886-6181
FAX # (519) 886-9540