




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	DEC19/17	L.CHAN
B	ADD GOLD FLASH OPTION	DEC08/22	KELVIN



FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0. COLOUR, BLACK.


CONTACTS:

PHOSPHOR BRONZE
PLATING: REFER TO PART NUMBER FOR GOLD THICKNESS ON MATING SURFACES.
50 μ " [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100 μ " [2.54 MICRONS]
MIN. MATTE-TIN OR GOLD FLASH ON CONTACT TAILS.

AMPHENOL PART NUMBER: RJE05-188-0X10-H

GOLD PLATING

- 1 = 6 μ INCH
- 2 = 15 μ INCH
- 3 = 30 μ INCH
- 4 = 50 μ INCH
- 5 = GOLD FLASH



RECOMMENDED PANEL CUTOUT



UNLESS SPECIFIED OTHERWISE	DRAWN HANSON.C	DEC19/17
PRIMARY UNITS INCHES	CHECKED L.CHAN	DEC19/17
SECONDARY MILLIMETERS	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APP'D	
1 DECIMAL PLACE	ENG. REL. NO.	
2 DECIMAL PLACES	REF.	
3 DECIMAL PLACES ±0.015		
ANGULAR DEGREES ±1.5°	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING

Amphenol Canada Corp.
Commercial Products

RJE05 SERIES MODULAR JACK,
8 POSITION, 8 CONTACTS, UNSHIELDED
ULTRA LOW PROFILE - RoHS COMPLIANT

DWG NO.	REV
P-RJE05-188-0X10-H	B
CODE ID NO. 03554	DWG SIZE X
SCALE N/A	SHEET 1 OF 1